

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION


Part Number: [0918143112](#)
Status: **Active**
Overview: [C-Grid III Interconnects](#)
Description: 2.54mm Pitch C-Grid III Dual Row Right-Angle Shrouded Header, 12 Circuits, Tin (Sn) over Nickel (Ni)

Documents:
[3D Model](#) [Product Specification PS-99020-0001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [Packaging Specification PK-91814-005 \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
UL E29179

General
Product Family PCB Headers
Series [91814](#)
Application Signal, Wire-to-Board
Overview [C-Grid III Interconnects](#)
Product Name C-Grid III
UPC 822350913560

Physical
Breakaway No
Circuits (Loaded) 12
Circuits (maximum) 12
Color - Resin Black
Durability (mating cycles max) 30
First Mate / Last Break No
Flammability 94V-0
Glow-Wire Capable No
Guide to Mating Part No
Keying to Mating Part None
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Net Weight 1.847/g
Number of Rows 2
Orientation Right Angle
PC Tail Length 2.10mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.60mm
Packaging Type Tray
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Plating min - Mating 3.048µm
Plating min - Termination 3.048µm
Polarized to Mating Part Yes
Polarized to PCB No
Shrouded Closed Ends
Stackable No
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating -55° to +125°C
Termination Interface: Style Through Hole



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[91814](#) Series

Mates With
[90142](#) C-Grid III Crimp Housing, [90119](#) C-Grid III Crimp Terminal

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	350V AC/DC

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-91814-005
Product Specification	PS-99020-0001-001
Sales Drawing	SD-91814-001-001

This document was generated on 01/18/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION