## **Fiber Optic Detector**

### **OPF482**



#### **Features:**

- High speed, low capacitance
- Popular ST® style receptacle
- Pre-tested with fiber to assure performance
- Component pre-mounted and ready to use
- 100MHz operation minimum



### **Description:**


The OPF482 is a low noise silicon PIN photodiode mounted in a low cost package for fiber op@c applica@ons. It offers fast response at moderate bias and is compa@ble with LED and laser diode sources in the 800-1000 nm wavelength region. Low capacitance improves signal to noise performance in typical short haul LAN applica@ons.

The OPF482 is designed to be compaible with mulimode opical fibers from 50/125 to 200/300 microns.

### **Applications:**

- Industrial Ethernet equipment
- Copper-to-fiber media conversion
- Intra-system fiber op@c links
- Video surveillance systems

## Typical Responsivity





RoHS

# **Fiber Optic Detector**

## **OPF482**



## **Electrical Specifications**

### Absolute Maximum Ratings (T<sub>A</sub> = 25° C unless otherwise noted)


Storage Temperature Range	-55° C to +100° C
Operating Temperature Range	-40° C to +85° C
Lead Soldering Temperature <sup>(1)</sup>	260° C
Continuous Power Dissipation <sup>(2)</sup>	200 mW
Maximum Reverse Voltage	100 VDC


## Electrical Characteristics (T<sub>A</sub> = 25° C unless otherwise noted)


SYMBOL	PARAMETER	MIN	ТҮР	MAX	UNITS	TEST CONDITIONS
R	Responsivity	0.45	0.55		A/W	V <sub>R</sub> = 5.0V; 50/125μm fiber; I = 850nm
I <sub>D</sub>	Dark Current		0.1	5.0	nA	V <sub>R</sub> = 5.0V
l <sub>p</sub>	Peak Response Wavelength		905		nm	
t <sub>r</sub>	Output Rise Time		2.0		ns	V <sub>R</sub> = 5V; R <sub>L</sub> = 50W, 10%-90%
C <sub>T</sub>	Total Capacitance		1.5	2.0	pF	V <sub>R</sub> = 5V

### Notes:

- 1. Maximum of 5 seconds with soldering iron. Duration can be extended to 10 seconds when flow soldering. RMA flux is recommended.
- 2. De-rate linearly at 2.67mW/°C above 25°C.







Issue A 11/2016 Page 2