



PANDUIT PART NO.	MAX BUNDLE DIAMETER	PACKAGE QTY	LENGTH ('L") +/- .3" [7]
MLTFC2S-CP316	2" [51]	100	7.9" [201]
MLTFC4S-CP316	4" [102]	100	14.3" [361]
MLTFC6S-CP316	6" [152]	100	20.5" [521]
MLTFC8S-CP316	8" [203]	100	26.8" [679]



```

1.) APPLICATION TOOLS - GS4MT,PPTMT,ST2MT,ST3MT,HTMT
2.) MINIMUM LOOP TENSILE STRENGTH - 100 LBS. (445 NEWTONS)
   WHEN TESTED ON A 1.5" MANDREL.
3.) BRACKETS [    ] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE
   SHOWN FOR REFERENCE ONLY
4.) TOLERANCES:
   .XXX =  $\pm .010$  [ .25 ]
   .XX  =  $\pm .02$  [ .5 ]
   .X   =  $\pm .03$  [ .8 ]
   ANGLES =  $\pm 2^\circ$ 
5.) MATERIAL: 316 STAINLESS STEEL
6.) COATING - POLYESTER
   COATING THICKNESS: .002 MIN./ .005 MAX. PER SIDE

```



SECTION A - A
SCALE 8:1

						PANDUIT CORP. TINLEY PARK, ILLINOIS				
01A	2/12	MIM	RGRO	NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY		METAL LOCKING TIE - COATED STANDARD SERIES-316 STAINLESS STEEL (CUSTOMER DRAWING)				
00A	8/05	JAMB	EJD	RELEASED						SS00021
REV	DATE	BY	CHK	DESCRIPTION		ECN #	DRAWN BY JAMB	CHK'D EJD	SCALE 2x	DRAWING NO. N41214BS_DC