

4		3		2		1			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION					
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.									
LOC		DIST		REVISIONS					
G		14		P	LTR	DESCRIPTION	DATE	DWN	APVD
				G		REV PER ECR 07-027324	13NOV07	JR	TM

1 STAMP AMP 16-14* APPROX AS SHOWN

2 WIRE INSULATION DIA: 2.7-3.8 [.105-.150]

3 TONGUE MATERIAL THK: 0.78±0.05 [.031±.002]

4 BODY & SLEEVE: TIN PLATE PER ASTM B545,

5 BODY & SLEEVE- CU PER ASTM B152
INSULATION - NYLON, COLOR - BLUE

6 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.

INSULATION

SLEEVE

BODY

4.34±0.08
[.171±.003] DIA
FOR #8 STUD

1

6.35
[.250]

7.11
[.280]
MIN

17.37 [.684] MAX

20.65 [.813] MAX

6

OBSOLETE		-5000	ON TAPE	2	130476	1
		1000	LOOSE PIECE	130476		
		QTY	PACKAGE TYPE	PART NO		

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 150°C MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 12NOV07		Tyco Electronics Corporation Harrisburg, Pa 17105-3608													
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK T MICHIELUTTI 12NOV07		NAME											
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] STRANDED		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD T MICHIELUTTI 12NOV07		PRODUCT SPEC											
FOR ORDER ENTRY		1-800-526-5142		MATERIAL		FINISH		APPLICATION SPEC		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO					
		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		- 5		- 4		WEIGHT		A3		00779		C-130476		-					
CUSTOMER DRAWING										SCALE		4:1		SHEET		1 OF 1		REV		G	

AMP 1470-19 REV 31MAR2000