

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

85003-3110

Status:


Active

Overview:

DIN 41612

Description:

2.54mm Pitch DIN 41612 C Style Male Header, Right Angle, Through Hole, 0.60µm Selective Gold (Au) Plating, 96 Circuits, without Mounting Clips, No Flux Proof



Series

image - Reference only

Documents:

- [Drawing \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)
- [Product Specification PS-85003-0001 \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Backplane Connectors
Series	85003
Application	Backplane
Comments	No Mounting Clips. No Flux Proof. 4.20mm Last-Mate-First-Break Contacts. 4.80mm Normal Contacts
Component Type	PCB Header
Overview	DIN 41612
Product Name	IEC 603-2/DIN 41612
Style	C
UPC	800753874039

Physical

Circuits (Loaded)	96
Circuits (maximum)	96
Circuits Detail	Standard Contacts at: A:a1,a2,a3,a31,a32; C:c2,c3,c31; . Last-Mate-First-Break Contacts at: D:a4-a30; E:b1-b32; F:c1,c4-c30,c32
Color - Resin	Gray
Durability (mating cycles max)	400
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Number of Columns	16
Number of Pairs	Open Pin Field
Number of Rows	3
Orientation	Right Angle
PC Tail Length	3.00mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Carton
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.610µm
Plating min - Termination	2.540µm
Polarized to PCB	Yes

<u>EU RoHS</u>	<u>China RoHS</u>
Compliance Status	
Not Reviewed	
REACH SVHC	
Not Reviewed	
Low-Halogen Status	
Not Reviewed	

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
85003Series

Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55°C to +125°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	1A
Data Rate	622.0 Mbps
Voltage - Maximum	250V AC (RMS)

Material Info

Reference - Drawing Numbers

Product Specification	PS-85003-0001
Sales Drawing	SD-85003-3110

This document was generated on 12/10/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

85003-3110