


Features


- Low Forward Voltage Drop
- Excellent High Temperature Stability
- Patented Super Barrier Rectifier Technology
- Soft, Fast Switching Capability
- **Lead Free Finish, RoHS Compliant (Note 1)**
- **“Green” Molding Compound (No Br, Sb)**
- Qualified to AEC-Q101 Standards for High Reliability

Mechanical Data

- Case: TO252 (DPAK)
- Case Material: Molded Plastic, UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Matte Tin Finish annealed over Copper leadframe. Solderable per MIL-STD-202, Method 208 (E3)
- Weight: 0.33 grams (approximate)



Top View



Polarity


Ordering Information (Note 2)

Part Number	Qualification	Case	Packaging
SBR1045D1-13	Commercial	TO252 (DPAK)	2500/Tape & Reel, 13-inch
SBR1045D1Q-13	Automotive	TO252 (DPAK)	2500/Tape & Reel, 13-inch

Notes:

1. EU Directive 2002/95/EC (RoHS). All applicable RoHS exemptions applied, see EU Directive 2002/95/EC Annex Notes.
2. For packaging details, go to our website at <http://www.diodes.com>.

Marking Information



SBR1045 = Product Type Marking Code
 AB = Foundry and Assembly Code
 YYWW = Date Code Marking
 YY = Last two digits of year (ex: 08 = 2008)
 WW = Week (01 - 53)

SBR is a registered trademark of Diodes Incorporated.

SBR1045D1
Document number: DS31374 Rev. 7 - 2

1 of 5
www.diodes.com

June 2011
© Diodes Incorporated

Maximum Ratings @ $T_A = 25^\circ\text{C}$ unless otherwise specified

Single phase, half wave, 60Hz, resistive or inductive load.
For capacitance load, derate current by 20%.

Characteristic	Symbol	Value	Unit
Peak Repetitive Reverse Voltage	V_{RRM}		
Working Peak Reverse Voltage	V_{RWM}	45	V
DC Blocking Voltage	V_{RM}		
RMS Reverse Voltage	$V_{R(\text{RMS})}$	32	V
Average Rectified Output Current @ $T_C = 140^\circ\text{C}$	I_O	10	A
Non-Repetitive Peak Forward Surge Current 8.3ms	I_{FSM}	90	A
Single Half Sine-Wave Superimposed on Rated Load			
Repetitive Peak Avalanche Power (1μs, 25°C)	P_{ARM}	5000	W

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Maximum Thermal Resistance			
Thermal Resistance Junction to Ambient (Note 3)	$R_{\theta JA}$	29	°C/W
Thermal Resistance Junction to Case (Note 3)	$R_{\theta JC}$	3	
Operating and Storage Temperature Range	T_J, T_{STG}	-65 to +150	°C

Electrical Characteristics @ $T_A = 25^\circ\text{C}$ unless otherwise specified

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
Reverse Breakdown Voltage (Note 4)	$V_{(BR)R}$	45	-	-	V	$I_R = 0.45\text{mA}$
Forward Voltage Drop (per leg)	V_F	-	0.42 0.37 - 0.50	0.48 0.41 0.58 0.56	V	$I_F = 5\text{A}, T_J = 25^\circ\text{C}$ $I_F = 5\text{A}, T_J = 125^\circ\text{C}$ $I_F = 10\text{A}, T_J = 25^\circ\text{C}$ $I_F = 10\text{A}, T_J = 125^\circ\text{C}$
Leakage Current (Note 4)	I_R	-	50 12	500 40	μA mA	$V_R = 45\text{V}, T_J = 25^\circ\text{C}$ $V_R = 45\text{V}, T_J = 125^\circ\text{C}$
Total Capacitance	C_T	-	400	-	pF	$V_R = 5\text{V}, f = 1\text{MHz}$ $T_J = 25^\circ\text{C}$

Notes: 3. Device mounted on polyimide substrate, 240mm² Copper pad, double-sided PC Board.

4. Short duration pulse test used to minimize self-heating effect.

5. Device mounted on polyimide substrate, 2" * 2" Copper pad, double-sided PC Board with minimum recommended pad layout.




Fig. 1 Forward Power Dissipation




Fig. 3 Typical Reverse Characteristics




Fig. 5 Forward Current Derating Curve




Fig. 2 Typical Forward Characteristics




Fig. 4 Total Capacitance vs. Reverse Voltage





Fig. 6 Operating Temperature Derating


SBR is a registered trademark of Diodes Incorporated.

SBR1045D1

Document number: DS31374 Rev. 7 - 2




Package Outline Dimensions



TO252			
Dim	Min	Max	Typ
A	2.19	2.39	2.29
A1	0.00	0.13	0.08
A2	0.97	1.17	1.07
b	0.64	0.88	0.783
b2	0.76	1.14	0.95
b3	5.21	5.46	5.33
c2	0.45	0.58	0.531
D	6.00	6.20	6.10
D1	5.21	—	—
e	—	—	2.286
E	6.45	6.70	6.58
E1	4.32	—	—
H	9.40	10.41	9.91
L	1.40	1.78	1.59
L3	0.88	1.27	1.08
L4	0.64	1.02	0.83
a	0°	10°	—

All Dimensions in mm

Suggested Pad Layout



Dimensions	Value (in mm)
Z	11.6
X1	1.5
X2	7.0
Y1	2.5
Y2	7.0
C	6.9
E1	2.3

SBR is a registered trademark of Diodes Incorporated.

SBR1045D1
Document number: DS31374 Rev. 7 - 2

4 of 5
www.diodes.com

June 2011
© Diodes Incorporated

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2011, Diodes Incorporated

www.diodes.com

SBR is a registered trademark of Diodes Incorporated.

SBR1045D1
Document number: DS31374 Rev. 7 - 2

5 of 5
www.diodes.com

June 2011
© Diodes Incorporated