










NOTES

1.COPLANARITY IS 0.1mm MAX.
2.MATERIAL : HOUSING-HIGH TEMPERATURE THERMOPLASTIC, GLASS FILLED, UL 94V-0, COLOR: NATURE(WHITE)
TERMINAL- COPPER ALLOY,
FITTING NAIL- COPPER ALLOY

PICK AND PLACE COVER-HIGH TEMPERATURE THERMOPLASTIC, GLASS FILLED UL 94V-0, COLOR: NATURE(WHITE)
3.FINISHES : TERMINAL : 48126-XX01:
TIN MATTE PLATED OVER ALL
THICKNESS : 3.05 MICROMETER MINIMUM,
NICKEL UNDERPLATED OVER ALL,
THICKNESS : 1.27 MICROMETER MINIMUM;
48126-XX11:
GOLD FLASH OVER ALL
THICKNESS : 0.025 MICROMETER MINIMUM,
NICKEL UNDERPLATED OVER ALL,
THICKNESS : 1.27 MICROMETER MINIMUM,
FITTING NAIL : 48126-XX01:
TIN MATTE PLATED OVER ALL
THICKNESS : 3.05 MICROMETER MINIMUM,
NICKEL UNDERPLATED OVER ALL,
THICKNESS : 1.27 MICROMETER MINIMUM;
48126-XX11:
GOLD FLASH OVER ALL
THICKNESS : 0.025 MICROMETER MINIMUM,
NICKEL UNDERPLATED OVER ALL,
THICKNESS : 1.27 MICROMETER MINIMUM,

4.PRODUCT SPECIFICATION REFER TO PS-48126-001
5.DRAWING PACKAGING REFER TO PK-48126-001
6.TEST SUMMARY REFER TO TS-48210-001
7.P/N LEGEND 48126-XXX1

NO OF CKTS

PLATING
0:MATTE TIN
1:GOLD FLASH OVER ALL

8.LEAD-FREE AND RoHS COMPLIANT PRODUCT

MOLEX P/N	DMA	DIMB	DIMC	DIMD	CKT	AVAILABLE
-	3.2	8.2	7.2	4.75	10	-
48126-12X1	4.0	9.0	8.0	5.55	12	YES
-	4.8	9.8	8.8	6.35	14	-
-	5.6	10.6	9.6	7.15	16	-
48126-20X1	7.2	12.2	11.2	8.75	20	YES
48126-22X1	8.0	13.0	12.0	9.55	22	YES
48126-24X1	8.8	13.8	12.8	10.35	24	YES
48126-30X1	11.2	16.2	15.2	12.75	30	YES



ADD P/N EC NO: SH-2008-0112 DRW: NEKA001 CHKD: APPR: WMSCHANG	2007/10/15 2007/10/15 2007/10/15 2007/10/19	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=2	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 6:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 		
					mm	INCH	DRAWN BY BERNIE	DATE 2005/01/27	TITLE MDC 0.8 MM BTB PLUG CONNECTOR SMT S/T TYPE			
				4 PLACES	± ---	± ---	CHECKED BY ERIC KAO	DATE 2005/01/27				
				3 PLACES	± ---	± ---	APPROVED BY WILSON	DATE 2005/01/27				
				2 PLACES	± 0.25	± ---	MATERIAL NO. SEE NOTES		DOCUMENT NO. SD-48126-001		SHEET NO. 1 OF 1	
				1 PLACE	± 0.25	± ---						
				ANGULAR ± 3 °		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		