



ENCLOSURE FOR COMMAND DEVICES, 22MM,
ROUND, ENCLOSURE MATERIAL PLASTIC,
ENCLOSURE TOP PART GRAY,
1 COMMAND POINT, A=PUSHBUTTON RED, 1NC,
SCREW CONNECTION, FLOOR MOUNTING,
LABEL: O, 1 X M20 EACH AT TOP AND BOTTOM

Enclosure:

Design of the enclosure	Enclosure for command and signaling devices with standard equipment
Material / of the enclosure	plastic
Color / of top part of the enclosure	grey
Number of Command Points	1
Product component / protective collar	No
Form / of the enclosure front	Square
Design of electrical connection / on enclosure	Cable routing above and below, both 1 x M20
Type of mounting / of enclosure	Vertical
Product function / EMERGENCY STOP function	No

Actuator / signaling device:

Design of the operating mechanism	Pushbutton
Assembling of the commanding and signaling device	A = Pushbutton
Number of mushroom pushbuttons	0
Number of indicator lights	0
Number of pushbuttons	1
Number of key-operated switches	0
Material / of the activation element	plastic
Product component / front ring	Yes

Material / of the front ring		plastic
Color / of the front ring		black
Type of unlocking device		without

Holder:

Material / of the holder		Plastic
---------------------------------	--	---------

Contact block / lampholder

Number of switching elements		1
Number of NC contacts / for auxiliary contacts		1
Number of NO contacts / for auxiliary contacts		0
Number of change-over switches / for auxiliary contacts		0
Product function / positive opening		Yes
Number of lampholders		0
Type of fixing/fixation / for contact blocks		Floor mounting
Design of electrical connection / of contact blocks, socket, and accessories		Screw-type terminal
Product component / fluorescent materials		No
Product extension / optional / fluorescent materials		No

Accessories:

Number of backing plates		0
Number of labeling plates		1
Labeling / of the name plate for command devices		O
Color / of labeling plate		Black
Product component / holder for 3 switching elements		No

General technical details:

Type of voltage / of the operating voltage		AC/DC
Operating voltage		
• for DC		
• rated value	V	5 ... 230
• 1 / for DC / rated value	V	230
• at 50 Hz / at AC		
• rated value	V	5 ... 400
• 1 / at 50 Hz / for AC / rated value	V	400
• at 60 Hz / at AC		
• rated value	V	5 ... 300
• 1 / at 60 Hz / for AC / rated value	V	300
Operating current		
• at AC-12		
• at 24 V / rated value	A	10

• at 48 V / rated value	A	10
• at 110 V / rated value	A	10
• at 230 V / rated value	A	10
• at 400 V / rated value	A	10
• at AC-15		
• at 24 V / rated value	A	6
• at 48 V / rated value	A	6
• at 110 V / rated value	A	6
• at 230 V / rated value	A	6
• at 400 V / rated value	A	3
• at DC-12		
• at 24 V / rated value	A	10
• at 48 V / rated value	A	5
• at 110 V / rated value	A	2.5
• at 230 V / rated value	A	1
• at DC-13		
• at 24 V / rated value	A	3
• at 48 V / rated value	A	1.5
• at 110 V / rated value	A	0.7
• at 230 V / rated value	A	0.3
Delivery state / pre-wired on strip terminal		No
Product component / stand/pedestal		No
Resistance against shock		
• for devices without incandescent lamp / according to IEC 60068-2-27		<= 50g
Resistance against vibration / according to IEC 60068-2-6		20 ... 200 Hz: 5g
Item designation		
• according to DIN EN 61346-2		S
• according to DIN 40719 extendable after IEC 204-2 / according to IEC 750		S
Tightening torque / of the screws in the bracket / maximum	N·m	1
Ambient temperature		
• during operating	°C	-25 ... +70
• during storage	°C	-40 ... +80
Protection class IP		IP65
climatic class / during the operating phase / according to EN 60721		3K6
Shape / of the installation hole		round
Mounting diameter	mm	22
Width	mm	85
Height	mm	85

Depth

mm

64

Certificates/approvals:

General Product Approval	Declaration of Conformity	Test Certificates
 CSA	 GOST	 UL
 EG-Konf.		Special Test Certificate
Shipping Approval	other	
 ABS	 DNV	 LRS
		 PRS
		Confirmation Environmental Confirmations

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

Cax online generator:

<http://www.siemens.com/cax>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SB3801-0DB3/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3SB3801-0DB3

last change:

Feb 8, 2013