




PANDUIT PART NO. *	BUNDLE DIA.		A	B	C	D	E	F	G	MIN. LOOP TENSILE lbs (N)	CROSS- SECTION	RECM. FASTENER	WEIGHT lbs/100pcs (g)
	MIN. in (mm)	MAX. in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)				
PLC2H-S25	.18 (4.8)	2.00 (51)	.075 (1.9)	.300 (7.6)	.94 (23.9)	.265 (6.7)	.500 (12.7)	9.0 (229)	.260 (6.6)	120 (534)	HEAVY	1/4 (M6) SCREW	.914 (415)
PLC4H-S25	.18 (4.8)	4.00 (102)	.075 (1.9)	.300 (7.6)	.94 (23.9)	.265 (6.7)	.500 (12.7)	15.1 (384)	.260 (6.6)	120 (534)	HEAVY	1/4 (M6) SCREW	1.44 (653)

NOTES:

- *1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
 2) RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.

SS_24665_XX.PRT

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.

PANDUIT CORP. TINLEY PARK, ILLINOIS

PAN-TY LOCKING CLAMP TIE
PLC HEAVY SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) $\pm$.005 (XXX) $\pm$.020 (.51)
(.XX) $\pm$.02 (.5) ANGLES $\pm$.005

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
D.L.Moody

MAT'L:

SCALE NONE

DATE
9-14-89

NYLON 6.6

DRAWING NO.
SS-24665DWG
A
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
-----	------	----	-----	-------------	-----	---	------	-----

CHK'D
HVP