







RECOMMENDED MOUNTING:
M4 FASTENER WITH 6.00 IN-LB [7.00 KGF-CM] OF TORQUE MAX.



CHARACTERISTICS

ELECTRICAL RATING	15A 250 VAC UL APPROVED 15A 250 VAC VDE APPROVED
TERMINAL	SCREW
OPER. FORCE MAX.	300 GMS
RELEASE FORCE MIN.	50 GMS
PRETRAVEL MAX.	.157 [4 mm]
OVERTRAVEL MIN.	.062 [1.6 mm]
MOVE. DIFF. MAX.	.051 [1.3 mm]
OPERATING POSITION	1.094 TO 1.157 [27.8 TO 29.4mm]

DWN: JED
APVD: SB
DATE: 25-May-04



THE CONFIDENTIAL AND PROPRIETARY
INFORMATION CONTAINED IN THIS DOCUMENT
IS OWNED BY CHERRY ELECTRICAL PRODUCTS,
A DIVISION OF THE CHERRY CORPORATION WHO
MUST GIVE WRITTEN PERMISSION BEFORE THE
DOCUMENT OR INFORMATION CAN BE COPIED,
DISCLOSED OR USED IN ANY WAY.

TOLERANCE UNLESS SPECIFIED

1. XX	X. XXX	ANGLES
± 0.02	± 0.015	± 0.0

CHERRY
ELECTRICAL PRODUCTS

NAME / DESCRIPTION

SPEC DRAWING

C ITEM NO. GPTCR01

D	13123	25-Jul-05	JED	SG
REV	FCN	NO	DATE	PREP/APVD

PROJECT / ESK

SCALE: 2:1

11290 80TH AVENUE
PLEASANT PRAIRIE, IL 60159

ORIGINAL ON PAGE