

Type: 3130-F



Single, two and three pole rocker switch/thermal trip free circuit breakers (S-type TO CBE to EN 60934) of compact design for snap-in panel mounting. Available either with protection on one/both/all poles or, in the case of the double pole version, protection on one pole only. Illumination is optional and there is a choice of rocker colours. Approved to CBE standard EN 60934 (IEC 60934).

Voltage rating:

- 3 AC 415 V
- AC 240 V
- DC 50 V
- UL/CSA: 3 AC 250 V
- UL/CSA: AC 250 V

Current ratings:

from 0.1 A to 20 A 1 pole
from 0.1 A to 16 A 2 and 3 pole

Number of poles:

single pole
double pole
three pole

Mounting method:

flange

Terminal design:

blade terminals
screw terminals

Actuation:

rocker

Auxiliary contacts:

without auxiliary contacts

Water splash protection:

with water splash protection
without water splash protection

Illumination:

with illumination
without illumination

Typical life:

30,000 operations at $1 \times I_N$, inductive, 1 and 3 pole
50,000 operations at $1 \times I_N$, inductive, 2 pole


Interrupting capacity I_{cn} :

0.1...2 A: $10 \times I_N$
2.5...20 A: 150 A 1 pole
2.5...16 A: 250 A 2 pole
2.5...12 A: 150 A 3 pole
14...16 A: 130 A 3 pole


Approvals:

VDE, UL, CSA

Dimensions



Internal connection diagrams



Description

Single, two and three pole rocker switch/thermal trip free circuit breakers (S-type TO CBE to EN 60934) of compact design for snap-in panel mounting. Available either with protection on one/both/all poles or, in the case of the double pole version, protection on one pole only. Illumination is optional and there is a choice of rocker colours.

Approved to CBE standard EN 60934 (IEC 60934).

Typical applications

Motors, transformers, solenoids, household and office machines, electrical tools, mobile homes, boating, construction vehicles, medical equipment to EN 60601.

Standard current ratings and typical internal resistance values

Current rating (A)	Internal resistance per pole (Ω)	Current rating (A)	Internal resistance per pole (Ω)
0.1	94	4	0.0435
0.2	24	5	0.0325
0.3	12	6	0.0215
0.4	5.30	7	0.0165
0.5	4.20	8	0.0165
0.8	1.50	10	< 0.02
1	0.9	12	< 0.02
1.2	0.80	14	< 0.02
1.5	0.45	15	< 0.02
2	0.27	16	< 0.02
2.5	0.0785	18	< 0.02
3	0.0595	20	< 0.02
3.5	0.0565		

Illumination voltage/power consumption


operating voltage	power consumption	
	filament/neon (B)	LED (G, R, Y)
6 V	60 mA	9 mA
12 V	20 mA	9 mA
24 V	20 mA	9 mA
48 V	20 mA	1.5 mA
115 V	< 1.5 mA	< 1 mA*
230 V	< 1.5 mA	< 1 mA*
415 V	< 1 mA	not available

* single pole version only

Approvals

Authority	Voltage rating	Current rating
VDE (EN 60934)	AC 240/415 V	0.1...20 A single pole
		0.1...16 A multipole
	DC 50 V	0.1...8 A single pole
		0.1...16 A multipole
UL, CSA	DC 28 V	0.1...20 A single pole
	AC 250 V; DC 50 V	0.1...16 A 1- and 2- pole
	3 AC 250 V	0.1...12 A 3-pole

All dimensions without tolerances are for reference only. In the interest of improved design, performance and cost effectiveness the right to make changes in these specifications without notice is reserved. Product markings may not be exactly as the ordering codes. Errors and omissions excepted.



Technical data

For further details please see chapter: Technical Information

Voltage rating	AC 240 V; 3 AC 415 V; DC 50 V (UL: AC 250 V; 3 AC 250 V; DC 50 V)		
Current ratings	0.1...20 A	1-pole 0.1...16 A 2- and 3-pole	
Typical life	1-pole AC 240 V: 0.1...20 A 30,000 operations at 1 x I _N , inductive DC 50 V: 0.1...4 A 30,000 operations at 1 x I _N , inductive 4.5...16 A 30,000 operations at 1 x I _N , resistive DC 28 V: 4.5...20 A 30,000 operations at 1 x I _N , inductive 2-pole AC 240 V: 0.1...16 A 50,000 operations at 1 x I _N , inductive DC 50 V: 0.1...16 A 50,000 operations at 1 x I _N , inductive 3-pole 3 AC 415 V: 0.1...16 A 30,000 operations at 1 x I _N , inductive		
Ambient temperature	-30...+60 °C (-22...+140 °F)		
Insulation co-ordination (IEC 60664 and 60664 A)	rated impulse withstand voltage 2.5 kV reinforced insulation in operating area	pollution degree 2	
Dielectric strength (IEC 60664 and 60664A) operating area current path/current path	test voltage AC 3,000 V AC 1,500 V		
Insulation resistance	> 100 MΩ (DC 500 V)		
Interrupting capacity I _{cn}	0.1...2 A 2.5...20 A 2.5...16 A 2.5...12 A 14 + 16 A	10 x I _N 150 A 250 A 150 A 130 A	1-pole 2-pole 3-pole 3-pole
Interrupting capacity (UL 1077)	I _N 1- + 2-pole 3-pole 1- + 2-pole	0.1...12 A AC 250V/3500A 3AC 250V/5000A DC 50V/2000A	14...16 A AC 250V/3500A DC 50V/2000A
Degree of protection (IEC 60529/DIN 40050)	operating area IP40 terminal area IP00		
Vibration	5 g (57-500 Hz) ± 0.38 mm (10-57 Hz) to IEC 60068-2-6, test Fc 10 frequency cycles/axis		
Shock	1-pole: 25 g (11 ms) 2 + 3-pole: 20 g (11 ms) to IEC 60068-2-27, test Ea		
Corrosion	96 hours at 5 % salt mist, to IEC 60068-2-11, test Ka		
Humidity	240 hours at 95 % RH, to IEC 60068-2-3, test Ca		
Mass	approx. 45 g (three pole) approx. 31 g (double pole) approx. 17 g (single pole)		

Ordering information - 1-pole

Type No.	3130	rocker switch/circuit breaker
Mounting	F	snap in frame
Frame	1	standard
	3	special single pole version
Number of poles	1	single pole, thermally protected
A	1-pole, unprotected**	
Frame mounting	0	panel thickness 1-2.5 mm (.039-.099 in) (only 3130-F1...-...)
	1	panel thickness 1.5-3.2 mm (.059-.126 in) (only 3130-F3.1-...)
Terminal design	P7	blade terminals DIN 46244-C-Ms-S (QC 2x.110)
H7	for terminals 1.1, 2.1 3.1 terminal screws M 3.5 for terminals 1.2, 2.2, 3.1 blade terminals (QC 2x.110)	
N7	blade terminals (QC 2x.110), with shunt terminal	
Characteristic curve	T1	thermal, 1.05-1.4 I _N
	Q1	switch, only with terminal design -N7
Switch style	W	rocker
	U	momentary switch function
Switch colour designation	opaque	translucent
	01 black	12 white
	02 white	14 red
	04 red	19 green
	09 green	29 black, rocker with green dot
Rocker markings	A	dot (ON position, only with switch colour designation 29)
	Q	"I" and "O" moulded in
Rocker illumination (optional)	12 Q Y	white rocker, yellow LED, AC/DC
	14 Q R	red rocker, red LED, AC/DC
	19 Q Y	green rocker, yellow LED, AC/DC
	29 A G	black rocker with dot, green LED
Illumination voltage range* (optional)	1	4 - 7 V (G,R,Y)
	2	10 - 14 V (G,R,Y)
	3	20 - 28 V (G,R,Y)
	4	42 - 54 V (R,Y)
	6	90 - 140 V (R,Y)
	7	185 - 275 V (R,Y)
	X	LED, DC 8 - 10 mA ***
Current ratings	0.1...20 A	
3130 - F 1 1 0 - P7 T1 - W 12 Q Y 7 - 5 A	ordering example	

* N/A for non-illuminated version

** unprotected poles have to ordered with terminal design N7

*** without series resistor and diode, to be selected by customer.

Recommendation:

4-7 V Rv 0.43 kΩ

10-14 V Rv 1.1 kΩ

20-28 V RV 2.7 kΩ

diode 1N4007

Ordering information - multipole


Type No.	3130	rocker switch/circuit breaker multipole
Mounting	F	snap in frame
Frame	1	standard
Number of poles	2	2-pole, thermally protected
	3	3-pole, thermally protected
	5	2-pole, thermally protected on one pole only
	6	3-pole, thermally protected on two poles only
B	2-pole, unprotected**	
C	3-pole, unprotected**	
Frame mounting	0	panel thickness 1-2.5 mm (.039-.099 in) (only 3130-F1...-...)
Terminal design	P7	blade terminals DIN 46244-C-Ms-S (QC 2x.110)
H7	for terminals 1.1, 2.1 3.1 terminal screws M 3.5; for terminals 1.2, 2.2, 3.1 blade terminals (QC 2x.110)	
N7	blade terminals DIN 46244-C-Ms-S (QC 2x.110), with shunt terminal	
Characteristic curve	T1	thermal, 1.05-1.4 I _N
	Q1	switch, only with terminal design -N7
Switch style	W	rocker
	U	momentary switch function
Switch colour designation	opaque	translucent
	01 black	12 white
	02 white	14 red
	04 red	19 green
	09 green	
Rocker markings	Q	"I" and "O" moulded in
Rocker illumination (optional)	B	filament (≤ AC/DC 48 V), neon (≥ AC 115 V)
	G	green LED, DC
	R	red LED, DC
	Y	yellow LED, DC
Illumination voltage range* (optional)	1	4 - 7 V (B,G,R,Y)
	2	10 - 14 V (B,G,R,Y)
	3	20 - 28 V (B,G,R,Y)
	4	42 - 54 V (B,R,Y)
	6	90 - 140 V (B)
	7	185 - 275 V (B)
	8	320 - 450 V (B)
Current ratings	0.1...16 A	
3130 - F 1 3 0 - P7 T1 - W 12 Q B 7 - 5 A	ordering example	

* N/A for non-illuminated version


** unprotected poles have to ordered with terminal design N7

Dimensions


3130-F110-...



3130-F120-...



3130-F130-...



3130-F311-...

