



## HP10-144-U1A

**3.0 m | 10 ft High Performance Parabolic Shielded Antenna, single-polarized, 14.400–15.350 GHz, UG-541A/U, gray antenna, standard white radome with flash, standard pack—one-piece reflector**

### General Specifications

Antenna Type	HP - High Performance Parabolic Shielded Antenna, single-polarized
Diameter, nominal	3.0 m   10 ft
Packing	Standard pack
Radome Color	White
Radome Material	Standard
Reflector Construction	One-piece reflector
Antenna Input	UG-541A/U
Antenna Color	Gray
Antenna Type	HP - High Performance Parabolic Shielded Antenna, single-polarized
Diameter, nominal	3.0 m   10 ft
Flash Included	Yes
Polarization	Single

### Electrical Specifications

Operating Frequency Band	14.400 – 15.350 GHz
Beamwidth, Horizontal	0.5 °
Beamwidth, Vertical	0.5 °
Cross Polarization Discrimination (XPD)	30 dB
Front-to-Back Ratio	71 dB
Gain, Low Band	50.2 dBi
Gain, Mid Band	50.5 dBi
Gain, Top Band	50.8 dBi
Operating Frequency Band	14.400 – 15.350 GHz
Radiation Pattern Envelope Reference (RPE)	LP807
Return Loss	26.4 dB
VSWR	1.10

### Mechanical Specifications

Fine Azimuth Adjustment	±5°
Fine Elevation Adjustment	±5°
Mounting Pipe Diameter	115 mm   4.5 in
Net Weight	261 kg   575 lb
Side Struts, Included	1 inboard   1 outboard
Side Struts, Optional	2 outboard

# Product Specifications

COMMSCOPE®

HP10-144U1A

Wind Velocity Operational	110 km/h   68 mph
Wind Velocity Survival Rating	200 km/h   124 mph

## Wind Forces At Wind Velocity Survival Rating


Angle a for MT Max	-110 °
Axial Force (FA)	17632 N   3964 lbf
Force on Inboard Strut Side	5870 N   1320 lbf
Force on Outboard Strut Side	8840 N   1987 lbf
Side Force (FS)	8734 N   1963 lbf
Twisting Moment (MT)	-8630 N•m
Weight with 1/2 in (12 mm) Radial Ice	577 kg   1272 lb
Zcg with 1/2 in (12 mm) Radial Ice	818 mm   32 in
Zcg without Ice	767 mm   30 in

# Product Specifications

COMMSCOPE®

HP10-144-U1A

## Wind Forces At Wind Velocity Survival Rating Image



## Packed Dimensions


Gross Weight, Packed Antenna	542.0 kg   1194.9 lb
Height	2530.0 mm   99.6 in
Length	3360.0 mm   132.3 in
Volume	19.5 m <sup>3</sup>
Width	2290.0 mm   90.2 in

# Product Specifications

COMMSCOPE®

HP10-144-U1A

## Antenna Dimensions And Mounting Information



ANTENNA DIMENSIONS			
All dimensions in mm (inches)			
A	3160 (124.5)	K	950 (37.5)
B	3315 (130.5)	L	200 (8)
C	800 (31.5)	M	330 (13)
D	615 (24.25)	N	950 (37.5)
E	140 (5.5)	P	895 (35.25)
F	1100 (43.25)	R	625 (24.5)
G	1525 (60)	S	1000 (39.25)
H	680 (26.75)	T	3050 (120)
J	275 (10.75)		

## Regulatory Compliance/Certifications

**Agency** **Classification**  
ISO 9001:2008 Designed, manufactured and/or distributed under this quality management system

## Included Products

HP10-144 (Product Component—not orderable) — 3.0 m | 10 ft High Performance Parabolic Shielded Antenna, single-polarized, 14.400–15.350 GHz

# Product Specifications



HP10-144U1A

## \* Footnotes

Axial Force (FA)	Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.
Cross Polarization Discrimination (XPD)	The difference between the peak of the co-polarized main beam and the maximum cross-polarized signal over an angle twice the 3 dB beamwidth of the co-polarized main beam.
Front-to-Back Ratio	Denotes highest radiation relative to the main beam, at $180^\circ \pm 40^\circ$ , across the band. Production antennas do not exceed rated values by more than 2 dB unless stated otherwise.
Gain, Mid Band	For a given frequency band, gain is primarily a function of antenna size. The gain of Andrew antennas is determined by either gain by comparison or by computer integration of the measured antenna patterns.
Operating Frequency Band	Bands correspond with CCIR recommendations or common allocations used throughout the world. Other ranges can be accommodated on special order.
Packing	Andrew standard packing is suitable for export. Antennas are shipped as standard in totally recyclable cardboard or wire-bound crates (dependent on product). For your convenience, Andrew offers heavy duty export packing options.
Radiation Pattern Envelope Reference (RPE)	Radiation patterns define an antenna's ability to discriminate against unwanted signals. Under still dry conditions, production antennas will not have any peak exceeding the current RPE by more than 3dB, maintaining an angular accuracy of $+/ - 1^\circ$ throughout
Return Loss	The figure that indicates the proportion of radio waves incident upon the antenna that are rejected as a ratio of those that are accepted.
Side Force (FS)	Maximum side force exerted on the mounting pipe as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.
Twisting Moment (MT)	Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.
VSWR	Maximum; is the guaranteed Peak Voltage-Standing-Wave-Ratio within the operating band.
Wind Velocity Operational	The wind speed where the antenna deflection is equal to or less than 0.1 degrees. In the case of ValuLine antennas, it is defined as a maximum deflection of $0.3 \times$ the 3 dB beam width of the antenna.
Wind Velocity Survival Rating	The maximum wind speed the antenna, including mounts and radomes, where applicable, will withstand without permanent deformation. Realignment may be required. This wind speed is applicable to antenna with the specified amount of radial ice.