

LOW FREQUENCY CERAMIC SURFACE MOUNT MICROPROCESSOR CRYSTAL

ABC2

RoHS compliant with exemption of Pb in glass
(exempt per RoHS 2002/95/EC Annex (5))

RoHS
Compliant



11.8 x 5.5 x 1.9mm

Moisture Sensitivity Level (MSL) – This product is Hermetically Sealed and not Moisture Sensitive - MSL = N/A: Not Applicable

FEATURES:

- Low frequency in small size SMD
- 1.9mm height ideal for high density circuit boards
- Ceramic package offers excellent environmental & heat resistance
- Extended temperature -40°C to +85°C for industrial applications
- Suitable for RoHS compliant reflow

APPLICATIONS:

- Wide range in communication & measuring equipment
- Commercial & Industrial applications

STANDARD SPECIFICATIONS:

Parameters	Minimum	Typical	Maximum	Units	Notes
Frequency Range	3.500	-----	30.000	MHz	Fundamental, AT
	30.000	-----	70.000		3 rd Overtone, AT
Operation Mode	Fundamental or 3 rd Overtone				
Operating Temperature	-40	-----	+85	°C	Guaranteed oscillation only. For tighter freq. stability over temp (option D), see stability options below
Storage Temperature	-55	-----	+125	°C	
Frequency Tolerance @+25°C	-50	-----	+50	ppm	See options
Frequency Stability over the Operating Temperature -10 °C to +60 °C (ref. to +25°C)	-50	-----	+50	ppm	Standard for below 6.0MHz (-10 °C to +60 °C) See options for other temperature
	-30	-----	+30		Standard for 6.0MHz and above; (-10 °C to +60 °C) See options for other temperature
Equivalent series resistance (R1)	See table 1 below			Ω	
Shunt capacitance (C0)	-----	-----	7	pF	
Load capacitance (CL)	-----	18	-----	pF	See options
Drive Level	-----	-----	100	μW	
Aging@25°C±3°C	-----	-----	±5	ppm	First year
Insulation Resistance	500	-----	-----	M Ω	@ 100Vdc ± 15V

Table 1

Frequency Ranges	Operation mode	ESR (max)
3.200MHz ~ 3.499MHz	Fundamental	200 Ω
3.500MHz ~ 3.999MHz	Fundamental	140 Ω
4.000MHz ~ 4.399MHz	Fundamental	120 Ω
4.400MHz ~ 4.899MHz	Fundamental	100 Ω
4.900MHz ~ 5.999MHz	Fundamental	80 Ω
6.000MHz ~ 6.999MHz	Fundamental	60 Ω
7.000MHz ~ 7.999MHz	Fundamental	50 Ω
8.000MHz ~ 10.999MHz	Fundamental	45 Ω
11.000MHz ~ 11.999MHz	Fundamental	40 Ω
12.000MHz ~ 14.999MHz	Fundamental	35 Ω
15.000MHz ~ 36.000MHz	Fundamental	30 Ω
27.000MHz ~ 70.000MHz	3rd OT	100Ω



LOW FREQUENCY CERAMIC SURFACE MOUNT MICROPROCESSOR CRYSTAL

ABC2


RoHS compliant with exemption of Pb in glass
(exempt per RoHS 2002/95/EC Annex (5))

RoHS
Compliant



11.8 x 5.5 x 1.9mm

OPTIONS AND PART IDENTIFICATION: (Left blank if standard)



* Option B and -10 ~60°C only

** Option Y, Z and Q only for F≥6.0MHz; Option Z and Q only for F<6.0MHz



LOW FREQUENCY CERAMIC SURFACE MOUNT MICROPROCESSOR CRYSTAL

ABC2


RoHS compliant with exemption of Pb in glass
(exempt per RoHS 2002/95/EC Annex (5))

RoHS
Compliant




11.8 x 5.5 x 1.9mm

OUTLINE DRAWING:




TAPE & REEL:

T: 1,000 pcs/reel



REFLOW PROFILE:



Need a test socket for the ABC2 Series? To view compatible **PRECISION TEST & BURN-IN SOCKETS** for these parts, [click here](#). P/N AXS-1155-04-01

ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS
ISO 9001:2008
CERTIFIED



Visit www.abracon.com for Terms & Conditions of Sale **Revised: 02.24.12**
30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000 | fax 949-546-8001 | www.abracon.com