





mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	 www.fciconnect.com
ltr	ecn no	dr	date	linear	angles		
A	T08-1164	WL	08/11/08	.X ± 0.25		projection	title 1.5mm WIRE TO BOARD HEADER
B	T08-1185	WL	11/13/08	.XX ± 0.15			SMT R/A TYPE
C	T08-1196	WL	12/10/08	.XXX ± 0.10			
D	T09-1005	WL	01/20/09	dr	0° ± 2°	MM	product family WTB
				engr	LEIF SHEN 06/18/08	scale	code TWN
				chr	LEIF SHEN 06/18/08		size dwg no
				appd	JOSEPH HSIA 06/18/08	A4	10089718
sheet index	revision sheet	D	1				sheet 1 of 1



RECOMMEND PCB LAYOUT



SEC. Y-Y



NOTES:
1. MATERIAL:
1.1 HOUSING: THERMOPLASTIC, HIGH TEMP.,UL94V-0;
1.2 CONTACT: COPPER ALLOY

2. FINISH:
UNDER PLATING: 50 μ MIN. NICKEL OVERALL
CONTACT AREA AND SOLDER TAIL: MATT TIN 100 μ MIN. OVERALL
3. REFLOW SOLDER CAPABLE TO 260°C PEAK TEMP.
FOR 10 SECONDS MAX.

4. SPEC. PLS. REFER TO GS-12-574.
5. PACKAGE PLS. REFER TO GS-14-1316.

6. PART NUMBER DESCRIPTION:
10089718-XXX 0 0 0 LF
NO. OF CONTACTS
PACKING 0: TAPE & REEL
COLOR 0: NATURAL
PLATING 0: MATTE TIN

CKT	Dim.A	Dim.B
007	9.0	11.8