

## Features

## Unregulated Converters

- UL/CSA and EN Safety certified
- EN-61010 for Test, Measurement and Lab Use
- EN-60601 for Medical Applications
- Reinforced Isolation 6.4kVDC or 8kVDC
- Optional Continuous Short Circuit Protected
- Unique Reinforced Isolation Transformer System
- /X2 Option for >9mm Input/Output Clearance

### Description

The RxxPxxS\_D Series of DC/DC Converters are certified to UL/CSA-60950. This makes them ideal for safety applications where approved or reinforced isolation is required. The reinforced versions are also EN61010-1 certified for Lab Equipment Safety.

### Selection Guide

| Part Number<br>SIP 7 | Reinforced Isolation<br>(kVDC) | Input Voltage<br>(VDC) | Output Voltage<br>(VDC) | Output Current<br>(mA) | Efficiency Std<br>(%) | Max Capacitive Load <sup>(1)</sup> |
|----------------------|--------------------------------|------------------------|-------------------------|------------------------|-----------------------|------------------------------------|
| RxxP3.3S*            | /R6.4 & /R8                    | 5, 9, 12, 15, 24       | 3.3                     | 303                    | 70~80                 | 2200µF                             |
| RxxP05S*             | /R6.4 & /R8                    | 5, 9, 12, 15, 24       | 5                       | 200                    | 75-80                 | 1000µF                             |
| RxxP09S*             | /R6.4 & /R8                    | 5, 9, 12, 15, 24       | 9                       | 111                    | 75-82                 | 1000µF                             |
| RxxP12S*             | /R6.4 & /R8                    | 5, 9, 12, 15, 24       | 12                      | 84                     | 75-82                 | 470µF                              |
| RxxP15S*             | /R6.4 & /R8                    | 5, 9, 12, 15, 24       | 15                      | 66                     | 75-83                 | 470µF                              |
| RxxP3.3D*            | /R6.4 & /R8                    | 5, 9, 12, 15, 24       | ±3.3                    | ±151                   | 72-79                 | ±1000µF                            |
| RxxP05D*             | /R6.4 & /R8                    | 5, 9, 12, 15, 24       | ±5                      | ±100                   | 75-82                 | ±470µF                             |
| RxxP09D*             | /R6.4 & /R8                    | 5, 9, 12, 15, 24       | ±9                      | ±55                    | 75-82                 | ±470µF                             |
| RxxP12D*             | /R6.4 & /R8                    | 5, 9, 12, 15, 24       | ±12                     | ±41                    | 75-82                 | ±220µF                             |
| RxxP15D*             | /R6.4 & /R8                    | 5, 9, 12, 15, 24       | ±15                     | ±33                    | 75-83                 | ±220µF                             |

xx = Input Voltage. Other input and output voltage combinations available on request.

\* add Suffix "P" for Continuous Short Circuit Protection, e.g. R05P05S/P, R05P05D/P

\* add Suffix "/X2" for single output with alternative pinout, e.g. R05P05S/X2, R05P05S/P/X2

\* add Suffix "/R6.4" or "/R8" for Reinforced Isolation, e.g. R05P05D/R6.4, R05P05S/P/X2/R8

### Specifications (measured at $T_A = 25^\circ\text{C}$ , nominal input voltage, full load and after warm-up)

|                                                   |                                                 |                |
|---------------------------------------------------|-------------------------------------------------|----------------|
| Input Voltage Range                               | ±10%                                            |                |
| Output Voltage Accuracy                           | ±5%                                             |                |
| Line Voltage Regulation                           | 1.2%/1% of $V_{in}$ typ.                        |                |
| Load Voltage Regulation                           | 3.3, 5V output types                            | 15% max.       |
| (10% to 100% full load)                           | other output types                              | 10% max.       |
| Output Ripple and Noise (20MHz BW)                | 200mVp-p max.                                   |                |
| Operating Frequency                               | 20kHz min. / 50kHz typ. / 85kHz max.            |                |
| Efficiency at Full Load                           | 65% min. / 75% typ.                             |                |
| Minimum Load = 0%                                 | Specifications valid for 10% minimum load only. |                |
| Reinforced Isolation /R6.4                        | (tested for 1 second)                           | 6400VDC        |
|                                                   | (rated for 1 minute**)                          | 3200VAC / 60Hz |
| Reinforced Isolation /R8                          | (tested for 1 second)                           | 8000VDC        |
|                                                   | (rated for 1 minute**)                          | 4000VAC / 60Hz |
| Isolation Capacitance                             | 4pF min. / 10pF max.                            |                |
| Isolation Resistance                              | 15 $\Omega$ min.                                |                |
| Short Circuit Protection                          | 1 Second                                        |                |
| P-Suffix                                          | Continuous                                      |                |
| Operating Temperature Range (free air convection) | -40°C to +85°C (see Graph)                      |                |
| Case Temperature                                  | 105°C max.                                      |                |
| Storage Temperature Range                         | -55°C to +125°C                                 |                |
| Relative Humidity                                 | 95% RH                                          |                |
| Package Weight                                    | 4.3g                                            |                |
| Packing Quantity                                  | 25 pcs per Tube                                 |                |

continued on next page

## ECONOLINE

### DC/DC-Converter

with 3 year Warranty

# RECOM

## 1 Watt


## SIP 7 Single & Dual Output



**EN-60950-1 Certified**  
**EN-60601-1 Certified**  
**UL/CSA 60950-1 Certified**  
**UL-60601-1 Certified**  
**EN-61010-1 Certified**  
**IEC-60601-1 CB Report**

# RxxPxx/R

## Derating-Graph (Ambient Temperature)




\*\*Any data referred to in this datasheet are of indicative nature and based on our practical experience only. For further details, please refer to our Application Notes.

Refer to Application Notes

**Specifications** (measured at  $T_A = 25^\circ\text{C}$ , nominal input voltage, full load and after warm-up))



|                                                |                                                                                                                                       |                                    |                                            |
|------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|------------------------------------|--------------------------------------------|
| Potting Material                               |                                                                                                                                       | Silicone Rubber Compound (UL94V-0) |                                            |
| MTBF (+25°C)                                   | } Detailed Information see<br>Application Notes chapter "MTBF"                                                                        | using MIL-HDBK 217F                | 2974 x 10 <sup>3</sup> hours               |
| (+85°C)                                        |                                                                                                                                       | using MIL-HDBK 217F                | 728 x 10 <sup>3</sup> hours                |
| Reinforced Isolation                           |                                                                                                                                       |                                    |                                            |
| Transformer Clearance                          | Reinforced Types                                                                                                                      | 5.5 mm min.                        |                                            |
| PCB Creepage & Clearance                       | Reinforced Types                                                                                                                      | 4.6 mm min.                        |                                            |
| Certifications                                 |                                                                                                                                       |                                    |                                            |
| Measurement, Control and Laboratory Use Safety |                                                                                                                                       | Report: T1301251-313               | EN61010-1 : 2010                           |
| CSA General Safety                             |                                                                                                                                       | Report: 2207629                    | UL 60950-1 1st Ed.<br>C22.2 No. 60950-1-03 |
| UL/cUL Medical Safety                          |                                                                                                                                       | Report: E314885-A5                 | UL60601-1 1st Edition                      |
| CSA Medical Safety                             |                                                                                                                                       | Report: 2207629                    | CAN/CSA-22.2 No 601.1-M90                  |
| EN General Safety                              |                                                                                                                                       | Report: SPCLVD1310079-1            | EN60950-1 : 2006                           |
| CB/EN Medical Safety                           |                                                                                                                                       | Report: CA-10169-A1-UL             | IEC/EN 60601-1 3rd Edition                 |
| ANSI/AAMI Medical Safety                       |                                                                                                                                       | Report: E314885-A5                 | ES60601-1 3rd Edition                      |
| Notes                                          |                                                                                                                                       |                                    |                                            |
| Note 1                                         | Maximum capacitive load is defined as the capacitive load that will allow start up in under 1 second without damage to the converter. |                                    |                                            |

**Tolerance Envelope**





**Typical Characteristics - Reinforced Version**

## RxxP05S/R6.4 RxxP05S/R8







## RxxP05D/R6.4 RxxP05D/R8








### Package Style and Pinning (mm)

#### 7 PIN SIP Package



#### Recommended Footprint Details



#### Pin Connections

| Pin # | Single | Dual  | /X2    |
|-------|--------|-------|--------|
| 1     | +Vin   | +Vin  | +Vin   |
| 2     | -Vin   | -Vin  | -Vin   |
| 5     | -Vout  | -Vout | No Pin |
| 6     | No Pin | Com   | -Vout  |
| 7     | +Vout  | +Vout | +Vout  |

XX.X ± 0.5 mm  
XX.XX ± 0.25 mm