


# EC-19.354M TR



## ELECTRICAL SPECIFICATIONS


|                               |                                                                                                              |
|-------------------------------|--------------------------------------------------------------------------------------------------------------|
| Nominal Frequency             | 19.354MHz                                                                                                    |
| Frequency Tolerance/Stability | $\pm 50\text{ppm}$ at $25^\circ\text{C}$ , $\pm 100\text{ppm}$ over $0^\circ\text{C}$ to $+70^\circ\text{C}$ |
| Aging at $25^\circ\text{C}$   | $\pm 5\text{ppm/year}$ Maximum                                                                               |
| Load Capacitance              | $18\text{pF}$ Parallel Resonant                                                                              |
| Shunt Capacitance (C0)        | $7\text{pF}$ Maximum                                                                                         |
| Equivalent Series Resistance  | 25 Ohms Maximum                                                                                              |
| Mode of Operation             | AT-Cut Fundamental                                                                                           |
| Drive Level                   | 2mWatts Maximum                                                                                              |
| Storage Temperature Range     | $-40^\circ\text{C}$ to $+85^\circ\text{C}$                                                                   |
| Insulation Resistance         | 500 Megaohms Minimum at 100Vdc                                                                               |

## ENVIRONMENTAL & MECHANICAL SPECIFICATIONS

|                              |                                       |
|------------------------------|---------------------------------------|
| Fine Leak Test               | MIL-STD-883, Method 1014, Condition A |
| Gross Leak Test              | MIL-STD-883, Method 1014, Condition C |
| Lead Integrity               | MIL-STD-883, Method 2004              |
| Mechanical Shock             | MIL-STD-202, Method 213, Condition C  |
| Resistance to Soldering Heat | MIL-STD-202, Method 210               |
| Resistance to Solvents       | MIL-STD-202, Method 215               |
| Solderability                | MIL-STD-883, Method 2003              |
| Temperature Cycling          | MIL-STD-883, Method 1010              |
| Vibration                    | MIL-STD-883, Method 2007, Condition A |

# EC-19.354M TR

MECHANICAL DIMENSIONS (all dimensions in millimeters)




| LINE | MARKING                                                               |
|------|-----------------------------------------------------------------------|
| 1    | <b>ECLIPTEK</b>                                                       |
| 2    | <b>E19.354M</b><br><i>E=Ecliptek Designator or Blank (No Marking)</i> |
| 3    | <b>XX</b><br><i>XX=Ecliptek Manufacturing Code</i>                    |


# EC-19.354M TR

## Tape & Reel Dimensions


Quantity Per Reel: 1,000 Pieces



\*Compliant to EIA 468B



## Recommended Solder Reflow Methods



### High Temperature Solder Bath (Wave Solder)

|                                                                |                    |
|----------------------------------------------------------------|--------------------|
| <b><math>T_S</math> MAX to <math>T_L</math> (Ramp-up Rate)</b> | 3°C/second Maximum |
|----------------------------------------------------------------|--------------------|

#### Preheat

|                                    |                  |
|------------------------------------|------------------|
| - Temperature Minimum ( $T_S$ MIN) | 150°C            |
| - Temperature Typical ( $T_S$ TYP) | 175°C            |
| - Temperature Maximum ( $T_S$ MAX) | 200°C            |
| - Time ( $t_s$ MIN)                | 60 - 180 Seconds |

|                                                            |                    |
|------------------------------------------------------------|--------------------|
| <b>Ramp-up Rate (<math>T_L</math> to <math>T_P</math>)</b> | 3°C/second Maximum |
|------------------------------------------------------------|--------------------|

#### Time Maintained Above:

|                         |                  |
|-------------------------|------------------|
| - Temperature ( $T_L$ ) | 217°C            |
| - Time ( $t_L$ )        | 60 - 150 Seconds |

|                                            |                                      |
|--------------------------------------------|--------------------------------------|
| <b>Peak Temperature (<math>T_P</math>)</b> | 260°C Maximum for 10 Seconds Maximum |
|--------------------------------------------|--------------------------------------|

|                                                          |               |
|----------------------------------------------------------|---------------|
| <b>Target Peak Temperature (<math>T_P</math> Target)</b> | 250°C +0/-5°C |
|----------------------------------------------------------|---------------|


|                                                          |                 |
|----------------------------------------------------------|-----------------|
| <b>Time within 5°C of actual peak (<math>t_p</math>)</b> | 20 - 40 seconds |
|----------------------------------------------------------|-----------------|

|                       |                    |
|-----------------------|--------------------|
| <b>Ramp-down Rate</b> | 6°C/second Maximum |
|-----------------------|--------------------|

|                                                       |                   |
|-------------------------------------------------------|-------------------|
| <b>Time 25°C to Peak Temperature (<math>t</math>)</b> | 8 minutes Maximum |
|-------------------------------------------------------|-------------------|

|                                   |         |
|-----------------------------------|---------|
| <b>Moisture Sensitivity Level</b> | Level 1 |
|-----------------------------------|---------|

## Recommended Solder Reflow Methods



### Low Temperature Solder Bath (Wave Solder)

|                                                       |                                                       |
|-------------------------------------------------------|-------------------------------------------------------|
| <b>Ts MAX to T<sub>L</sub> (Ramp-up Rate)</b>         | 5°C/second Maximum                                    |
| <b>Preheat</b>                                        |                                                       |
| - Temperature Minimum (T <sub>s</sub> MIN)            | N/A                                                   |
| - Temperature Typical (T <sub>s</sub> TYP)            | 150°C                                                 |
| - Temperature Maximum (T <sub>s</sub> MAX)            | N/A                                                   |
| - Time (t <sub>s</sub> MIN)                           | 30 - 60 Seconds                                       |
| <b>Ramp-up Rate (T<sub>L</sub> to T<sub>P</sub>)</b>  | 5°C/second Maximum                                    |
| <b>Time Maintained Above:</b>                         |                                                       |
| - Temperature (T <sub>L</sub> )                       | 150°C                                                 |
| - Time (t <sub>L</sub> )                              | 200 Seconds Maximum                                   |
| <b>Peak Temperature (T<sub>P</sub>)</b>               | 245°C Maximum                                         |
| <b>Target Peak Temperature (T<sub>P</sub> Target)</b> | 245°C Maximum 1 Time / 235°C Maximum 2 Times          |
| <b>Time within 5°C of actual peak (t<sub>p</sub>)</b> | 5 seconds Maximum 1 Time / 15 seconds Maximum 2 Times |
| <b>Ramp-down Rate</b>                                 | 5°C/second Maximum                                    |
| <b>Time 25°C to Peak Temperature (t)</b>              | N/A                                                   |
| <b>Moisture Sensitivity Level</b>                     | Level 1                                               |

### Low Temperature Manual Soldering

185°C Maximum for 10 seconds Maximum, 2 times Maximum.

### High Temperature Manual Soldering

260°C Maximum for 5 seconds Maximum, 2 times Maximum.