




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		G	REVISED PER ECR-12-013219	08JAN13	KH	KR



- MATING TAB THK IS 0.81 ± 0.025 [.032 $\pm$.001]
- WIRE SIZE IS [#22-#18] AWG.
- INSULATION RANGE IS 2.03-3.05 [.080-.120] DIA.
- $\triangle$ PREPRODUCTION - FASR REQ



0.002032 [.000080] MIN TIN			521436-2		
-			4 521436-1		
TERMINAL FINISH			PART NO.		
DWN	JR RUTH	22OCT01	 TE Connectivity		
CHK	J HUMMEL	22OCT01			
APVD	J HUMMEL	22OCT01	NAME ASSEMBLY, RECEPTACLE, ULTRA-POD, 2.79 [.110] SERIES		
PRODUCT SPEC 108-1285					
APPLICATION SPEC 114-2124		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
WEIGHT -		A2	00779	C=521436	-
CUSTOMER DRAWING				SCALE	SHEET
				6:1	1 of 1
				REV	G

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm [INCHES]	
	0 PLC $\pm$ -
	1 PLC $\pm$ -
	2 PLC $\pm$ 0.25 [.010]
	3 PLC $\pm$ -
	4 PLC $\pm$ -
	ANGLES $\pm$ -
MATERIAL	FINISH
TERMINAL - BRASS	TERMINAL - SEE TABLE
HSG - 6/6 NYLON, V2	HOUSING - NATURAL