

Customer Information Sheet

DRAWING No.: M22-19X00XX

SHEET 1 OF 2


IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



SPECIFICATIONS:

MATERIALS:

MOULDING = GLASS FILLED POLYESTER UL94V-0

CONTACT = BERYLLIUM COPPER

FINISH:

CONTACT:

05 = 0.13μ GOLD ON CONTACT FACE OVER NICKEL

46 = 3μ 100% TIN OVER NICKEL

MOULDING COLOUR = SEE ORDER CODE

ELECTRICAL:

CURRENT RATING AT 25°C = 2A MAX

WORKING VOLTAGE = 250V AC/DC

VOLTAGE PROOF = 500V AC/DC @ 50Hz

CONTACT RESISTANCE (MAXIMUM):

TIN/LEAD = 20MILLOHMS INITIAL

25 MILLIOHMS AFTER CONDITIONING

GOLD = 15 MILLIOHMS INITIAL

20 MILLIOHMS AFTER CONDITIONING

INSULATION RESISTANCE (MINIMUM):

INITIAL = 1000 MEGOHMS

AFTER CONDITIONING = 1000 MEGAOHMS

ENVIRONMENTAL:

TEMPERATURE RANGE = -40°C TO +85°C

MECHANICAL:

DURABILITY:

TIN/LEAD = 50 OPERATIONS

GOLD = 300 OPERATIONS

INSERTION FORCE = 10N MAX

WITHDRAWAL FORCE = 1N MIN

FOR COMPLETE SPECIFICATION, SEE COMPONENT SPECIFICATION C013XX (LATEST ISSUE)

ORDER CODE:

M22-19X00XX

MOULDING COLOUR

0 = BLACK

1 = BLUE

2 = RED

3 = LIGHT GREY

CONTACT FINISH

05 = GOLD

46 = 100% TIN

RA	5	08.10.08	10154
NAME	ISS.	DATE	C/NOTE
APPROVED: R. ADDE			
CHECKED: M.G. PLESTED			
DRAWN: W. J. BOURNE			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN USA TEL: 603 893 5376 FAX: 603 893 5396 mis@harwin.com	HARWIN Europe (UK) TEL: 023 9231 4545 FAX: 023 9231 4590 mis@harwin.co.uk	HARWIN Asia TEL: +65 6 779 4909 FAX: +65 6 779 3868 mis@harwin.com.sg
--	--	--

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:

FINISH:

S/AREA:

mm²

TITLE:

2mm PITCH JUMPER SOCKET
ASSEMBLY (OPEN TOP)

DRAWING NUMBER:

M22-19X00XX

SHT
1 OF 2