6-Pin DIP High BV_{CEO} Phototransistor Optocouplers

CNY17 Series, MOC8106M



PDIP6
CASE 646BY



PDIP6
CASE 646BX



PDIP6
CASE 646BZ

Description

The CNY17XM, CNY17FXM, and MOC8106M devices consist of a gallium arsenide infrared emitting diode coupled with an NPN phototransistor in a dual in−line package.

Features

- High BV_{CEO}: 70 V Minimum (CNY17XM, CNY17FXM, MOC8106M)
- Closely Matched Current Transfer Ratio (CTR) Minimizes Unit−to−Unit Variation
- Current Transfer Ratio In Select Groups
- Very Low Coupled Capacitance Along With No Chip−to−Pin 6 Base Connection for Minimum Noise Susceptibility (CNY17FXM, MOC8106M)
- Safety and Regulatory Approvals:
  - UL1577, 4,170 VAC_{RMS} for 1 Minute
  - DIN−EN/IEC60747−5−5, 850 V Peak Working Insulation Voltage

Applications

- Power Supply Regulators
- Digital Logic Inputs
- Microprocessor Inputs
- Appliance Sensor Systems
- Industrial Controls

MARKING DIAGRAM



1. ON = **onsemi** Logo
2. CNY17 = Device Number
3. V = DIN EN/IEC60747−5−5 Option (only appears on component ordered with this option)
4. X = One−Digit Year Code
5. YY = Digit Work Week
6. Q = Assembly Package Code

ORDERING INFORMATION

See detailed ordering and shipping information on page 8 of this data sheet.

© Semiconductor Components Industries, LLC, 2006

SCHEMATICS



Figure 1. Schematics

SAFETY AND INSULATION RATINGS

As per DIN EN/IEC 60747−5−5, this optocoupler is suitable for “safe electrical insulation” only within the safety limit data. Compliance with the safety ratings shall be ensured by means of protective circuits.

Parameter		Characteristics
Installation Classifications per DIN VDE 0110/1.89 Table 1, For Rated Mains Voltage	< 150 V_{RMS}	I–IV
	< 300 V_{RMS}	I–IV
Climatic Classification		55/100/21
Pollution Degree (DIN VDE 0110/1.89)		2
Comparative Tracking Index		175

Symbol	Parameter	Value	Unit
V_{PR}	Input−to−Output Test Voltage, Method A, V_{IORM} x 1.6 = V_{PR}, Type and Sample Test with t_m = 10 s, Partial Discharge < 5 pC	1360	Vpeak
	Input−to−Output Test Voltage, Method B, V_{IORM} x 1.875 = V_{PR}, 100% Production Test with t_m = 1 s, Partial Discharge < 5 pC	1594	Vpeak
V_{IORM}	Maximum Working Insulation Voltage	850	Vpeak
V_{IOTM}	Highest Allowable Over−Voltage	6000	Vpeak
	External Creepage	≥ 7	mm
	External Clearance	≥ 7	mm
	External Clearance (for Option TV, 0.4” Lead Spacing)	≥ 10	mm
DTI	Distance Through Insulation (Insulation Thickness)	≥ 0.5	mm
T_S	Case Temperature (Note 1)	175	°C
$I_{S, INPUT}$	Input Current (Note 1)	350	mA
$P_{S, OUTPUT}$	Output Power (Note 1)	800	mW
R_{IO}	Insulation Resistance at T_S, V_{IO} = 500 V (Note 1)	> 10^9	Ω

1. Safety limit values – maximum values allowed in the event of a failure.

ABSOLUTE MAXIMUM RATINGS

Symbol	Parameter	Value	Unit
TOTAL DEVICE			
T_{STG}	Storage Temperature	−40 to +125	°C
T_A	Ambient Operating Temperature	−40 to +100	°C
T_J	Junction Temperature	−40 to +125	°C
T_{SOL}	Lead Solder Temperature	260 for 10 seconds	°C
P_D	Total Device Power Dissipation @ 25°C (LED plus detector)	270	mW
	Derate Linearly From 25°C	2.94	mW/°C
EMITTER			
I_F	Continuous Forward Current	60	mA
V_R	Reverse Voltage	6	V
I_F (pk)	Forward Current − Peak (1 μs pulse, 300 pps)	1.5	A
P_D	LED Power Dissipation 25°C Ambient	120	mW
	Derate Linearly From 25°C	1.41	mW/°C
DETECTOR			
I_C	Continuous Collector Current	50	mA
V_{CEO}	Collector−Emitter Voltage	70	V
V_{ECO}	Emitter Collector Voltage	7	V
P_D	Detector Power Dissipation @ 25°C	150	mW
	Derate Linearly from 25°C	1.76	mW/°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

ELECTRICAL CHARACTERISTICS

(T_A = 25°C unless otherwise specified)

INDIVIDUAL COMPONENT CHARACTERISTICS

Symbol	Parameter	Test Conditions	Device	Min.	Typ.	Max.	Unit
EMITTER							
V_F	Input Forward Voltage	I_F = 10 mA	All Devices	1.0	1.15	1.50	V
		I_F = 60 mA	CNY17XM, CNY17FXM	1.0	1.35	1.65	V
C_J	Capacitance	V_F = 0 V, f = 1.0 MHz	All Devices	–	18	–	pF
I_R	Reverse Leakage Current	V_R = 6 V	All Devices	–	0.001	10	μA
DETECTOR							
BV_{CEO}	Breakdown Voltage Collector–to–Emitter	I_C = 1 mA, I_F = 0	All Devices	70	100	–	V
BV_{CBO}	Collector–to–Base	I_C = 10 μA, I_F = 0	CNY17XM	70	120	–	V
BV_{ECO}	Emitter–to–Collector	I_E = 100 μA, I_F = 0	All Devices	7	10	–	V
I_{CEO}	Leakage Current Collector–to–Emitter	V_{CE} = 10 V, I_F = 0	All Devices	–	1	50	nA
I_{CBO}	Collector–to–Base	V_{CB} = 10 V, I_F = 0	CNY17XM	–	–	20	nA
C_{CE}	Capacitance Collector–to–Emitter	V_{CE} = 0, f = 1 MHz	All Devices	–	8	–	pF
C_{CB}	Collector–to–Base	V_{CB} = 0, f = 1 MHz	CNY17XM	–	20	–	pF
C_{EB}	Emitter–to–Base	V_{EB} = 0, f = 1 MHz	CNY17XM	–	10	–	pF

TRANSFER CHARACTERISTICS

Symbol	Parameter	Test Conditions	Device	Min.	Typ.	Max.	Unit
COUPLED							
CTR	Current Transfer Ratio	I_F = 10 mA, V_{CE} = 10 V	MOC8106M	50	–	150	%
		I_F = 10 mA, V_{CE} = 5 V	CNY171M, CNY17F1M	40	–	80	%
		I_F = 10 mA, V_{CE} = 5 V	CNY172M, CNY17F2M	63	–	125	%
		I_F = 10 mA, V_{CE} = 5 V	CNY173M, CNY17F3M	100	–	200	%
		I_F = 10 mA, V_{CE} = 5 V	CNY174M, CNY17F4M	160	–	320	%
$V_{CE(SAT)}$	Collector–Emitter Saturation Voltage	I_C = 0.5 mA, I_F = 5 mA	MOC8106M	–	–	0.4	V
		I_C = 2.5 mA, I_F = 10 mA	CNY17XM/CNY17FXM	–	–		

AC CHARACTERISTICS

Symbol	Parameter	Test Conditions	Device	Min.	Typ.	Max.	Unit
NON−SATURATED SWITCHING TIME							
t_{on}	Turn−On Time	I_C = 2.0 mA, V_{CC} = 10 V, R_L = 100 Ω	All Devices	–	2.0	10.0	μs
t_{off}	Turn−Off Time	I_C = 2.0 mA, V_{CC} = 10 V, R_L = 100 Ω	All Devices	–	3.0	10.0	μs
t_d	Delay Time	I_F = 10 mA, V_{CC} = 5 V, R_L = 75 Ω	CNY17XM/CNY17FXM	–	–	5.6	μs
t_r	Rise Time	I_F = 10 mA, V_{CC} = 5 V, R_L = 75 Ω	CNY17XM/CNY17FXM	–	–	4.0	μs
t_s	Storage Time	I_F = 10 mA, V_{CC} = 5 V, R_L = 75 Ω	CNY17XM/CNY17FXM	–	–	4.1	μs
t_f	Fall Time	I_F = 10 mA, V_{CC} = 5 V, R_L = 75 Ω	CNY17XM/CNY17FXM	–	–	3.5	μs
SATURATED SWITCHING TIME							
t_d	Delay Time	I_F = 20 mA, V_{CC} = 5 V, R_L = 1 kΩ	CNY171M/F1M	–	–	5.5	μs
		I_F = 10 mA, V_{CC} = 5 V, R_L = 1 kΩ	CNY172M/3M/4M CNY17F2M/F3M/F4M	–	–	8.0	μs
t_r	Rise Time	I_F = 20 mA, V_{CC} = 5 V, R_L = 1 kΩ	CNY171M/F1M	–	–	4.0	μs
		I_F = 10 mA, V_{CC} = 5 V, R_L = 1 kΩ	CNY172M/3M/4M CNY17F2M/F3M/F4M	–	–	6.0	μs
t_s	Storage Time	I_F = 20 mA, V_{CC} = 5 V, R_L = 1 kΩ	CNY171M/F1M	–	–	34.0	μs
		I_F = 10 mA, V_{CC} = 5 V, R_L = 1 kΩ	CNY172M/3M/4M CNY17F2M/F3M/F4M	–	–	39.0	μs
t_f	Fall Time	I_F = 20 mA, V_{CC} = 5 V, R_L = 1 kΩ	CNY171M/F1M	–	–	20.0	μs
		I_F = 10 mA, V_{CC} = 5 V, R_L = 1 kΩ	CNY172M/3M/4M CNY17F2M/F3M/F4M	–	–	24.0	μs

ISOLATION CHARACTERISTICS

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
V_{ISO}	Input−Output Isolation Voltage	t = 1 Minute	4170	–	–	VAC_{RMS}
C_{ISO}	Isolation Capacitance	V_{I-O} = 0 V, f = 1 MHz	–	0.2	–	pF
R_{ISO}	Isolation Resistance	V_{I-O} = ±500 VDC, T_A = 25°C	10^{11}	–	–	Ω

TYPICAL PERFORMANCE CHARACTERISTICS



Figure 2. Normalized CTR vs. Forward Current



Figure 3. Normalized CTR vs. Ambient Temperature



Figure 4. CTR vs. RBE (Unsaturated)



Figure 5. CTR vs. RBE (Saturated)



Figure 6. Switching Speed vs. Load Resistor



Figure 7. Normalized t_{on} vs. R_{BE}

TYPICAL PERFORMANCE CHARACTERISTICS (Continued)



Figure 8. Normalized t_{off} vs. R_{BE}



Figure 9. LED Forward Voltage vs. Forward Current



Figure 10. Collector−Emitter Saturation Voltage vs. Collector Current

SWITCHING TEST CIRCUIT AND WAVEFORMS



Figure 11. Switching Test Circuit and Waveforms

REFLOW PROFILE



Figure 12. Reflow Profile

Profile Feature	Pb − Free Assembly Profile
Temperature Min. (Tsmin)	150°C
Temperature Max. (Tsmax)	200°C
Time (t_S) from (Tsmin to Tsmax)	60–120 seconds
Ramp − up Rate (t_L to t_P)	3°C/second max.
Liquidous Temperature (T_L)	217°C
Time (t_L) Maintained Above (T_L)	60–150 seconds
Peak Body Package Temperature	260°C +0°C / −5°C
Time (t_P) within 5°C of 260°C	30 seconds
Ramp − down Rate (T_P to T_L)	6°C / second max.
Time 25°C to Peak Temperature	8 minutes max.

Table 1. ORDERING INFORMATION

Part Number	Package	Packing Method†
CNY171M	DIP 6−Pin	Tube (50 Units)
CNY171SM	SMT 6−Pin (Lead Bend)	Tube (50 Units)
CNY171SR2M	SMT 6−Pin (Lead Bend)	Tape and Reel (1000 Units)
CNY171TM	DIP 6−Pin, 0.4” Lead Spacing	Tube (50 Units)
CNY171VM	DIP 6−Pin, DIN EN/IEC60747−5−5 Option	Tube (50 Units)
CNY171SVM	SMT 6−Pin (Lead Bend), DIN EN/IEC60747−5−5 Option	Tube (50 Units)
CNY171SR2VM	SMT 6−Pin (Lead Bend), DIN EN/IEC60747−5−5 Option	Tape and Reel (1000 Units)
CNY171TVM	DIP 6−Pin, 0.4” Lead Spacing, DIN EN/IEC60747−5−5 Option	Tube (50 Units)

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

2. The product orderable part number system listed in this table also applies to the CNY17FXM product family and the MOC8106M device.

PDIP6 8.51x6.35, 2.54P
CASE 646BX
ISSUE O

DATE 31 JUL 2016





NOTES:

A) NO STANDARD APPLIES TO THIS PACKAGE.

B) ALL DIMENSIONS ARE IN MILLIMETERS.

C) DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSION

DOCUMENT NUMBER:	**98AON13449G**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	**PDIP6 8.51X6.35, 2.54P**	**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

PDIP6 8.51x6.35, 2.54P
CASE 646BY
ISSUE A

DATE 15 JUL 2019



NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009.
2. CONTROLLING DIMENSION: MILLIMETERS
3. DIMENSIONS A, A1, AND L ARE MEASURED WITH THE PACKAGE SEATED.
4. DIMENSIONS D, D1, AND E1 DO NOT INCLUDE MOLD FLASH OR PROTRUSIONS. MOLD FLASH OR PROTRUSIONS ARE NOT TO EXCEED 2.54mm.
5. PACKAGE CONTOUR IS OPTIONAL (ROUNDED OR SQUARE CORNERS).
6. CENTER LINE OF CORNER LEADS ARE LOCATED BY LOCATING THE CENTER OF FEATURE b2 AND b3.

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	---	---	4.80
A1	0.38	---	---
A2	3.28	3.40	3.53
A3	2.49 REF		
A4	1.89 REF		
b	0.41	0.46	0.51
b1	0.76	0.92	1.14
b2	0.25	0.28	0.36
b3	1.02	1.40	1.78
b4	1.778 REF		
c	0.20	0.25	0.30
D	8.13	8.51	8.89
D1	0.86 REF		
E	6.10	6.35	6.60
E1	8.43	9.17	9.90
E2	8.13 REF		
e	2.54 BSC		
L	0.16	0.52	0.88







* For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

DOCUMENT NUMBER:	**98AON13450G**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	**PDIP6 8.51x6.35, 2.54P**	**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

© Semiconductor Components Industries, LLC, 2016

PDIP6 8.51x6.35, 2.54P
CASE 646BZ
ISSUE O

DATE 31 JUL 2016



NOTES:

A) NO STANDARD APPLIES TO THIS PACKAGE.

B) ALL DIMENSIONS ARE IN MILLIMETERS.

C) DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSION

DOCUMENT NUMBER:	**98AON13451G**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION:	**PDIP6 8.51X6.35, 2.54P**		**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales