



DUAL-IN-LINE SOCKETS


SERIES 146 • SOLDERLESS PRESS-FIT, COMPLIANT TAIL • OPEN FRAME



- Unique compliant tail pins conform to a $.040" \pm .003"$ finished plated through hole diameter without stressing inner layers
- Two tails lengths are offered for .060"-.100" and .090"-.130" thick panels
- Series 146 uses MM #4612 or MM #4613 pins with a BeCu #30 contact, rated at 3 amps. See page 162 for details
- Insulators are high temperature thermoplastic
- For Electrical, Mechanical and Environmental Data, see page 264 for details




APPLICATION OF COMPLIANT TAIL PINS



Mill-Max's patented* precision-machined pins feature compliant tails that are hollow and slotted to conform to a $.040" \pm .003"$ diameter PTH. As the pin is inserted, the slot compresses to fit the PTH, thus avoiding damage (see illustration at left). The pin's tail has fine serrations that form a perfect "gas tight" connection that doesn't require soldering. And since the pin doesn't damage the hole, compliant tail sockets and connectors can be easily replaced.

*Patent No. 4,799,904.

Total number of pins				Quantity per tube	ORDERING INFORMATION							
	A	B	C		L = .120 (for .060"-.100" thick panel)	L = .175 (for .090"-.130" thick panel)						
6	0.3	0.3	0.4	67	146-XX-306-41-012000	146-XX-306-41-013000	 					
8	0.4	0.3	0.4	50	146-XX-308-41-012000	146-XX-308-41-013000						
14	0.7	0.3	0.4	28	146-XX-314-41-012000	146-XX-314-41-013000						
16	0.8	0.3	0.4	25	146-XX-316-41-012000	146-XX-316-41-013000						
18	0.9	0.3	0.4	22	146-XX-318-41-012000	146-XX-318-41-013000						
20	1.0	0.3	0.4	20	146-XX-320-41-012000	146-XX-320-41-013000						
24	1.2	0.3	0.4	16	146-XX-324-41-012000	146-XX-324-41-013000						
22	1.1	0.4	0.5	18	146-XX-422-41-012000	146-XX-422-41-013000						
24	1.2	0.6	0.7	16	146-XX-624-41-012000	146-XX-624-41-013000						
28	1.4	0.6	0.7	14	146-XX-628-41-012000	146-XX-628-41-013000						
32	1.6	0.6	0.7	12	146-XX-632-41-012000	146-XX-632-41-013000						
40	2.0	0.6	0.7	10	146-XX-640-41-012000	146-XX-640-41-013000						
SPECIFY PLATING CODE XX =						91	93		41 	43 		
Sleeve (Pin) 						200 μ" Sn/Pb		200 μ" Sn/Pb		200 μ" Sn	200 μ" Sn	
Contact (Clip) 						10 μ" Au		30 μ" Au		10 μ" Au	30 μ" Au	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[146-93-640-41-013000](#) [146-93-640-41-012000](#) [146-93-632-41-013000](#) [146-93-632-41-012000](#) [146-93-628-41-013000](#) [146-93-628-41-012000](#) [146-93-624-41-013000](#) [146-93-624-41-012000](#) [146-93-422-41-013000](#) [146-93-422-41-012000](#) [146-93-324-41-013000](#) [146-93-324-41-012000](#) [146-93-320-41-013000](#) [146-93-320-41-012000](#) [146-93-318-41-013000](#) [146-93-318-41-012000](#) [146-93-316-41-013000](#) [146-93-316-41-012000](#) [146-93-314-41-013000](#) [146-93-314-41-012000](#) [146-93-308-41-013000](#) [146-93-308-41-012000](#) [146-93-306-41-013000](#) [146-93-306-41-012000](#) [146-44-308-41-012000](#) [146-43-640-41-013000](#) [146-43-640-41-012000](#) [146-43-632-41-013000](#) [146-43-632-41-012000](#) [146-43-628-41-013000](#) [146-43-628-41-012000](#) [146-43-624-41-013000](#) [146-43-624-41-012000](#) [146-43-422-41-013000](#) [146-43-422-41-012000](#) [146-43-324-41-013000](#) [146-43-324-41-012000](#) [146-43-320-41-013000](#) [146-43-320-41-012000](#) [146-43-318-41-013000](#) [146-43-318-41-012000](#) [146-43-316-41-013000](#) [146-43-316-41-012000](#) [146-43-314-41-013000](#) [146-43-314-41-012000](#) [146-43-308-41-013000](#) [146-43-308-41-012000](#) [146-43-306-41-013000](#) [146-43-306-41-012000](#) [146-91-306-41-013000](#) [146-91-314-41-013000](#) [146-91-316-41-013000](#) [146-91-318-41-013000](#) [146-91-320-41-013000](#) [146-91-324-41-012000](#) [146-91-324-41-013000](#) [146-91-422-41-012000](#) [146-91-422-41-013000](#) [146-91-624-41-012000](#) [146-91-624-41-013000](#) [146-91-316-41-012000](#) [146-91-320-41-012000](#) [146-91-306-41-012000](#) [146-91-314-41-012000](#) [146-91-318-41-012000](#) [146-91-308-41-012000](#)