



SPECIFICATIONS:

PANDUIT TOOL NO: TGJT
TOOL WEIGHT (WITH LANYARD): 8.30 oz (235.3 gr.)

CUTS AND ASSEMBLES ALL TG STYLE COPPER JACK MODULES

THIS TOOL'S FEATURES INCLUDE:

- * SINGLE HANDLE TRIGGER FOR FAST INSTALLATION.
- * DUAL SIDE ACTION - ONE SIDE FOR CUTTING EXCESS WIRES AT WIRE CAP.
- ONE SIDE FOR ASSEMBLING CAP INTO JACKMODULE.
- * CUT-OFF CAPABILITY WITH THE COMPLETE HAND CYCLE.
- * TRIMMED WIRES HELD FOR EASY REMOVAL.
- * TOOL SPRING RETURNED TO OPEN POSITION.

DIMENSIONS SHOWN IN PARENTHESES ARE (mm) METRIC (WITHOUT LANYARD): [DIMENSIONS ARE ROUNDED AND SUBJECT TO CHANGE WITHOUT NOTICE.]

A	= 5.75	(146.05)	OVERALL WIDTH
B	= 5.11	(129.87)	OVERALL HEIGHT
C	= 1.58	(40.23)	OVERALL DEPTH
D	= 4.10	(104.04)	TOTAL HANDLE SPAN
E	= 4.87	(123.60)	REAR HANDLE HEIGHT
F	= 1.36	(34.54)	HEAD HEIGHT
G	= 1.08	(27.31)	HEAD DEPTH
H	= 0.74	(18.87)	HANDLE WIDTH
I	= 0.21	(5.39)	OPENED BLADE GAP

TOOL DIV.
ENGINEERING DEPT.

DEC 29 2006

COPY

CAD FILENAME/LAYERS R25199BA_DS_CP25199B01_00A

PANDUIT CORP TINLEY PARK, ILLINOIS

CD * TGJT TOOL

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.0X) ± --- (.XXX) ± ---
(.XX) ± --- ANGLES ± ---

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION

REV	DATE	BY	CHK	RELEASED	4222	--	DATE	MAT'L:	SCALE
00	12/28/06	BJPU					8-23-06		1/2" = 1"
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	DRAWING NO.

CP25199B01 B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[TGJT](#)