


# 150 Watt HEW Single Series DC/DC Converters



## Description

The 4:1 Input Voltage 150 W single HEW Series of DC/DC converters provide precisely regulated dc outputs. The output voltage is fully isolated from the input, allowing the output to be positive or negative polarity and with various ground connections. The HEW Series meets the most rigorous performance standards in an industry standard case size for data communications and process control applications.

The 4:1 Input Voltage 150 Watt HEW Series includes remote sensing, output trim, and remote on/off. Threaded-through holes are provided to allow easy mounting or add a heat sink for extended temperature use.

## Features

- 4:1 input voltage range
- High power density
- Small size 2.4"x2.28"x0.55"
- Excellent thermal performance with metal baseplate
- Volt-seconds clamp and fast over voltage protection
- Pulse-by-pulse current limiting, short circuit frequency foldback, dead short shut down
- Over-temperature protection
- Auto-softstart
- Low noise
- Industry-standard pinout
- Constant frequency for normal operation
- Remote Sense
- Remote ON/OFF
- Super energy saving, 2 mA input idle current
- Output trim with very low temperature coefficient
- Water Washable, wide humidity applications
- Good shock & vibration damping

**Selection Chart**

| Model       | Input Range VDC |     | I in ADC | V out VDC | I out ADC |
|-------------|-----------------|-----|----------|-----------|-----------|
|             | Min             | Max | Typ      |           |           |
| 24S3.30HEW  | 9               | 36  | 5.00     | 3.3       | 30        |
| 24S5.30HEW  | 9               | 36  | 7.26     | 5         | 30        |
| 24S12.12HEW | 9               | 36  | 7.18     | 12        | 12.5      |
| 24S15.10HEW | 9               | 36  | 7.10     | 15        | 10        |
| 24S24.6HEW  | 9               | 36  | 7.10     | 24        | 6.26      |
| 48S3.30HEW  | 18              | 75  | 2.45     | 3.3       | 30        |
| 48S5.30HEW  | 18              | 75  | 3.60     | 5         | 30        |
| 48S12.12HEW | 18              | 75  | 3.57     | 12        | 12.5      |
| 48S15.10HEW | 18              | 75  | 3.50     | 15        | 10        |
| 48S24.6HEW  | 18              | 75  | 3.50     | 24        | 6.26      |

Default ON/OFF logic is positive.

Add -N to the model number to order negative ON/OFF logic.

# 150 Watt HEW Single Series DC/DC Converters

Unless otherwise stated, these specifications apply for ambient temperature  $T_A=23 \pm 2^\circ\text{C}$ , nominal input voltage, and rated full load. (1)

| Input Parameters                               |     |            |            |             |             |            |        |
|------------------------------------------------|-----|------------|------------|-------------|-------------|------------|--------|
| Model                                          |     | 24S3.30HEW | 24S5.30HEW | 24S12.12HEW | 24S15.10HEW | 24S24.6HEW | Units  |
| Voltage Range                                  | MIN | 9          |            |             |             |            | VDC    |
|                                                | TYP | 24         |            |             |             |            |        |
|                                                | MAX | 36         |            |             |             |            |        |
| Input Overvoltage<br>100 mSec                  | MAX | 50         |            |             |             |            | VDC    |
| Input Ripple Rejection<br>(120Hz)              | TYP | 60         |            |             |             |            | dB     |
| Undervoltage Lockout                           |     | Yes        |            |             |             |            |        |
| Input Reverse Voltage Protection               |     | Yes        |            |             |             |            |        |
| Input Current No Load<br>100% Load             | TYP | 12         | 12         | 12          | 12          | 12         | mA     |
|                                                | TYP | 5.00       | 7.26       | 7.18        | 7.10        | 7.10       | A      |
| Inrush Current                                 | MAX | 0.5        |            |             |             |            | A²S    |
| Reflected Ripple, 12µH<br>Source Impedance (3) | TYP | 30         |            |             |             |            | mA P-P |
| Efficiency                                     | TYP | 78         | 84         | 85          | 86          | 86         | %      |
| Switching Frequency                            | TYP | 325        |            |             |             |            | kHz    |
| Recommended Fuse                               |     | (2)        |            |             |             |            | AMPS   |

| Input Parameters                               |     |                |            |             |             |            |         |
|------------------------------------------------|-----|----------------|------------|-------------|-------------|------------|---------|
| Model                                          |     | 48S3.30HEW     | 48S5.30HEW | 48S12.12HEW | 48S15.10HEW | 48S24.6HEW | Units   |
| Voltage Range                                  | MIN | 18<br>48<br>75 |            |             |             |            | VDC     |
|                                                | TYP |                |            |             |             |            |         |
|                                                | MAX |                |            |             |             |            |         |
| Input Overvoltage<br>100 mSec                  | MAX | 80             |            |             |             |            | VDC     |
| Input Ripple Rejection<br>(120Hz)              | TYP | 60             |            |             |             |            | dB      |
| Undervoltage Lockout                           |     | Yes            |            |             |             |            |         |
| Input Reverse Voltage Protection               |     | Yes            |            |             |             |            |         |
| Input Current No Load<br>100% Load             | TYP | 12             | 12         | 12          | 12          | 12         | mA<br>A |
|                                                | TYP | 2.45           | 3.60       | 3.57        | 3.50        | 3.50       |         |
| Inrush Current                                 | MAX | 0.5            |            |             |             |            | A²S     |
| Reflected Ripple, 12µH<br>Source Impedance (3) | TYP | 30             |            |             |             |            | mA P-P  |
| Efficiency                                     | TYP | 81             | 85         | 88          | 88          | 89         | %       |
| Switching Frequency                            | TYP | 325            |            |             |             |            | kHz     |
| Recommended Fuse                               |     | (2)            |            |             |             |            | AMPS    |

\* Absolute Maximum Ratings. Caution: Stresses in excess of the Absolute Maximum Ratings can cause permanent damage to the device (see Note 1).

# 150 Watt HEW Single Series DC/DC Converters

Unless otherwise stated, these specifications apply for ambient temperature  $T_A=23 \pm 2^\circ\text{C}$ , nominal input voltage, and rated full load. (1)


| Output Parameters                                      |     |                          |                          |                            |                            |                          |                  |
|--------------------------------------------------------|-----|--------------------------|--------------------------|----------------------------|----------------------------|--------------------------|------------------|
| Model                                                  |     | 24S3.30HEW<br>48S3.30HEW | 24S5.30HEW<br>48S5.30HEW | 24S12.12HEW<br>48S12.12HEW | 24S15.10HEW<br>48S15.10HEW | 24S24.6HEW<br>48S24.6HEW | Units            |
| Output Voltage                                         |     | 3.3                      | 5                        | 12                         | 15                         | 24                       | VDC              |
| Output Voltage Setpoint Accuracy                       | MAX | ±1                       |                          |                            |                            |                          | %                |
| Turn On Overshoot                                      | TYP | 0                        |                          |                            |                            |                          | %                |
| Temperature Coefficient                                | TYP | 0.005                    | 0.003                    |                            |                            |                          | % / °C           |
|                                                        | MAX | 0.01                     | 0.005                    |                            |                            |                          |                  |
| Noise (8)                                              | TYP | 75                       | 75                       | 150                        | 150                        | 250                      | mV P-P<br>mV RMS |
|                                                        | TYP | 20                       | 20                       | 60                         | 60                         | 100                      |                  |
| Load Current (4)                                       | MIN | 3                        | 3                        | 1.25                       | 1                          | .626                     | ADC              |
|                                                        | MAX | 30                       | 30                       | 12.5                       | 10                         | 6.26                     |                  |
| Load Transient Overshoot (7)                           | TYP | 3                        |                          |                            |                            |                          | %                |
| Load Transient Recovery Time (6)                       | TYP | 200                      |                          |                            |                            |                          | µSec             |
| Load Regulation (5)<br>Min-Max Load                    | TYP | 0.02                     |                          |                            |                            |                          | %                |
|                                                        | MAX | 0.2                      |                          |                            |                            |                          |                  |
| Line Regulation<br>Vin = Min-Max                       | TYP | 0.01                     |                          |                            |                            |                          | %                |
|                                                        | MAX | 0.1                      |                          |                            |                            |                          |                  |
| Overvoltage Protection (OVP)<br>Threshold              | MIN | 115                      |                          |                            |                            |                          | %                |
| OVP Type - Non-latching<br>Open Loop Overvoltage Clamp | MAX | 135                      |                          |                            |                            |                          |                  |
| Output Current Limit<br>V out = 90% of V out-nom       | TYP | 120                      |                          |                            |                            |                          | %                |
| Output Short Circuit Current<br>V out = 0.25 V         | TYP | 140                      |                          |                            |                            |                          | %                |
|                                                        | MAX | 150                      |                          |                            |                            |                          |                  |

## NOTES:

- (1) Refer to the CALEX Application Notes for the definition of terms, measurement circuits, and other information.
- (2) Refer to the CALEX Application Notes for information on fusing. For inrush current, refer to the specifications above.
- (3) 100  $\mu\text{F}$  capacitor connected to two "Input" pins. Then place current sensor in series with 1.0  $\mu\text{H}$  inductor between 100  $\mu\text{F}$  and the source. The reflected ripple current is measured over a 5 Hz to 20 MHz bandwidth.(current sensor is located between the converter input pin and the 1.0  $\mu\text{H}$  inductor)
- (4) Optimum performance is obtained when this power supply is operated within the minimum to maximum load specifications. No damage to the module will occur when the output is operated at less than minimum load, however the output voltage may contain a low frequency component that may exceed output noise specifications.
- (5) Load regulation is defined as the output voltage change when changing load current from maximum to minimum.
- (6) Load Transient Recovery Time is defined as the time for the output to settle from a 50 to 75% step load change to a 1% error band (rise time of step = 2 $\mu\text{Sec}$ ).
- (7) Load Transient Overshoot is defined as the peak overshoot during a transient as defined in the Note 6 above.
- (8) Noise is measured per the CALEX Application Notes. Output noise is measured with a 10 $\mu\text{F}$  tantalum capacitor in parallel with a 0.1  $\mu\text{F}$  ceramic capacitor connected across the output to CMN. Measurement bandwidth is 0-20 MHz.
- (9) When an external On/Off switch is used, such as open collector switch, logic high requires the switch to be high-impedance. Switch leakage currents greater than 10  $\mu\text{A}$  may be sufficient to trigger the On/Off to the logic-low state.
- (10) Most switches would be suitable for logic On/Off control. In case there is a problem, you can make following estimations and then leave some margin.  
When open collector is used for logic high, "Open Circuit Voltage at On/Off Pin", "Output Resistance" and "External Leakage Current Allowed for Logic High" are used to estimate the high impedance requirement of open collector.  
When switch is used for logic low, "Open Circuit Voltage at On/Off Pin", "Output Resistance" and "LOW Logic Level" are used to estimate the low impedance requirement of switch.
- (11) Thermal impedance is tested with the converter mounted vertically and facing another printed circuit board 1/2 inch away. If converter is mounted horizontally with no obstructions, thermal impedance is approximately 8  $^\circ\text{C/W}$ .
- (12) Water Washability - Calex DC/DC converters are designed to withstand most solder/wash processes. Careful attention should be used when assessing the applicability in your specific manufacturing process. Converters are not hermetically sealed.
- (13) Torque fasteners into threaded mounting inserts at 12 in. oz. or less. Greater torque may result in damage to unit and void the warranty.
- (14) Input impedance on these units needs to be kept to a minimum. The 9-36Vdc DC units need a maximum input impedance of 0.135 Ohms and the 18-75Vdc DC units need a maximum input impedance of 0.54 Ohms. In order to support this requirement, the 9-36Vdc DC units need 55  $\mu\text{Farads}$  of capacitance (low ESR) for every 1.0  $\mu\text{Henry}$  of inductance between the power source and the DC-DC converter. The 18-75Vdc DC units need 3.5  $\mu\text{Farads}$  of capacitance (low ESR) for every 1.0  $\mu\text{Henry}$  of inductance between the power source and the DC-DC converter. Inductance includes all sources and should take into account input power lines.

# 150 Watt HEW Single Series DC/DC Converters

| General Specifications                                |                                      |                      |           |
|-------------------------------------------------------|--------------------------------------|----------------------|-----------|
| All Models                                            |                                      |                      | Units     |
| Remote ON/OFF Function                                |                                      |                      |           |
| HIGH Logic Level or Leave ON/OFF Open                 | MIN                                  | 3.0                  | VDC       |
| External Leakage Current Allowed for Logic High (9)   | MAX                                  | 10                   | μA        |
| Input Diode Protection Voltage                        | MAX                                  | 50                   | VDC       |
| LOW Logic Level or Tie ON/OFF Pin to -Input           | MAX                                  | 1.0                  | VDC       |
| Sinking Current for Logic Low                         | MAX                                  | 500                  | μA        |
| Open Circuit Voltage at On/Off Pin (10)               |                                      |                      |           |
| Positive Logic                                        | TYP                                  | 2.3                  | VDC       |
| Negative Logic                                        | TYP                                  | 1.5                  | VDC       |
| Output Resistance (10)                                | TYP                                  | 3                    | k Ohm     |
| Idle Current (Module is OFF)                          | TYP                                  | 2                    | mADC      |
| Turn-on Time to 1% error                              | TYP                                  | 20                   | mSec      |
| Positive Logic Option                                 | HIGH - Module ON<br>LOW - Module OFF |                      |           |
| Negative Logic Option                                 | HIGH - Module OFF<br>LOW - Module ON |                      |           |
| Output Voltage Remote Sensing                         |                                      |                      |           |
| Maximum Voltage Drops on Leads                        | MAX                                  | 10                   | %         |
| Line Regulation under remote sensing                  | TYP                                  | 0.02                 | %         |
|                                                       | MAX                                  | 0.1                  | %         |
| Load Regulation under remote sensing                  | TYP                                  | 0.05                 | %         |
|                                                       | MAX                                  | 0.2                  | %         |
| Output Voltage Trim                                   |                                      |                      |           |
| Trim Range                                            | MIN<br>MAX                           | -10<br>+10           | % of Vout |
| Input Resistance                                      | TYP                                  | 10                   | k Ohm     |
| Open Circuit Voltage                                  | TYP                                  | 2.5                  | V         |
| Trim Limit                                            |                                      |                      |           |
| Maximum Output Voltage                                | MAX                                  | 110                  | % of Vout |
| Isolation                                             |                                      |                      |           |
| Input to Output Isolation 10μA Leakage                |                                      |                      |           |
| Vnom = 24V                                            | MAX                                  | 700                  | VDC       |
| Vnom = 48V                                            | MAX                                  | 1544                 | VDC       |
| Input to Output Resistance                            | MIN                                  | 10                   | Mohm      |
| Input to Output Capacitance                           | TYP                                  | 1600                 | pF        |
| Environmental                                         |                                      |                      |           |
| Calculated MTBF, Bellcore Method 1, Case 1            |                                      | >1,000,000           | Hr        |
| Baseplate Operating Temperature Range                 | MIN<br>MAX                           | -40<br>100           | °C        |
| Storage Temperature                                   | MIN<br>MAX                           | -40<br>120           | °C        |
| Thermal Impedance (11)                                | TYP                                  | 7                    | °C/W      |
| Thermal Shutdown Baseplate Temperature (Auto Restart) | MIN<br>TYP                           | 100<br>110           | °C        |
| General                                               |                                      |                      |           |
| Unit Weight                                           | TYP                                  | 4.6/114              | oz/g      |
| Case Dimension                                        |                                      | 2.4" x 2.28" x 0.55" |           |
| Torque on Mounting Inserts                            | MAX                                  | 12 in. oz.           |           |
| Agency Approvals                                      |                                      |                      |           |
| UL, TUV                                               | Pending for UL60950, EN60950 (TUV)   |                      |           |
| Chassis Mounting Kit                                  | MS21                                 |                      |           |



Mechanical tolerances unless otherwise noted:

X.XX dimensions: ±0.020 inches

X.XXX dimensions: ±0.005 inches

| Pin | Function | 9-36 VDC pin dia. | 18-75 VDC pin dia. |
|-----|----------|-------------------|--------------------|
| 1   | - INPUT  | 0.08"             | 0.04"              |
| 2   | CASE     | 0.04"             | 0.04"              |
| 3   | ON/OFF   | 0.04"             | 0.04"              |
| 4   | +INPUT   | 0.08"             | 0.04"              |
| 5   | - OUTPUT | 0.08"             | 0.08"              |
| 6   | - SENSE  | 0.04"             | 0.04"              |
| 7   | TRIM     | 0.04"             | 0.04"              |
| 8   | +SENSE   | 0.04"             | 0.04"              |
| 9   | +OUTPUT  | 0.08"             | 0.08"              |