


DO NOT SCALE

DIMENSIONS IN mm

METRIC




THIRD ANGLE

PROJECTION





NOTES:

- 1 FOR USE ON MINIATURE APPLICATORS (LEFT-RIGHT FEED)
- 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI




2	OBSOLETE	1	PRE-TINPLATED	BRASS	160869-7	F1
2	OBSOLETE	1	PRE-TINPLATED	PHOSPHORBRONZE	160869-6	F1
		1	UNPLATED	PHOSPHORBRONZE	160869-5	F1
	OBSOLETE	1	TINPLATED	PHOSPHORBRONZE	160869-4	F1
2	OBSOLETE	1	UNPLATED	PHOSPHORBRONZE	160869-3	F1
		1	TINPLATED	BRASS	160869-2	F1
	OBSOLETE	1	UNPLATED	BRASS	160869-1	F2
			PLATING	PLATING	MATERIAL	PARTNUMBER
						REV.



WIRE RANGE :
0,5-1,0 mm²
INSULATION RANGE :
2,0-2,7mm DIA.

DIRECTION OFF TOP OF REEL



CUSTOMER DRAWING					FOR REFERENCE ONLY WILL NOT BE UPDATED	
© COPYRIGHT 19- BY TE ITALIA S.p.A.					ALL INTERNATIONAL RIGHTS RESERVED. TE PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.	
THIS DRAWING IS UNPUBLISHED					RELEASED FOR PUBLICATION	
TE Connectivity					NAME	
FASTIN-FASTON® Connector					.250" sr. TAB CONTACT	
REVISION RECORD					DR. J.v.LIEMPT. CHK. A.BIJNEN. APP. L.v.SOEST. DATE: 23 MAR 1992 DATE: - DATE: -	
DWG.No. C-160869					REV.LTR. F2 SHEET 1 OF 1	