



## Motor Terminal Blocks

### TYPE 711

20 mm spacing - 6 poles

[Inventory Check](#)

| Series | Download PDF | 3D Model | Can plug with | How to order | Print |
|--------|--------------|----------|---------------|--------------|-------|
|--------|--------------|----------|---------------|--------------|-------|



#### Dimensions: mm (in.)

L = 54.0 (2.13)  
 W = 34.0 (1.34)  
 H = 27.0 (1.06)  
 A = 20.0 (0.79)  
 B = M4  
 C = 5.3 (0.21)

## Description

Series 71 steatite motor terminal board have two recessed mounting holes; they feature separating walls molded between each clamping bolt to help prevent unwanted contact between adjacent connections. They are supplied with plain washers and brass nuts.

Recommended mounting hardware: M10 pan head screw (#10-24 pan head screw)

- Ceramic Motor Terminal Board
- With Clamping Nuts and Plain Washers
- With Mounting Holes

## Technical Data

**Center to Center Spacing:** 20 mm (0.79 in.)

**Nominal Cross Section:**

1.5 mm<sup>2</sup> (1550 mils<sup>2</sup>)

(maximum load at 40°C (104°F) ambient temperature)

**Recommended operating**

**Voltage:** 500 V

**Recommended operating**

**Current:** 16A

**Recommended operating Wire**

**Range:** 14 AWG

## Material

**Molding:** Steatite KER 220, DIN 40685, color white

**Temperature upper limit:** 240°C (464°F)

**Threaded Post:** M4, Blank brass

**Nut:** Blank brass

**Washer:** Zinc plated blue passivated, steel substrate

## How to order

Item

711

**Ordering Note:** For use with jumper 751-A

**Request sample**

**Request quote**

Quantity

### Accessories

Jumpers, Series 75.

711

[Add to shopping cart](#)