

	1	1	-	C	2-456403-4			CRIMPER, WIRE		1			
	-3	-2	U/M	DWG SIZE	PART NO		DESCRIPTION			ITEM NO			
← REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)													
QTY REQD PER ASSY					PARTS LIST								
DIMENSIONS IN INCHES. DO NOT SCALE PRINT. TOLERANCES UNLESS OTHERWISE SPECIFIED: 2 PLC DEC ±.02 3 PLC DEC ±- 4 PLC DEC ±- ANGLES ±- SURF TEXTURE: 				MATL		-	HT TR		-	FIN	-		
				DR		5/19/95	APP	5-30-95	 AMP Incorporated Harrisburg, PA 17105-3508				
				L. COLLINS			BEDDOCK						
				CHK		5-30-95	REL	6/9/95					
				C. ERISMAN			B. MORGAN						
NAME					SIDE FEED HDM APPLICATOR					MACHINE REF			
										MINI APPL			
REMOVE BURRS, BREAK SHARP EDGES R.015 MAX				SCALE	-		DWG NO	466689		SHEET 1 OF 1	REV H		
CASE CODE 00779		CUSTOMER AND ASSEMBLY DRAWING							RESTRICTED TO				



QTY REQD PER ASSY				PARTS LIST	
			H	0150-9637-99	
			G	015A-0414-99	
			F1	0150-9573-99, ADD -3	
			F	0150-7810-97	
			E	0150-6393-95	
			D	0150-6151-95	
P	F	LTR		REVISION RECORD	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[466689-2](#)