


Rotary Switches



Dual In Line Type



Dimensions : Millimetres (Inches)

Truth Table

O Real Code				
Position	Code			
	1	2	4	8
0	●	●	●	●
1	○	●	●	●
2	●	○	●	●
3	○	○	●	●
4	●	●	○	●
5	○	●	○	●
6	●	○	○	●
7	○	○	○	●
8	●	●	●	○
9	○	●	●	○
A	●	○	●	○
B	○	○	●	○
C	●	●	○	○
D	○	●	○	○
E	●	○	○	○
F	○	○	○	○





Rotary Switches

Dual In Line Type




MCRH4



Dimensions : Millimetres (Inches)


MCRH3



Dimensions : Millimetres (Inches)

Rotary Switches

Dual In Line Type



Specifications:

Mechanical:

Mechanical life : 200 mΩ maximum, 20,000 steps
Maximum operating force : 400 gf

Environmental:

Operating temperature range : -25°C to +80°C
Storage temperature range : -40°C to +85°C

Electrical:

Electrical life : 200 mΩ maximum, 20,000 steps
Non-Switching rating : 100 mA, 50 V dc
Switching rating : 25 mA, 24 V dc
Contact resistance : 100 mΩ maximum (initial)
200 mΩ (final - after test)

Minimum insulation resistance : 100 MΩ at 250 V dc
Voltage proof : 250 V ac for 1 minute


Materials:

Base and cover : UL 94V-0 nylon thermoplastic
Colour : Black
Actuator : UL 94V-0 LCP thermoplastic
Colour : White
Contact : Alloy copper with gold plated over nickel
Terminal : Brass with gold plated

Rotary Switches



Dual In Line Type



Reflow Temperature Profile

Soldering Process:

Hand Soldering : Use a soldering iron of 30 watts, controlled at (350°C) approximately maximum 5 seconds

Wave Soldering : Recommended temperature at 500°F (260°C) maximum of 5 s (for through hole type)

Reflow Soldering : When applying reflow soldering, the peak temperature or the reflow oven should be set at 260°C maximum

Part Number Table

Description	Part Number
Rotary Dip Switch	MCRH4AF-10R
Rotary Dip Switch	MCRH3AF-10R
Rotary Dip Switch	MCRH2AF-10R
Rotary Dip Switch	MCRH4AF-16R
Rotary Dip Switch	MCRH3AF-16R
Rotary Dip Switch	MCRH2AF-16R
Rotary Dip Switch, SMD	MCRM4AF-10R
Rotary Dip Switch, SMD	MCRM3AF-10R
Rotary Dip Switch, SMD	MCRM2AF-10R
Rotary Dip Switch, SMD	MCRM4AF-16R
Rotary Dip Switch, SMD	MCRM3AF-16R
Rotary Dip Switch, SMD	MCRM2AF-16R




Rotary Switches



Dual In Line Type

Part Number Explanation:



- | | |
|-------------------------|---|
| Terminal Type | : H = Through Hole
M = SMT |
| Number of Terminals | : 2 = 3 × 2
3 = 3 × 3
4 = 4 × 1 |
| Actuator Type | :  = Recessed Actuator |
| Solder Plating | : A = Terminal : Gold Plated Over Nickel |
| Maximum Operating Force | : 200gf cm |
| Number of Steps | : 10 = 10 Steps
16 = 16 Steps |

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

