

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

MAY ,2006.

© COPYRIGHT 2006 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

C

ECR-06-012506

31MAY06

JMS

FWK

NOTES:

1 PACK IN ACCORDANCE WITH AMP SPEC 107-3275

2 100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275

3 Au PLATING

4 Ni PLATING

5 THIS ITEM MUST BE WHITE

6 ELECTRICAL CHARACTERISTICS

FREQUENCY RANGE:

DC - 500 MHz

NOMINAL IMPEDANCE:

Non Constant

INSULATION RESISTANCE:

5000 MOhm

WORKING VOLTAGE:

500 Volts RMS at Sea Level

DIELECTRIC WITHSTAND VOLTAGE:

1500 Volts RMS Max

CONTACT RESISTANCE:

CENTRE CONTACT:

3.00 mOhm Max

OUTER CONTACT:

2.00 mOhm Max

7 MECHANICAL CHARACTERISTICS

COUPLING NUT RETENTION FORCE:

N/A

CABLE RETENTION FORCE:

170N Min

CLAMP NUT RECOMMENDED TORQUE:

4N

DURABILITY:

500 Cycles Min



8 ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE:

-65 to +165 DegC

9 FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE

10 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED

RECOMMENDED
CABLE STRIPPING DIM'S

		1	1	BRASS	4	CLAMP NUT	7
		1	1	SILICONE RUBBER	5	GASKET	6
		1	1	BRASS	4	SLEEVE	5
		1	1	PTFE		INSULATION	4
		1	1	BRASS	3	CONTACT	3
		1	1	PTFE		INSULATION	2
		1	1	BRASS	4	BODY	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		2	1				
QUANTITY PER ASSY				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN J.SANDWELL 31MAY06

CHK S.PARLOW 31MAY06

APVD F.WHEELER-KING 31MAY06

PRODUCT SPEC

APPLICATION SPEC

411-3257

WEIGHT -

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics Corporation
Bideford EX39 4HE

NAME

UHF STRAIGHT JACK SOLDER
RG58C/U, 141A/U, URM43, 76, KX15

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1337652

SCALE NTS

SHEET 1 OF 1

REV C