

**M52734SP****3-CHANNEL VIDEO AMPLIFICATION WITH OSD BLANKING****DESCRIPTION**

The M52734SP is a semiconductor integrated circuit amplifies video signals, having a 3-channel amplifier with a band width of 130MHz. The circuit also features the OSD mixing function.

The circuit is most useful with high resolution displays that have OSD, and its function are available for each channel, including OSD blanking, OSD mixing, wide-band amplification, contrast control (main and sub), and brightness control.

**FEATURES**

- Frequency band width: RGB.....130MHz (3VP-P)  
OSD.....50MHz
- Input :RGB.....0.7VP-P (typ.)  
OSD.....3.0VP-P min. (positive)  
BLK .....3.0VP-P min. (positive)
- Output :RGB.....4.0VP-P (max.)  
OSD.....4.0VP-P (max.)
- To adjust contrast, two types of controls are provided, main and sub. With the main control, the contrast of the 3-channels can be changed simultaneously. Sub controls are used to adjust the contrast of a given channel individually. The control terminals can be controlled by applying a voltage of 0 to 5V.
- The DC power remains stable at the IC output terminal because a feedback circuit is built in.


**APPLICATION**

Display monitor

**RECOMMENDED OPERATING CONDITION**


Supply voltage range.....11.5 to 12.5V

Rated supply voltage.....12.0V

**PIN CONFIGURATION (TOP VIEW)**

Outline 36P4E

NC : NO CONNECTION

**BLOCK DIAGRAM**

**M52734SP****3-CHANNEL VIDEO AMPLIFICATION WITH OSD BLANKING****ABSOLUTE MAXIMUM RATINGS** (Ta=25°C)

Symbol	Parameter	Ratings	Unit
V <sub>CC</sub>	Supply voltage	13.0	V
P <sub>d</sub>	Power dissipation	2016	mW
T <sub>opr</sub>	Ambient temperature	-20 to +85	°C
T <sub>stg</sub>	Storage temperature	-40 to +150	°C
V <sub>opr</sub>	Recommended supply voltage	12.0	V
V <sub>opr'</sub>	Recommended supply voltage range	11.5 to 12.5	V
Surge	Electrostatic discharge	±200	V

**ELECTRICAL CHARACTERISTICS** (V<sub>CC</sub>=12V, Ta=25°C, unless otherwise noted)

Symbol	Parameter	Test conditions										Limits			Unit
		Test point (s)	Input			External power supply (V)				Pulse input		Min.	Typ.	Max.	
			SW13 R-ch	SW8 G-ch	SW3 B-ch	V4	V17	V19	V36	SW18	SW1 5, 10, 15				
Icc	Circuit current	A	a –	a –	a –	5	5	5	2	b SG5	a –	70	100	140	mA
Vomax	Output dynamic range	T.P.35 T.P.30 T.P.25	b SG6	b SG6	b SG6	5	5	Variable	5	b SG5	a –	5.8	6.8	9.0	VP-P
Vimax	Maximum input	T.P.35 T.P.30 T.P.25	b SG6	b SG6	b SG6	5	2.5	1	5	b SG5	a –	1	1.8	–	VP-P
Gv	Maximum gain	T.P.35 T.P.30 T.P.25	b SG6	b SG6	b SG6	5	5	2	5	b SG5	a –	15	17	20	dB
ΔGv	Relative maximum gain		Relative to measured values above									0.8	1	1.2	–
VCR1	Contrast control characteristics (typical)	T.P.35 T.P.30 T.P.25	b SG6	b SG6	b SG6	5	4	2	5	b SG5	a –	14	15.5	17	dB
ΔVCR1	Contrast control relative characteristics (typical)		Relative to measured values above									0.8	1	1.2	–
VCR2	Contrast control characteristics (minimum)	T.P.35 T.P.30 T.P.25	b SG6	b SG6	b SG6	5	1	2	5	b SG5	a –	0.3	0.6	0.9	VP-P
ΔVCR2	Contrast control relative characteristics (minimum)		Relative to measured values above									0.8	1	1.2	–
VSCR1	Sub contrast control characteristics (typical)	T.P.35 T.P.30 T.P.25	b SG6	b SG6	b SG6	4	5	2	5	b SG5	a –	14	15.5	17	dB
ΔVSCR1	Sub contrast control relative characteristics (typical)		Relative to measured values above									0.8	1	1.2	–
VSCR2	Sub contrast control characteristics (minimum)	T.P.35 T.P.30 T.P.25	b SG6	b SG6	b SG6	1	5	2	5	b SG5	a –	0.5	0.9	1.3	VP-P
ΔVSCR2	Sub contrast control relative characteristics (minimum)		Relative to measured values above									0.8	1	1.2	–
VSCR3	Contrast/sub contrast control characteristics (typical)	T.P.35 T.P.30 T.P.25	b SG6	b SG6	b SG6	3	3	2	5	b SG5	a –	0.8	1.5	2.2	VP-P
ΔVSCR3	Contrast/sub contrast control relative characteristics (typical)		Relative to measured values above									0.8	1	1.2	–
VB1	Brightness control characteristics (maximum)	T.P.35 T.P.30 T.P.25	a –	a –	a –	5	5	4	5	b SG5	a –	3.0	3.6	4.2	V
ΔVB1	Brightness control relative characteristics (maximum)		Relative to measured values above									-0.3	0	0.3	V

**3-CHANNEL VIDEO AMPLIFICATION WITH OSD BLANKING****ELECTRICAL CHARACTERISTICS** (cont.)

Symbol	Parameter	Test point (s)	Test conditions									Limits			Unit
			Input			External power supply (V)				Pulse input		Min.	Typ.	Max.	
			SW13 R-ch	SW8 G-ch	SW3 B-ch	V4	V17	V19	V36	SW18	SW1 5, 10, 15				
V <sub>B2</sub>	Brightness control characteristics (typical)	T.P.35 T.P.30 T.P.25	a —	a —	a —	5	5	2.5	5	b SG5	a —	1.7	2.3	2.9	V
ΔV <sub>B2</sub>	Brightness control relative characteristics (typical)		Relative to measured values above									-0.3	0	0.3	V
V <sub>B3</sub>	Brightness control characteristics (minimum)	T.P.35 T.P.30 T.P.25	a —	a —	a —	5	5	1	5	b SG5	a —	0.5	0.9	1.3	V
ΔV <sub>B3</sub>	Brightness control relative characteristics (minimum)		Relative to measured values above									-0.3	0	0.3	V
F <sub>C1</sub>	Frequency characteristics 1 (f=50MHz;maximum)	T.P.35 T.P.30 T.P.25	b SG2	b SG2	b SG2	5	2.5	V <sub>T</sub>	—	a —	a —	-2.5	-1	3	dB
ΔF <sub>C1</sub>	Frequency relative characteristics 1 (f=50MHz;maximum)		Relative to measured values above									-1	0	1	dB
F <sub>C1</sub> '	Frequency characteristics 1 (f=130MHz;maximum)	T.P.35 T.P.30 T.P.25	b SG3	b SG3	b SG3	5	2.5	V <sub>T</sub>	—	a —	a —	-3	-2	3	dB
ΔF <sub>C1</sub> '	Frequency relative characteristics 1 (f=130MHz;maximum)		Relative to measured values above									-1	0	1	dB
F <sub>C2</sub>	Frequency characteristics 2 (f=50MHz; maximum)	T.P.35 T.P.30 T.P.25	b SG2	b SG2	b SG2	5	1.5	V <sub>T</sub>	—	a —	a —	-3	0	3	dB
ΔF <sub>C2</sub> '	Frequency relative characteristics 2 (f=130MHz; maximum)	T.P.35 T.P.30 T.P.25	b SG3	b SG3	b SG3	5	1.5	V <sub>T</sub>	—	a —	a —	-1	0	1	dB
C.T.1	Crosstalk 1 (f=50MHz)	T.P.35 T.P.30 T.P.25	b SG2	a —	a —	5	5	V <sub>T</sub>	—	a —	a —	—	-30	-20	dB
C.T.1'	Crosstalk 1 (f=130MHz)	T.P.35 T.P.30 T.P.25	b SG3	a —	a —	5	5	V <sub>T</sub>	—	a —	a —	—	-20	-15	dB
C.T.2	Crosstalk 2 (f=50MHz)	T.P.35 T.P.30 T.P.25	a —	b SG2	a —	5	5	V <sub>T</sub>	—	a —	a —	—	-30	-20	dB
C.T.2'	Crosstalk 2 (f=130MHz)	T.P.35 T.P.30 T.P.25	a —	b SG3	a —	5	5	V <sub>T</sub>	—	a —	a —	—	-20	-15	dB
C.T.3	Crosstalk 3 (f=50MHz)	T.P.35 T.P.30 T.P.25	a —	a —	b SG2	5	5	V <sub>T</sub>	—	a —	a —	—	-30	-20	dB
C.T.3'	Crosstalk 3 (f=130MHz)	T.P.35 T.P.30 T.P.25	a —	a —	b SG3	5	5	V <sub>T</sub>	—	a —	a —	—	-20	-15	dB
Tr	Pulse characteristics 1	T.P.35 T.P.30 T.P.25	b SG4	b SG4	b SG4	5	3.3	2	—	b SG5	a —	—	3	7	nsec
Tf	Pulse characteristics 2	T.P.35 T.P.30 T.P.25	b SG4	b SG4	b SG4	5	3.3	2	—	b SG5	a —	—	4	8	nsec
V14th	Clamp pulse threshold voltage	T.P.35 T.P.30 T.P.25	a —	a —	a —	5	5	2	—	b SG5	a —	1.0	1.5	2.0	V <sub>DC</sub>
W14	Clamp pulse minimum width	T.P.35 T.P.30 T.P.25	a —	a —	a —	5	5	2	—	b SG5	a —	—	0.1	0.5	μsec
P <sub>DCH</sub>	Pedestal voltage temperatere characteristics1	T.P.35 T.P.30 T.P.25	b SG6	b SG6	b SG6	5	5	2		b SG5	a —	-0.3	0	0.3	V <sub>DC</sub>

**3-CHANNEL VIDEO AMPLIFICATION WITH OSD BLANKING****ELECTRICAL CHARACTERISTICS** (cont.)

Symbol	Parameter	Test conditions										Limits			Unit
		Test point (s)	Input			External power supply (V)				Pulse input					
			SW13 R-ch	SW8 G-ch	SW3 B-ch	V4	V17	V19	V36	SW18	SW1 5, 10, 15	Min.	Typ.	Max.	
PDCL	Pedestal voltage temperatere characteristics2	T.P.35 T.P.30 T.P.25	b SG6	b SG6	b SG6	5	5	2	–	b SG5	a –	-0.3	0	0.3	VDC
OTr	OSD pulse characteristics1	T.P.35 T.P.30 T.P.25	a –	a –	a –	5	5	2	3	a –	b SG7	–	4	8	nsec
OTf	OSD pulse characteristics2	T.P.35 T.P.30 T.P.25	a –	a –	a –	5	5	2	3	a –	b SG7	–	4	8	nsec
Oaj1	OSD adjusting control characteristics (maximum)	T.P.35 T.P.30 T.P.25	a –	a –	a –	5	5	2	4	a –	b SG7	3.5	4.0	4.5	VP-P
ΔOaj1	OSD adjusting control relative characteristics (maximum)		Relative to measured values above									0.8	1	1.2	–
Oaj2	OSD adjusting control characteristics (minimum)	T.P.35 T.P.30 T.P.25	a –	a –	a –	5	5	2	0	a –	b SG7	–	0	0.5	VP-P
ΔOaj2	OSD adjusting control relative characteristics (minimum)		Relative to measured values above									0.8	1	1.2	–
OSDth	OSD input threshold voltage	T.P.35 T.P.30 T.P.25	a –	a –	a –	5	5	2	5	a –	b SG7	1.7	2.5	3.5	VDC
V1th	BLK input threshold voltage	T.P.35 T.P.30 T.P.25	b SG6	b SG6	b SG6	5	5	2	5	a –	SW1 only b SG7	1.7	2.5	3.5	VDC

**ELECTRICAL CHARACTERISTICS TEST METHOD**

1. Because a description of signal input pin and pulse input pin switch numbers is already given in Supplementary Table, only external power supply switch numbers are included in the notes below.

Sub contrast voltages V4, V9 and V14 are always set to the same voltage, therefore only V4 is referred to in Supplementary Table.

**Icc Circuit current**


Measuring conditions are as listed in Supplementary Table.

Measured with an ammeter At test point A when SW1 is set to a.

**Vomax Output dynamic range**

Voltage V19 is varied as described below:

- Increase V19 gradually while inputting SG6 to pin 13 (8 or 3). Measure the voltage when the top of the waveform output at T.P.25 (30 or 35) is distorted. The voltage is called V<sub>TR1</sub> (V<sub>TG1</sub> or V<sub>TB1</sub>). Next, decrease V19 gradually, and measure the voltage when the bottom of the waveform output at T.P.35 (30 or 25) is distorted. The voltage is called V<sub>TR2</sub> (V<sub>TG2</sub> or V<sub>TB2</sub>).



Waveform Output at T.P.25  
(Identical to output at T.P.30 and T.P.35.)

- Voltage V<sub>T</sub> (V<sub>TR</sub>, V<sub>TG</sub> and V<sub>TB</sub>) is calculated by the equation below:

$$V_{TR} (V_{TG}, V_{TB}) = \frac{V_{TR1} (V_{TG1}, V_{TB1}) + V_{TR2} (V_{TG1}, V_{TB1})}{2}$$

Use relevant voltages, depending on the pin at which the waveform is output; specifically, use V<sub>TR1</sub> when it is output at T.P.25; V<sub>TG1</sub>, at T.P.30, and V<sub>TB</sub>, at T.P.35.

## 3-CHANNEL VIDEO AMPLIFICATION WITH OSD BLANKING

3. After setting  $V_{TR}$  ( $V_{TG}$  or  $V_{TB}$ ), increase the SG6 amplitude gradually, starting from 700mV. Measure the amplitude when the top and bottom of the waveform output at T.P25 (30 or 35) starts becoming distorted synchronously.

**Vimax Maximum input**

Measuring conditions are the same as those used above, except that the setting of V17 is changed to 2.5V as specified in Supplementary Table. Increase the input signal amplitude gradually, starting from 700mV<sub>P-P</sub>. Measure the amplitude when the output signal starts becoming distorted.

**Gv Maximum gain****ΔGv Relative maximum gain**

1. Input SG6 to pin 13 (8 or 3), and read the amplitude at output T.P25 (30 or 35). The amplitude is called  $V_{OR1}$  ( $V_{OG1}$  or  $V_{OB1}$ ).
2. Maximum gain  $G_v$  is calculated by the equation below:

$$G_v = 20 \log \frac{V_{OR1} (V_{OG1}, V_{OB1})}{0.7} \frac{[V_{P-P}]}{[V_{P-P}]}$$

3. Relative maximum gain  $\Delta G$  is calculated by the equation below:

$$\Delta G_v = V_{OR1}/V_{OG1}, V_{OG1}/V_{OB1}, V_{OB1}/V_{OR1}$$

**Vcr1 Contrast control characteristics (typical)****ΔVcr1 Contrast control relative characteristics (typical)**

1. Measuring conditions are as given in Supplementary Table. The setting of V17 is changed to 4V.
2. Measure the amplitude output at T.P25 (30 or 35). The measured value is called  $V_{OR2}$  ( $V_{OG2}$  or  $V_{OB2}$ ).
3. Contrast control characteristics  $V_{CR1}$  and relative characteristics  $\Delta V_{CR1}$  are calculated, respectively, by the equations below:

$$V_{CR1} = 20 \log \frac{V_{OR2} (V_{OG2}, V_{OB2})}{0.7} \frac{[V_{P-P}]}{[V_{P-P}]}$$

$$\Delta V_{CR1} = V_{OR2}/V_{OG2}, V_{OG2}/V_{OB2}, V_{OB2}/V_{OR1}$$

**Vcr2 Contrast control characteristics (minimum)****ΔVcr2 Contrast control relative characteristics (minimum)**

1. Measuring conditions are as given in Supplementary Table. The setting of V17 is changed to 1.0V.
2. Measure the amplitude output at T.P25 (30 or 35). The measured value is called  $V_{OR3}$  ( $V_{OG3}$  or  $V_{OB3}$ ), and is treated as  $V_{CR2}$ .
3. Contrast control relative characteristics  $\Delta V_{CR2}$  are calculated by the equation below:

$$\Delta V_{CR2} = V_{OR3}/V_{OG3}, V_{OG3}/V_{OB3}, V_{OB3}/V_{OR3}$$

**Vscr1 Sub contrast control characteristics (typical)****ΔVscr1 Sub contrast control relative characteristics (typical)**

1. Set V4, V9 and V14 to 4.0V. Other conditions are as given in Supplementary Table.
2. Measure the amplitude output at T.P25 (30 or 35). The measured value is called  $V_{OR4}$  ( $V_{OG4}$  or  $V_{OB4}$ ).
3. Sub contrast control characteristics  $V_{SCR1}$  and relative characteristics  $\Delta V_{SCR1}$  are calculated, respectively, by the equations below:

$$V_{SCR1} = 20 \log \frac{V_{OR4} (V_{OG4}, V_{OB4})}{0.7} \frac{[V_{P-P}]}{[V_{P-P}]}$$

$$\Delta V_{SCR1} = V_{OR4}/V_{OG4}, V_{OG4}/V_{OB4}, V_{OB4}/V_{OR4}$$

**Vscr2 Sub contrast control characteristics (minimum)****ΔVscr2 Sub contrast control relative characteristics (minimum)**

1. Set V4, V9 and V14 to 1.0V. Other conditions are as given in Supplementary Table.
2. Measure the amplitude output at T.P25 (30 or 35). The measured value is called  $V_{OR5}$  ( $V_{OG5}$  or  $V_{OB5}$ ).
3. Relative characteristics  $\Delta V_{SCR2}$  are calculated by the equation below:

$$\Delta V_{SCR2} = V_{OR5}/V_{OG5}, V_{OG5}/V_{OB5}, V_{OB5}/V_{OR5}$$

**Vscr3 Contrast/sub contrast control characteristics (typical)****ΔVscr3 Contrast/sub contrast control relative characteristics (typical)**

1. Set V4, V9, V14 and V17 to 3.0V. Other conditions are as given in Supplementary Table.
2. Measure the amplitude at T.P25 (30 or 35). The measured value is called  $V_{OR6}$  ( $V_{OG6}$  or  $V_{OB6}$ ).

$$V_{CR3} = 20 \log \frac{V_{OR6} (V_{OG6}, V_{OB6})}{0.7} \frac{[V_{P-P}]}{[V_{P-P}]}$$

$$\Delta V_{CR3} = V_{OR6}/V_{OG6}, V_{OG6}/V_{OB6}, V_{OB6}/V_{OR6}$$

**Vb1 Brightness control characteristics (maximum)****ΔVb1 Brightness control relative characteristics (maximum)**

1. Measuring conditions are as given in Supplementary Table.
2. Measure the output at T.P25 (30 or 35) with a voltmeter. The measured value is called  $V_{OR7}$  ( $V_{OG7}$  or  $V_{OB7}$ ), and is treated as  $V_{B1}$ .
3. To obtain brightness control relative characteristics, calculate the difference in the output between the channels, using  $V_{OR7}$ ,  $V_{OG7}$  and  $V_{OB7}$ .

$$\Delta V_{B1} = V_{OR7} - V_{OG7} \quad [mV]$$

$$= V_{OG7} - V_{OB7}$$

$$= V_{OB7} - V_{OR7}$$

**3-CHANNEL VIDEO AMPLIFICATION WITH OSD BLANKING****VB2 Brightness control characteristics (typical)****ΔVB2 Brightness control relative characteristics (typical)**

1. Measuring conditions are as given in Supplementary Table.
2. Measure the output at T.P25 (30 or 35) with a voltmeter.  
The measured value is called VOR7' (VOG7' or VOB7'), and is treated as VB2.
3. To obtain brightness control relative characteristics (ΔVB2), calculate the difference in the output between the channels, using VOR7', VOG7', and VOB7'.

$$\begin{aligned}\Delta VB2 &= VOR7' - VOG7' & [mV] \\ &= VOG7' - VOB7' \\ &= VOB7' - VOR7'\end{aligned}$$

**VB3 Brightness control characteristics (minimum)****ΔVB3 Brightness control relative characteristics (minimum)**

1. Measuring conditions are as given in Supplementary Table.
2. Measure the output at T.P25 (30 or 35) with a voltmeter.  
The measured value is called VOR7'' (VOG7'' or VOB7''), and is treated as VB2.
3. To obtain brightness control relative characteristics (ΔVB3), calculate the difference in the output between the channels, using VOR7'', VOG7'' and VOB7''.

$$\begin{aligned}\Delta VB3 &= VOR7'' - VOG7'' & [mV] \\ &= VOG7'' - VOB7'' \\ &= VOB7'' - VOR7''\end{aligned}$$

**FC1 Frequency characteristics1 (f=50MHz; maximum)****ΔFC1 Frequency relative characteristics1****(f=50MHz; maximum)****FC1' Frequency characteristics1 (f=130MHz; maximum)****ΔFC1' Frequency relative characteristics1****(f=130MHz; maximum)**

1. Measuring conditions are as given in Supplementary Table.
2. SG1·SG2 and SG3 are input. The amplitude of the waveform output at T.P25 (30 or 35) is measured.
3. Supposing that the measured value is treated as amplitude VOR1 (VOG1 or VOB1) when SG1 is input, as VOR8 (VOG8 or VOB8) when SG2 is input, or as VOR9 (VOG9 or VOB9) when SG3 is input, frequency characteristics FC1 and FC1' are calculated as follows:

$$\begin{aligned}FC1 &= 20 \text{LOG} \frac{VOR8 (VOG8, VOB8)}{VOR1 (VOG1, VOB1)} \frac{[VP-P]}{[VP-P]} \\ FC1' &= 20 \text{LOG} \frac{VOR9 (VOG9, VOB9)}{VOR1 (VOG1, VOB1)} \frac{[VP-P]}{[VP-P]}\end{aligned}$$

4. Frequency relative band widths ΔFC1 and ΔFC1' are equal to the difference in FC1 and FC1', respectively, between the channels.

**FC2 Frequency characteristics2 (f=50MHz; maximum)****ΔFC2' Frequency relative characteristics2****(f=130MHz; maximum)**

Measuring conditions and procedure are the same as described in FC1, ΔFC1, FC1', ΔFC1', except that CONTRAST (V17) is turned down to 1.5V.

**C.T.1 Crosstalk1 (f=50MHz)****C.T.1' Crosstalk1 (f=130MHz)**

1. Measuring conditions are as given in Supplementary Table.
2. Input SG2 (or SG3) to pin 13 (R-ch) only, and then measure the waveform amplitude output at T.P25 (30 or 35). The measured value is called VOR, VOG and or VOB respectively.
3. Crosstalk C.T. 1 is calculated by the equation below:

$$\begin{aligned}C.T.1 &= 20 \text{LOG} \frac{VOG \text{ or } VOB}{VOR} \frac{[VP-P]}{[VP-P]} \text{ [dB]} \\ (C.T.1')\end{aligned}$$

**C.T.2 Crosstalk2 (f=50MHz)****C.T.2' Crosstalk2 (f=130MHz)**

1. Change the input pin from pin 13 (R-ch) to pin 8 (G-ch), and measure the output in the same way as in C.T.1, C.T.1'.
2. Crosstalk C.T. 2 is calculated by the equation below:

$$\begin{aligned}C.T.2 &= 20 \text{LOG} \frac{VOR \text{ or } VOB}{VOG} \frac{[VP-P]}{[VP-P]} \text{ [dB]} \\ (C.T.2')\end{aligned}$$

**C.T.3 Crosstalk3 (f=50MHz)****C.T.3' Crosstalk3 (f=130MHz)**

1. Change the input pin from pin 13 (R-ch) to pin 3 (B-ch), and measure the output in the same way as in C.T.1, C.T.1'.
2. Crosstalk C.T. 3 is calculated by the equation below:


$$\begin{aligned}C.T.3 &= 20 \text{LOG} \frac{VOR \text{ or } VOG}{VOB} \frac{[VP-P]}{[VP-P]} \text{ [dB]} \\ (C.T.3')\end{aligned}$$

**3-CHANNEL VIDEO AMPLIFICATION WITH OSD BLANKING****Tr Pulse characteristics1****Tf Pulse characteristics2**

1. Measuring conditions are as given in Supplementary Table.
2. Measure the time needed for the input pulse to rise from 10% to 90% (Tr1) and to fall from 90% to 10% (Tf1) with an active prove.
3. Measure the time needed for the output pulse to rise from 10% to 90% (Tr2) and to fall from 90% to 10% (Tf2) with an active prove.
4. Pulse characteristics Tr and Tf are calculated by the equation below:

$$Tr \text{ (nsec)} = \sqrt{(Tr2)^2 - (Tr1)^2}$$

$$Tf \text{ (nsec)} = \sqrt{(Tf2)^2 - (Tf1)^2}$$

**V14th Clamp pulse threshold voltage**

1. Measuring conditions are as given in Supplementary Table.
2. Turn down the SG5 input level gradually, monitoring the output (about 2.0 VDC). Measure the SG5 input level when the output reaches 0V.

**W14 Clamp pulse minimum width**

Under the same conditions as given in Note 19, reduce the SG5 pulse width gradually, monitoring the output. Measure the SG5 pulse width when the output reaches 0V.

**PdCH Pedestal voltage temperature characteristics1****PdCL Pedestal voltage temperature characteristics2**

1. Measuring conditions are as given in Supplementary Table.
2. Measure the pedestal voltage at room temperature.  
The measured value is called Pdc1.
3. Measure the pedestal voltage at temperatures of -20°C and 85°C. The measured value is called, respectively, Pdc2 and Pdc3.
4.  $PdCH = Pdc1 - Pdc2$   
 $PdCL = Pdc1 - Pdc3$

**OTr OSD pulse characteristics1****OTf OSD pulse characteristics2**

1. Measuring conditions are as given in Supplementary Table.
2. Measure the time needed for the the output pulse to rise from 10% to 90% (OTr) and to fall from 90% to 10% (OTf) with an active prove.

**Oaj1 OSD adjusting control characteristics (maximum)****ΔOaj1 OSD adjusting control relative characteristics (maximum)**

1. Measuring conditions are as given in Supplementary Table.
2. Measure the amplitude at T.P25 (30 or 35). The measured value is called VORA (VOGA or Voba), and is treated as Oaj1.
3. OSD adjusting control relative characteristics ΔOaj1 are calculated by the equation below:

**Oaj2 OSD adjusting control characteristics (minimum)****ΔOaj2 OSD adjusting control relative characteristics (minimum)**

1. Measuring conditions are as given in Supplementary Table, except that V36 is set to 0V.
2. Measure the amplitude at T.P25 (30 or 35). The measured value is called VORB (VOGB or VObB), and is treated as Oaj2.
3. OSD adjusting control relative characteristics ΔOaj2 are calculated by the equation below:






**OSDth OSD input threshold voltage**

1. Measuring conditions are as given in Supplementary Table.
2. Reduce the SG7 input level gradually, monitoring output.  
Measure the SG7 level when the output reaches 0V. The measured value is called OSDth.

**V1th BLK input threshold voltage**

1. Measuring conditions are as given in Supplementary Table.
2. Make sure that signals are not being output synchronously with SG7 (blanking period).
3. Reduce the SG7 input level gradually, monitoring output.  
Measure the SG7 level when the blanking period disappears.  
The measured value is called V1th.

**3-CHANNEL VIDEO AMPLIFICATION WITH OSD BLANKING****INPUT SIGNAL**


SG No.	Signals
SG1	<p>Sine wave of amplitude 0.7V<sub>P-P</sub> (f=1MHz)</p> 
SG2	Sine wave with amplitude of 0.7V <sub>P-P</sub> (f=50MHz)
SG3	Sine wave with amplitude of 0.7V <sub>P-P</sub> (f=130MHz)
SG4	<p>Pulse with amplitude of 0.7V<sub>P-P</sub> (f=1MHz, duty=50%) Pulses which are synchronous with SG4 pedestal portion</p> 
SG5	<p>Pulses which are synchronous with standard video step waveform pedestal portion: amplitude, 2.0V<sub>P-P</sub>; and pulse width, 3.0μs (pulse width and amplitude sometimes variable)</p> 
SG6 Standard video step waveform	 <p>Video signal with amplitude of 0.7V<sub>P-P</sub> (f=30kHz, amplitude sometimes variable)</p>
SG7 OSD BLK and OSD signals	 <p>Pulses which are synchronous with standard video step waveform's video portions: amplitude, 4.0V<sub>P-P</sub>; and pulse width, 25μs</p>




# M52734SP

## 3-CHANNEL VIDEO AMPLIFICATION WITH OSD BLANKING

### TEST CIRCUIT




### TYPICAL CHARACTERISTICS



# M52734SP

## 3-CHANNEL VIDEO AMPLIFICATION WITH OSD BLANKING

### APPLICATION EXAMPLE



Units Resistance :  $\Omega$   
Capacitance : F

**M52734SP****3-CHANNEL VIDEO AMPLIFICATION WITH OSD BLANKING****DESCRIPTION OF PIN**

Pin No.	Name	DC voltage (V )	Peripheral circuit of pins	Description of function
1	OSD BLK IN	—		<p>·Input pulses of minimum 3V.</p> <p>·Connected to GND if not used.</p>
2 7 12	Vcc (B-ch) Vcc (G-ch) Vcc (R-ch)	12	—	·Apply equivalent voltage to 3 channels.
3 8 13	INPUT (B) INPUT (G) INPUT (R)	2.5		<p>·Clamped to about 2.5V due to clamp pulses from pin 18.</p> <p>·Input at low impedance.</p>
4 9 14	Subcontrast (B) Subcontrast (G) Subcontrast (R)	2.5		·Use at maximum 5V for stable operation.
5 10 15	OSD IN (B) OSD IN (G) OSD IN (R)	—		<p>·Input pulses of minimum 3V.</p> <p>·Connected to GND if not used.</p>



**3-CHANNEL VIDEO AMPLIFICATION WITH OSD BLANKING**
**DESCRIPTION OF PIN** (cont.)

Pin No.	Name	DC voltage (V )	Peripheral circuit of pins	Description of function
6, 31 11, 26 16, 21	GND (B-ch) GND (G-ch) GND (R-ch)	GND	—	
17	Main contrast	2.5		·Use at maximum 5V for stable operation.
18	CP IN	—		·Input pulses of minimum 2.5V.  ·Input at low impedance.
19	Brightness	—		
20, 22, 27, 32	NC	—	—	·Connected to GND usually; otherwise kept open.
23 28 33	Hold (R) Hold (G) Hold (B)	Variable		·A capacity is needed on the GND side.

# M52734SP

## 3-CHANNEL VIDEO AMPLIFICATION WITH OSD BLANKING

### DESCRIPTION OF PIN (cont.)

Pin No.	Name	DC voltage (V )	Peripheral circuit of pins	Description of function
24 29 34	Vcc2 (R) Vcc2 (G) Vcc2 (B)	Apply 12		<ul style="list-style-type: none"> <li>Used to supply power to output emitter follower only.</li> <li>Apply equivalent voltage to 3 channels.</li> </ul>
25 30 35	OUTPUT (R) OUTPUT (G) OUTPUT (B)	Variable		<ul style="list-style-type: none"> <li>A resistor is needed on the GND side.</li> <li>Set discretionally to maximum 15mA, depending on the required driving capacity.</li> </ul>
36	OSD adjust	Apply at open 5.5V		<ul style="list-style-type: none"> <li>Pulled up directly to Vcc or open if not used.</li> </ul>