

	13	12	11	10	9	8	7	6	5	4	3	2	1											
J	1.25MM CENTER FFC JUMPER CABLE (HIGH TEMPERATURE) CHART																							J
	"A" DIM.	1.18 +/- .079 INCHES 30 +/-2.00 MM		2 +/- .079 INCHES 51+/-2.00 MM		3 +/- .118 INCHES 76+/-3.00 MM		4 +/- .118 INCHES 102+/-3.00 MM		5 +/- .157 INCHES 127+/-4.00 MM		6 +/- .157 INCHES 152+/-4.00 MM		7 +/- .157 INCHES 178+/-4.00 MM		8 +/- .157 INCHES 203+/-4.00 MM		9 +/- .197 INCHES 229+/-5.00 MM		10 +/- .197 INCHES 254+/-5.00 MM		12 +/- .197 INCHES 305+/-5.00 MM		
	STIFFENER	TYPE "A"	TYPE "D"	TYPE "A"	TYPE "D"	TYPE "A"	TYPE "D"	TYPE "A"	TYPE "D"	TYPE "A"	TYPE "D"	TYPE "A"	TYPE "D"	TYPE "A"	TYPE "D"	TYPE "A"	TYPE "D"	TYPE "A"	TYPE "D"	TYPE "A"	TYPE "D"	TYPE "A"	TYPE "D"	
I	CKTS: 4	152680701	152680700	152680703	152680702	152680705	152680704	152680707	152680706	152680709	152680708	152680711	152680710	152680713	152680712	152680715	152680714	152680717	152680716	152680719	152680718	152680721	152680720	I
	CKTS: 6	152680101	152680102	152680103	152680104	152680105	152680106	152680107	152680108	152680109	152680110	152680111	152680112	152680113	152680114	152680115	152680116	152680117	152680118	152680119	152680120	152680121	152680122	
	CKTS: 8	152680123	152680124	152680125	152680126	152680127	152680128	152680129	152680130	152680131	152680132	152680133	152680134	152680135	152680136	152680137	152680138	152680139	152680140	152680141	152680142	152680143	152680144	
	CKTS: 10	152680145	152680146	152680147	152680148	152680149	152680150	152680151	152680152	152680153	152680154	152680155	152680156	152680157	152680158	152680159	152680160	152680161	152680162	152680163	152680164	152680165	152680166	
	CKTS: 12	152680167	152680168	152680169	152680170	152680171	152680172	152680173	152680174	152680175	152680176	152680177	152680178	152680179	152680180	152680181	152680182	152680183	152680184	152680185	152680186	152680187	152680188	
	CKTS: 14	152680189	152680190	152680191	152680192	152680193	152680194	152680195	152680196	152680197	152680198	152680199	152680200	152680201	152680202	152680203	152680204	152680205	152680206	152680207	152680208	152680209	152680210	
H	CKTS: 16	152680211	152680212	152680213	152680214	152680215	152680216	152680217	152680218	152680219	152680220	152680221	152680222	152680223	152680224	152680225	152680226	152680227	152680228	152680229	152680230	152680231	152680232	
	CKTS: 18	152680233	152680234	152680235	152680236	152680237	152680238	152680239	152680240	152680241	152680242	152680243	152680244	152680245	152680246	152680247	152680248	152680249	152680250	152680251	152680252	152680253	152680254	
	CKTS: 20	152680255	152680256	152680257	152680258	152680259	152680260	152680261	152680262	152680263	152680264	152680265	152680266	152680267	152680268	152680269	152680270	152680271	152680272	152680273	152680274	152680275	152680276	
	CKTS: 22	152680277	152680278	152680279	152680280	152680281	152680282	152680283	152680284	152680285	152680286	152680287	152680288	152680289	152680290	152680291	152680292	152680293	152680294	152680295	152680296	152680297	152680298	
	CKTS: 24	152680299	152680300	152680301	152680302	152680303	152680304	152680305	152680306	152680307	152680308	152680309	152680310	152680311	152680312	152680313	152680314	152680315	152680316	152680317	152680318	152680319	152680320	
	CKTS: 26	152680321	152680322	152680323	152680324	152680325	152680326	152680327	152680328	152680329	152680330	152680331	152680332	152680333	152680334	152680335	152680336	152680337	152680338	152680339	152680340	152680341	152680342	
G	CKTS: 28	152680343	152680344	152680345	152680346	152680347	152680348	152680349	152680350	152680351	152680352	152680353	152680354	152680355	152680356	152680357	152680358	152680359	152680360	152680361	152680362	152680363	152680364	
	CKTS: 30	152680365	152680366	152680367	152680368	152680369	152680370	152680371	152680372	152680373	152680374	152680375	152680376	152680377	152680378	152680379	152680380	152680381	152680382	152680383	152680384	152680385	152680386	
	CKTS: 32	152680387	152680388	152680389	152680390	152680391	152680392	152680393	152680394	152680395	152680396	152680397	152680398	152680399	152680400	152680401	152680402	152680403	152680404	152680405	152680406	152680407	152680408	
	CKTS: 34	152680409	152680410	152680411	152680412	152680413	152680414	152680415	152680416	152680417	152680418	152680419	152680420	152680421	152680422	152680423	152680424	152680425	152680426	152680427	152680428	152680429	152680430	
	CKTS: 36	152680431	152680432	152680433	152680434	152680435	152680436	152680437	152680438	152680439	152680440	152680441	152680442	152680443	152680444	152680445	152680446	152680447	152680448	152680449	152680450	152680451	152680452	
	CKTS: 38	152680453	152680454	152680455	152680456	152680457	152680458	152680459	152680460	152680461	152680462	152680463	152680464	152680465	152680466	152680467	152680468	152680469	152680470	152680471	152680472	152680473	152680474	
	CKTS: 40	152680475	152680476	152680477	152680478	152680479	152680480	152680481	152680482	152680483	152680484	152680485	152680486	152680487	152680488	152680489	152680490	152680491	152680492	152680493	152680494	152680495	152680496	
F																								F
E																								E
D																								D
C																								C
B																								B
A																								A
	13	12	11	10	9	8	7	6	5	4	3	2	1											

NOTES:
1. NO PRINTING ON JUMPER CABLE UNLESS OTHERWISE SPECIFIED. IF PRINTING IS REQUIRED, THEN IT WOULD BE CONSIDERED A SPECIAL JUMPER CABLE.

SHOW CONTINEUOUS
INSULATION FOR TAILS

EC NO: USW2014-0256
DRWN: MFI 2014/05/07

DESCRIPTION

REV

QUALITY
SYMBOL

▽=0

▽C=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

mm

INCH

4 PLACES ±--- ±---

3 PLACES ±--- ±---

2 PLACES ±--- ±---

1 PLACE ±--- ±---

ANGULAR ±1/2°

DRAFT WHERE
APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM

DRAWN BY

DATE

CHECKED BY

DATE

APPROVED BY

DATE

DRASMUSS 2010/11/17

MATERIAL NO.

SEE CHART

SIZE

C

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SCALE

DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION

1.25MM CENTER
FFC JUMPER CABLE

Molex

MOLEX INCORPORATED

DOCUMENT NO.

SD-15268-001

SHEET NO.

1 OF 2

NOTES:

1. NO PRINTING ON JUMPER CABLE UNLESS OTHERWISE SPECIFIED. IF PRINTING IS REQUIRED, THEN IT WOULD BE CONSIDERED A SPECIAL JUMPER CABLE.

SHOW CONTINEUOUS
INSULATION FOR TAILS

EC NO: USW2014-0256
DRWN: MFI 2014/05/07

DESCRIPTION

REV

3

QUALITY
SYMBOL

▽=0

▽C=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

mm

INCH

4 PLACES ±--- ±---

3 PLACES ±--- ±---

2 PLACES ±--- ±---

1 PLACE ±--- ±---

ANGULAR ±1/2°

DRAFT WHERE
APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE

MM

DRAWN BY

DATE

CHECKED BY

DATE

APPROVED BY

DATE

DRASMUSS 2010/11/17

MATERIAL NO.

SEE CHART

SIZE

C

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SCALE

DESIGN UNITS

METRIC

THIRD ANGLE
PROJECTION

1.25MM CENTER
FFC JUMPER CABLE

Molex

MOLEX INCORPORATED

DOCUMENT NO.

SD-15268-001

SHEET NO.

1 OF 2

