

### Self-Laminating Fiber Optic Cable Marker Tags



Material Chart

| Material                        | Print Method | Temperature Range               | Features                                                                                                                                        |
|---------------------------------|--------------|---------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|
| Rigid Vinyl,<br>Self-Laminating | Pre-Printed  | 0°F to 176°F<br>(-18°C to 80°C) | Indoor/outdoor rated; high quality, rugged material resistant to abrasion; legend is protected by overlamine; use where adhesives will not work |

| Part Number | Legend                                                 | Color<br>(Legend/Background) | Width |      | Height |      | Tags<br>Per<br>Pkg. | Std.<br>Pkg.<br>Qty. | Std.<br>Ctn.<br>Qty. |
|-------------|--------------------------------------------------------|------------------------------|-------|------|--------|------|---------------------|----------------------|----------------------|
|             |                                                        |                              | In.   | mm   | In.    | mm   |                     |                      |                      |
| PST-FO      | CAUTION FIBER OPTIC<br>CABLE TYPE _____<br>COUNT _____ | Black/Yellow                 | 3.50  | 89.0 | 2.00   | 51.0 | 5                   | 1                    | 40                   |
| PST-FOBLNK  | BLANK                                                  | Yellow                       | 3.50  | 89.0 | 2.00   | 51.0 | 5                   | 1                    | 40                   |

### Photoluminescent Safety Signs

- Used to mark egress routes, fire alarms, and fire equipment that is clearly visible for up to ten hours after power is lost
- Absorbs energy from ambient light and releases this energy in the form of a glow when power is lost
- Recommended for use with Photoluminescent Tapes see page O.27 for more information
- Panduit Photoluminescent Signs meet or exceed the following safety standard specification for photoluminescent safety markings including: ASTM E 2072-00, ASTM E 2073-00, ASTM E 2030-99, DIN67510-1, IMO Resolution A.752.18, ISO/CD 15370, DIN 67510, UL 924, ASTM 162, ASTM 648, ASTM 662, MIL-L-3891 B, NFPA 101 Life Safety Code, OSHA 1910.37



PPS0710G001  
PPS1014G002



PPS0710G020



PPS1209G010



PPS1209G011



PPS1209G012

Size Reference Chart

| Part Number | Width |       | Height |       | Signs Per Card | Std. Pkg. Qty. |
|-------------|-------|-------|--------|-------|----------------|----------------|
|             | In.   | mm    | In.    | mm    |                |                |
| *0710*      | 10.00 | 254.0 | 7.00   | 177.8 | 1              | 1 Sign         |
| *1014*      | 14.00 | 355.6 | 10.00  | 254.0 | 1              | 1 Sign         |
| *1209*      | 9.00  | 228.6 | 12.00  | 304.8 | 1              | 1 Sign         |

\*Denotes the part number's prefix and suffix.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PPS0710G001](#) [PPS0710G020](#) [PPS1209G012](#) [PPS1209G010](#) [PPS1014G002](#) [PPS1209G011](#)