

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0310681012](#)
Status: **Active**
Overview: H-DAC 64™ Unsealed Connector System
Description: 2.54mm H-DAC 64™, 4 Way Receptacle Assembly, Single Row, Polarization C



Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-31100-0001-001 \(PDF\)](#)
[Application Specification AS-31067-100-001 \(PDF\)](#)
[Packaging Specification PK-30907-737 \(PDF\)](#)
[Packaging Specification PK-31301-076 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Crimp Housings
Series [31068](#)
Application Power, Wire-to-Board
Comments Polarization Option C, Brown
Overview [H-DAC 64™ Unsealed Connector System](#)
Product Name H-DAC 64™
UPC 756054393130

Physical
Circuits (maximum) 4
Circuits Detail 4
Color - Resin Brown (Carmel), White
Gender Receptacle
Glow-Wire Compliant No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin Modified Polystyrene, Polyester
Net Weight 1.385/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Polarized to Mating Part Yes
Ports 1
Stackable No
Temperature Range - Operating -40°C to +100°C

Electrical
Current - Maximum per Contact 11.0A, 9.0A

Solder Process Data
Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers
Application Specification AS-31067-100-001
Packaging Specification PK-30907-737, PK-31301-076
Product Specification PS-31100-0001-001
Sales Drawing SD-31109-003

EU ELV
Compliant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Contained Per -
ED/30/2017 (7 July
2017)
Boric acid
Halogen-Free
Status
Not Relevant

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[31068](#) Series

Mates With
HDAC 64™, 4 Way Male Housing Assembly
[31068-1042](#) , [31068-1072](#) , [31100-0042](#) ,
[31101-0042](#)

Use With
See Product Specification