






SYMBOL DEFINITION			MISSING SYMBOLS							ZONE	REVISION HISTORY			AUTH	DR	APPROV			
			DWG STATUS																
			DATE	STG	REV	N/P	CHG												
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.			TOTAL NO OF INSPECTIONS REQUIRED	16	NO MISSING SYMBOL NUMBER							CLEARED REV COL. REDRAWN TO PD AND MAT'L SPEC WAS R0100233			268583	CCV	JAA	MB	
			LAST NO. USED	14															



OPTIONAL CONSTRUCTION
4X CORE SUPPORT SLOT MAY BE REMOVED




NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. MATERIAL RECYCLING CODE PER ISO 11469, (11)X(0.1) CHARACTERS
AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
3. THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:

CAVITIES TO ACCEPT TERMINAL 12084912
CONNECTOR/CABLE SEAL 12129229
TERMINAL POSITION ASSURANCE LOCK 12129231
STRAIN RELIEF 12129233
4. THIS PART ALSO USED WITH CPA 12110299, CAVITY PLUG(S) 12129557.
NOTE: THERE IS NO MATING HEADER CONNECTOR ASSEMBLY FOR THIS PART.
5. (11)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY
EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.
OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED".

7 PROCESS SENSITIVE DIMENSION										REFERENCE										DRAWING NAME CONN 32 F MIC/P 100W NAT SLD									
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED																													
DIMENSIONAL RANGE (MM)										THIRD ANGLE PROJECTION										DO NOT SCALE									
FROM TO >20 >30 >70 >100 >150 >250 >350 >500																													
0 20 100 150 250 350 500																													
TOLERANCE UNLESS OTHERWISE SPECIFIED																													
± 0.15 ± 0.2 ± 0.4 ± 0.5 ± 0.6 ± 0.8 ± 1 ± 1.2																				12129228									
ANGULAR TOLERANCE 12°																				USE MATH DATA									
SIZE A0										SCALE 2:1										FRAME 1 OF 1									
																				SHEET 1 OF 1									
																				REV R									
																				J6 N/P									

DRG TYPE PART DRAWING	
STYLE 4.196	DISTR CODE 
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 DIMENSIONAL PRACTICES AND TOLERANCES OF MECHANICAL PARTS TELEPHONE: (800) 541-3931, SEPARATE PATTERN OF THIS DRAWING IS AVAILABLE FOR PURCHASE AT \$10.00 PER SET	

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
	DATE
DR	
APVD1 BRIAN MADISON	11JL91
APVD2 BRIAN MADISON	18JL91
APVD3 R. POLEHONK1	05AU91
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL: M4695001 PBT NAT	
DRAWING NAME	
CONN 32 F M/C/P 100W NAT SLD	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delphi Connection Systems:](#)

[12129228-B](#)