


**Part Number: 94529-9103**

5.00mm Pitch RAST, Receptacle, Natural Color, PA Polyamide (Nylon) 6/6, 3 Circuits



Series image - Reference only

Status:	OBsolete
Replacement:	Contact Molex
Series:	94529
Category:	Crimp Housings

Mates With Part(s):
PCB thickness 1.50mm**Use With:**
[945291203](#) Terminal**Product Environmental Compliance****EU RoHS:** ELV and RoHS Compliant**China RoHS:** **REACH SVHC:** Not Reviewed**Low-Halogen Status:** Not Reviewed**Part Detail****General**

Status	Obsolete
Category	Crimp Housings
Series	94529
Application	Power
Product Name	Pitch 5 Edge Card

Physical

Breakaway	No
Circuits (maximum)	3
Color - Resin	Natural
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.00mm
Pitch - Termination Interface	5.00mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40°C to +105°C, -40°C to +85°C

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact 6A

Material Info

UPC 756054155752

Reference - Drawing NumbersProduct Specification PS-94529-001, PS-94529-002
Sales Drawing SD-94529-026**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application**Tooling**[Check our list of old tooling that used to be available for this part](#)

