


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P2	REVISED PER ECO-11-004820	11MAR11	RK	HMR
	R	REVISED PER ECR-16-017870	20APR2017	BDA	MZ

D

C

B

A



DETAIL B

DETAIL A

RECOMMENDED PANEL CUTOUT

- WILL ACCEPT (20) MULTIMATE AND 2 TYPE XII PIN CONTACTS.
- CAVITY IDENTIFICATION ON FRONT AND REAR FACE.

△ NUMBER 4 FASTENERS RECOMMENDED FOR MOUNTING.

△ HOUSING: NYLON, BLACK.
PERIPHERAL SEAL: ELASTOMER, GRAY.

△ APPLIES TO 206613-6 ONLY.

△ PERMANENT WHITE MARKED OR WHITE INK STAMPED CAVITY IDENTIFICATION.

△ HOUSING: NYLON, RED.
PERIPHERAL SEAL: ELASTOMER, GRAY.

△ WHITE DOT NEAR POSITION 1 ON WIRE ENTRY FACE.

OBSOLETE	△△	—	YES	A	1-206613-2
OBSOLETE	△	—	YES	A	206613-9
PRELIMINARY	△△	—	YES	A	206613-7
OBSOLETE	△	4	NO	A	206613-6
	△	—	YES	A	206613-5
	△	—	NO	B	206613-3
	△	—	NO	A	206613-1
NOTES		THREADED INSERTS	PERIPHERAL SEAL	SEE DETAIL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. BINNER 05/26/94	TE Connectivity		
DIMENSIONS: INCHES		CHK R. STONE 6-23-94			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —	NAME		
0 PLC ± — 1 PLC ± — 2 PLC ± 0.13 [.005] 3 PLC ± — 4 PLC ± — ANGLES ± —		PRODUCT SPEC 108-10024	RECEPTACLE HOUSING, STANDARD SEX, SHELL SIZE 23, CPC		
MATERIAL		APPLICATION SPEC —			
FINISH —		WEIGHT —	RESTRICTED TO		
CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1 REV		