


International

IR Rectifier

SCHOTTKY RECTIFIER

MBRS340TR

3 Amp




Major Ratings and Characteristics

Characteristics	Value	Units
$I_{F(AV)}$ Rectangular waveform	3.0	A
V_{RRM}	40	V
I_{FSM} @ $t_p=5\mu s$ sine	1580	A
V_F @ 3.0Apk, $T_J=125^\circ C$	0.43	V
T_J range	- 55 to 150	°C

Description/ Features

The MBRS340TR surface-mount Schottky rectifier has been designed for applications requiring low forward drop and small foot prints on PC boards. Typical applications are in disk drives, switching power supplies, converters, free-wheeling diodes, battery charging, and reverse battery protection.

- Small foot print, surface mountable
- Very low forward voltage drop
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability



Voltage Ratings

Part number	MBRS340TR
V_R Max. DC Reverse Voltage (V)	40
V_{RWM} Max. Working Peak Reverse Voltage (V)	

Absolute Maximum Ratings

Parameters		Value	Units	Conditions		
$I_{F(AV)}$	Max. Average Forward Current	3.0	A	50% duty cycle @ $T_L = 118^\circ\text{C}$, rectangular waveform		
		4.0		50% duty cycle @ $T_L = 110^\circ\text{C}$, rectangular waveform		
I_{FSM}	Max. Peak One Cycle Non-Repetitive	1580	A	5μs Sine or 3μs Rect. pulse	Following any rated load condition and with rated V_{RRM} applied	
	Surge Current	80		10ms Sine or 6ms Rect. pulse		
E_{AS}	Non Repetitive Avalanche Energy	6	mJ	$T_J = 25^\circ\text{C}$, $I_{AS} = 1.0\text{A}$, $L = 12\text{mH}$		
I_{AR}	Repetitive Avalanche Current	1.0	A	Current decaying linearly to zero in 1 μsec Frequency limited by T_J max. $V_a = 1.5 \times V_r$ typical		

Electrical Specifications

Parameters		Value	Units	Conditions
V_{FM}	Max. Forward Voltage Drop (1)	0.525	V	@ 3A
		0.68	V	@ 6A
		0.43	V	@ 3A
		0.57	V	@ 6A
I_{RM}	Max. Reverse Leakage Current	2.0	mA	$T_J = 25^\circ C$
		20	mA	$T_J = 100^\circ C$
		35	mA	$T_J = 125^\circ C$
				$V_R = \text{rated } V_R$
C_T	Max. Junction Capacitance	230	pF	$V_R = 5V_{DC}$ (test signal range 100KHz to 1Mhz) $25^\circ C$
L_S	Typical Series Inductance	3.0	nH	Measured lead to lead 5mm from package body
dv/dt	Max. Voltage Rate of Change	10000	V/μs	(Rated V_R)

(1) Pulse Width < 300 μ s. Duty Cycle < 2%

Thermal-Mechanical Specifications

Parameters		Value	Units	Conditions
T_J	Max. Junction Temperature Range (*)	-55 to 150	°C	
T_{stg}	Max. Storage Temperature Range	-55 to 150	°C	
R_{thJL}	Max. Thermal Resistance Junction to Lead (**)	12	°C/W	DCoperation
R_{thJA}	Max. Thermal Resistance Junction to Ambient	46	°C/W	DCoperation
wt	Approximate Weight	0.24(0.008)	g(oz.)	
Case Style		SMC		Similar to DO-214AB
Device Marking		IR34		

(*) $\frac{dP_{tot}}{dT_j} < \frac{1}{R_{th(j-a)}}$ thermal runaway condition for a diode on its own heatsink

(**) Mounted 1 inch square PCB




Fig. 1 - Max. Forward Voltage Drop Characteristics (PerLeg)




Fig. 2 - Typical Values Of Reverse Current Vs. Reverse Voltage (PerLeg)




Fig. 3 - Typical Junction Capacitance Vs. Reverse Voltage (PerLeg)




Fig. 4 - Max. Thermal Impedance Z_{thJC} Characteristics (Per Leg)




Fig. 4 - Maximum Average Forward Current Vs. Allowable Lead Temperature




Fig. 5 - Maximum Average Forward Dissipation Vs. Average Forward Current





Fig. 6 - Maximum Peak Surge Forward Current Vs. Pulse Duration


- (2) Formula used: $T_c = T_j - (P_d + P_{d_{REV}}) \times R_{thJC}$;
 $P_d = \text{Forward Power Loss} = I_{F(AV)} \times V_{FM} @ (I_{F(AV)} / D)$ (see Fig. 6);
 $P_{d_{REV}} = \text{Inverse Power Loss} = V_{R1} \times I_R (1 - D)$; $I_R @ V_{R1} = 80\% \text{ rated } V_R$

Tape & Reel Information



Marking & Identification

Each device has 2 rows for identification. The first row designates the device as manufactured by International Rectifier as indicated by the letters "IR", and the Part Number (indicates the current and the voltage rating). The second row indicates the year, the week of manufacturing and the Site ID.



Ordering Information

MBRS340TR - TAPE AND REEL

WHEN ORDERING, INDICATE THE PART NUMBER AND THE QUANTITY (IN MULTIPLES OF 3000 PIECES).

EXAMPLE: MBRS340TR - 6000 PIECES

MBRS340TR

Bulletin PD-20585 rev. D 03/03

International
IR Rectifier

Data and specifications subject to change without notice.
This product has been designed and qualified for Industrial Level.
Qualification Standards can be found on IR's Web site.

International
IR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
TAC Fax: (310) 252-7309
Visit us at www.irf.com for sales contact information. 03/03