



Micro Commercial Components



Micro Commercial Components
20736 Marilla Street Chatsworth
CA 91311
Phone: (818) 701-4933
Fax: (818) 701-4939

BC847AT, BT, CT

Features

- Halogen free available upon request by adding suffix "-HF"
- Lead Free Finish/RoHS Compliant ("P" Suffix designates RoHS Compliant. See ordering information)
- Epitaxial Die Construction
- Complementary PNP Type Available (BC857AT,BT,CT)
- Ultra-Small Surface Mount Package
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1

Maximum Data

- Case: SOT-523
- Terminals: Solderable per MIL-STD-202, Method 208
- Polarity: See Diagram
- Marking: BC847AT--1E, BC847BT--1F, BC847CT-1G.


Maximum Ratings @ 25°C Unless Otherwise Specified

Symbol	Parameter	Value	Units
OFF CHARACTERISTICS			
$V_{(BR)CEO}$	Collector-Emitter Breakdown Voltage	45	Vdc
$V_{(BR)CBO}$	Collector-Base Breakdown Voltage	50	Vdc
$V_{(BR)EBO}$	Collector-Emitter Breakdown Voltage	6.0	Vdc
I_C	Collector Current	100	mA dc
P_d	Power Dissipation (Note 1)	150	mW
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient (Note 1)	833	°C/W
T_J, T_{STG}	Operating & Storage Temperature	-55~+150	°C

Note: 1. Device mounted on FR-4 PCB with recommended pad layout

NPN Surface Mount Small Signal Transistor 150mW

SOT-523



DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	.059	.067	1.50	1.70	
B	.030	.033	0.75	0.85	
C	.057	.069	1.45	1.75	
D	.020 Nominal		0.50 Nominal		
E	.035	.043	0.90	1.10	
G	.000	.004	.000	.100	
H	.028	.031	.70	0.80	
J	.004	.008	.100	.200	
K	.010	.014	.25	.35	

Electrical Characteristics @ 25°C Unless Otherwise Specified

Symbol	Parameter	Min	Typ	Max	Units	Test Condition
OFF CHARACTERISTICS						
h_{FE}	DC Current Gain (Note 2) Current Gain A B C	110 200 420	--- 290 520	222 450 800	---	$V_{CE}=5.0V, I_C=2.0mA$
$V_{CE(SAT)}$	Collector-Emitter Saturation Voltage (Note 2)	---	---	250 600	mV	$I_C=10mA, I_B=0.5mA$ $I_C=100mA, I_B=5.0mA$
$V_{BE(SAT)}$	Base-Emitter Saturation Voltage (Note 2)	---	700 900	---	mV	$I_C=10mA, I_B=0.5mA$ $I_C=100mA, I_B=5.0mA$
$V_{BE(ON)}$	Base-Emitter Voltage (Note 2)	580 ---	660 ---	700 770	mV	$V_{CE}=5.0V, I_C=2.0mA$ $V_{CE}=5.0V, I_C=10mA$
I_{CBO} I_{CBO}	Collector-Cutoff Current (Note 2)	---	---	15 5.0	nA μA	$V_{CB}=30V, I_E=0$ $V_{CB}=30V, T_J=125^\circ C$
f_T	Gain Bandwidth Product	100	---	---	MHz	$V_{CE}=5.0V, I_C=10mA, f=100MHz$
C_{CBO}	Collector-Base Capacitance	---	---	4.5	pF	$V_{CB}=10V, f=1.0MHz$
NF	Noise Figure BC847BT BC847CT	---	---	10 4.0	dB	$V_{CE}=5V, R_S=2.0Kohm, f=1.0MHz, BW=200HZ$

Note: 2. Short duration pulse test used to minimize self-heating effect.

Ordering Information :

Device	Packing
Part Number-TP	Tape&Reel; 3Kpcs/Reel

Note : Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Micro Commercial Components \(MCC\):](#)

[BC847BT-T](#) [BC847AT-T](#) [BC847CT-T](#)