

Data sheet



Item no.:	784-601
Product description:	2-CONDUCTOR THROUGH TERMINAL BLOCK; CENTRE MARKING; CARRIER RAIL DIN 35; TOPJOB®-ENTRY; CAGE CLAMP®CONNECTION



Packing unit 25 pieces

Cross section from [mm²]	0,2 mm²
Cross section to [mm²]	10 mm²
Cross section from [AWG]	24 AWG
Cross section to [AWG]	08 AWG
Connection method	CAGE CLAMP®CONNECTION
Voltage CSA	600 V
Voltage UL	600 V
Current UL	50 A
Current CSA	35 A
Cross section from [mm²]	0,2 mm²
Cross section to [mm²]	16 mm²
Cross section from [AWG]	24 AWG
Cross section to [AWG]	06 AWG
Measured voltage EN	1000 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	57 A
Weight	23,22 g
Color	grey
Wiring type	topJob®
No. of connection Points	2
No. of potentials	1
Height	43,5 mm
Height	1,71 in
Width	10 mm
Width	0,394 in
Depth	82,5 mm
Depth	3,25 in
Strip length from	12 mm
Strip length to	13 mm
Strip length	0,49 in

Specifications are subject to changes and errors may be expected