

10

9

8

7

6




5

4

3

2

39170



NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. MATES WITH: 50 POSITION MALE D-SUB
4. END CAP MOUNT SCREW TORQUE: 0.5 N-m (4.4 lbf-in) MINIMUM
0.6 N-m (5.3 lbf-in) MAXIMUM
5. TERMINAL BLOCK SCREW TORQUE: 0.8 N-m (7.1 lbf-in)
6. ASSEMBLY ROHS COMPLIANCE NOT REQUIRED.

TYPICAL SCHEMATIC

SEE NOTE 5

2

SEE NOTE 4

74.0
2.91

ADD SCREW TORQUE	EC NO: ETC2007-0331	2007/03/12	2007/03/14	2007/03/15
DRWN: CLYORK	CHKD: JMACNEIL	APPR: JMACNEIL	REV	DESCRIPTION
B				

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±.005
2 PLACES	±0.13	±.01
1 PLACE	±0.3	±---
ANGULAR ± 2 °		

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

3	2	DIN RAIL ADAPTOR UNIT	THERMOPLASTIC	BLACK
2	1	FEMALE D-SUB TO 5.08 HEADER, PC BOARD ASSY.	-	-
1	4	5.08 PLUGGABLE BTS, 13 POSITION	SEE SD-39860-004	BLACK
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

DIMENSION STYLE	
MM/IN	
DRAWN BY	DATE
C. YORK	2004/11/12
CHECKED BY	DATE
R. STONE	2004/11/16
APPROVED BY	DATE
G. ROBERTSON	2004/11/16

SCALE
1:1DESIGN UNITS
INCHTHIRD ANGLE
PROJECTIONTITLE
DIN RAIL INTERFACE MOD,
50 POSITION FEMALE D-SUB
TO 5.08MM VERT EURO PLUG

moLEX MOLEX INCORPORATED

DOCUMENT NO.

SHEET NO.

39170-3150 SD-39170-007 1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION