






P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O. PI6753	21JULY2000	-	RDR
	B	REVISED PER PCN-24-226269	10JAN2025	AJT	MB




4. MATERIAL: CONNECTOR: PA66 GF15, GRAY
CAP: PA66 GF15, BLACK
WEDGE LOCK (INCLUDED): PBT GF30 (GREEN)
PINS: COPPER ALLOY, NICKEL PLATED

3. THE 6 PIN BUSBAR HAS A MAXIMUM CURRENT RATING OF 39 AMPS.

2. ORIENTATION OF "DEUTSCH" AND "-P021" TO BE OPTIONAL.

1. MATES WITH DT06-6S-XXXX (XXXX = ALL MODIFICATIONS).
CONSULT FACTORY FOR MODIFICATIONS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. YOHANNES CHK - APVD - PRODUCT SPEC 108-151009 APPLICATION SPEC 114-1510009 WEIGHT 14 g		06 JULY 2000 11 JULY 2000 21 JULY 2000		 TE Connectivity	
DIMENSIONS: INCHES[mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME DT 6 WAY RECEPTACLE 6 PIN BUSBAR NICKEL PLATED COLOR: GRAY			
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		SIZE A3			
MATERIAL 		FINISH -		CAGE CODE 00779		DRAWING NO C-DT04-6P-P021	
CUSTOMER DRAWING				SCALE 2:1		SHEET 1 OF 1	
				RESTRICTED TO -		REV B	