

PK SERIES


85°C Standard

◆FEATURES

- Load life : 85°C 2000 hours.
- RoHS compliance.

◆SPECIFICATIONS

Items	Characteristics	
Category Temperature Range	-40~+85°C	-25~+85°C
Rated Voltage Range	6.3~400V.DC	450V.DC
Capacitance Tolerance	±20%(20°C, 120Hz)	
Leakage Current(MAX)	6.3~100V.DC	160~450V.DC
	I=0.01CV or 3μA whichever is greater. (After 2 minutes application of rated voltage)	CV≤1000
		I=0.1CV+40μA (1minute) I=0.03CV+15μA (5minutes)
		CV>1000
Dissipation Factor(MAX) (tanδ)	I=Leakage Current(μA) C=Capacitance(μF) V=Rated Voltage(V)	
	Rated Voltage (V)	6.3 10 16 25 35 50 63 100 160 200 250 350 400 450 (20°C, 120Hz)
	tanδ	0.28 0.24 0.20 0.16 0.14 0.12 0.10 0.10 0.20 0.20 0.20 0.25 0.25 0.25
When capacitance is over 1000μF, tanδ shall be added 0.02 to the listed value with increase of every 1000μF.		
Endurance	After applying rated voltage with rated ripple current for 2000 hours at 85°C, the capacitors shall meet the following requirements.	
	Capacitance Change	Within ±25% of the initial value.
	Dissipation Factor	Not more than 200% of the specified value.
	Leakage Current	Not more than the specified value.
Low Temperature Stability Impedance Ratio(MAX)	Rated Voltage (V)	6.3 10 16 25 35 50 63 100 160 200 250 350 400 450 (120Hz)
	Z(-25°C)/Z(20°C)	5 4 3 2 2 2 2 2 3 3 4 5 5 7
	Z(-40°C)/Z(20°C)	12 10 8 5 4 3 3 3 4 4 8 8 10 -




◆MULTIPLIER FOR RIPPLE CURRENT

Frequency(Hz)		60(50)	120	500	1k	10k≤
Coefficient	0.47~1μF	0.50	1.00	1.20	1.30	1.50
	2.2~4.7μF	0.65	1.00	1.20	1.30	1.50
	10~47μF	0.80	1.00	1.20	1.30	1.50
	100~1000μF	0.80	1.00	1.10	1.15	1.20
	2200~33000μF	0.80	1.00	1.05	1.10	1.15

◆DIMENSIONS

(mm)



◆OPTION

	Code
PET Sleeve	EFC

◆PART NUMBER

□□□ PK □□□□□ M □□□ □□ D×L
 Rated Voltage Series Capacitance Capacitance Tolerance Option Lead Forming Case Size

◆ **STANDARD SIZE**

Size $\phi D \times L$ (mm), Ripple Current (mA r.m.s./85°C, 120Hz)[illegible][illegible]