

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDF-Pre-Terminat ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips 

Text Search: 'F66D2-NM10Y'

Your search criteria matched only one product, shown below

F66D2-NM10Y



Fan-Out Cords – Multimode 62.5/125µm (OM1)

- Pass all TIA/EIA-568-B.3 performance requirements
- Insertion loss per connection: 0.10dB typical; 0.30dB maximum
- Pigtalled (open) end allows quick high performance field fusion splice during installation to provide the lowest installed cost
- 900µm tight-buffered fibers break out to terminated colored buffers for quick and easy identification of separate channels for accurate installations
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode fan-out cord
- Lifetime traceability of test data to a Q.C. number on each fan-out cord
- Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber

▪ Part Number	F66D2-NM10Y
▪ RoHS Compliance Status	Compliant
▪ Note	F66D2-NM10Y replaces F66D2-NM10
▪ Part Description	ST to pigtail 6-fiber fan-out cord (six ST connectors on one end and open on the other end on distribution cable) – 62.5/125µm.
▪ Product Type	Fan-Out Cords
▪ Length (m)	10
▪ Fiber Compatibility	62.5/125µm
▪ Fiber Type	Multimode
▪ Cable Color	Orange
▪ Cable Type	Duplex
▪ CE Compliant	No
▪ Connector 1 Type	ST Connector
▪ Connector 2 Type	Pigtail
▪ End Configurations	ST to Pigtail
▪ Fiber Count	6
▪ Flammability Rating	Riser (OFNR)
▪ Pricing Description	PC 6-Fiber mm 6 ST-MTP* 62.5µm 10m
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.