


SPECIFICATIONS

Model Number: MX2B1
Part Number: 028420

April 20, 2006



Mechanical Drawing:



Motor:

Nominal Voltage	= 115 VAC
Frequency	= 50 / 60 Hz
Nominal Running Current	= 0.20 / 0.18 amps
Locked Rotor Current	= 0.26 / 0.24 amps
Running Power	= 17 / 15 Watts
Average Speed	= 2700 / 3100 RPM
Bearings	= Ball
Air Flow	= 92 / 108 CFM
Acoustic	= 44.8 / 48.7 dBA

Construction:

Venturi: Zinc Alloy, Black.
 Propeller: Plastic, Black, UL 94V-0

Life Expectancy:

This fan is designed for continuous duty life of 83,000 hours at 40°C.

Additional Features:

Shaded Pole Induction Motor	
Impedance Protected	
Insulation System:	UL recognized Class B
Feathered Edge Propeller	
Operating Temperature:	-28°C to 70°C
Storage Temperature:	-40°C to 85°C

Termination:

0.120" Wide Terminals

Agency Approvals:

UL, CSA, VDE, CE