

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL INTERNATIONAL RIGHTS RESERVED.

© COPYRIGHT — BY TYCO ELECTRONICS CORPORATION.

	LOC
--	-----

	DIST
--	------

REVISIONS

BD

0

	F
--	---

LTR

DESCRIPTION

DATE _____

	DWN
--	-----

	APVD
--	------


LM

REVISÉD PER EC0-09-012344

22MAY09

9 | HMR

RMS



(2) #5-20 SELF-TAPPING SCREWS,
 SOLID OR SLOTTED SHANK.
 MATERIAL: 
 LENGTH: .50⁺⁰⁰_{-.05}

.850±.025 DIA

$$-1.000 \pm .010$$
$$1.450 \pm .030$$

CLAMPING AREA SHADED 2/3

1 PARTS PACKAGED UNASSEMBLED.

2 CABLE CLAMPING AREA ADJUSTABLE FROM .010 TO .161 SQ IN
BY REVERSING CLAMPING INSERTS.
(2 INSERTS SUPPLIED, -1 AND -2 ONLY)


 CABLE CLAMPING AREA ADJUSTABLE FROM .010 TO .161 SQ IN
BY CHANGING CLAMPING INSERTS. (4 INSERTS SUPPLIED, -3 ONLY)

4 .453 MAXIMUM CABLE OUTSIDE DIAMETER.

 BULK PACKAGED KITS TO BE ORDERED IN MULTIPLES OF 200 ONLY.

6 STEEL, ZINC PLATE WITH NON-HEXAVALENT CHROMATE.

	6	5	BULK	206358-6
	6		INDIVIDUAL	206358-5
	6		INDIVIDUAL	206358-4
OBSOLETE		5	BULK	206358-3
	6	5	BULK	206358-2
	6		INDIVIDUAL	206358-1
			PACKAGING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A GRAFF		4/23/91		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK W.G.LENKER		7-23-92	
		APVD —		—		NAME	
		PRODUCT SPEC		108-10024		CABLE CLAMP KIT, LARGE, SHELL SIZE 11, CPC	
		APPLICATION SPEC		—			
		—		—			
MATERIAL THERMOPLASTIC		FINISH —		WEIGHT —		SIZE A3	
						CAGE CODE 00779	
						DRAWING NO C-206358	
						RESTRICTED TO	
						—	
				CUSTOMER DRAWING		SCALE NTS	
						SHEET 1 OF 1	
						REV M	