





PRODUCT NO.
10041195-001LF
10041195-001




NOTE1. COPLANARITY BETWEEN TERMINAL AND HOLD DOWN
OF SHELL SHOULD BE 0.08mm MAX.
2. TERMINALS No.1 AND No.32 ARE APPROPRIATE FOR GROUND CONTACTS.

REVISIONS				
REV	DESCRIPTION	ECN	BY	DATE
A	RELEASED	J05-0016	M.H.	1/14/06
B	RELEASED	T05-0184	S.L.H	08/17/05
C	REVISED	T05-0299	S.L.H	12/28/05
D	REVISED	T06-0090	A.C	5/05/06
E	REVISED	T06-0002	A.C	5/22/06
F	REVISED	T07-1112	A.C	7/09/07
G	REVISED	T07-1135	A.C	10/12/07
H	REVISED	T08-1129	S.L.H	07/07/08



NO.	DESCRIPTION	Quantity (pcs)	Material	FINISH	REMARKS
1	Signal Contact	30	COPPER ALLOY	CONTACT AREA : Au 0.2um (8u")MIN. OVER IN 1.5um (60u")MIN.	SOLDER AREA : Au FLASH. OVER IN 1.5um (60u")MIN.
2	Ground Contact	1	COPPER ALLOY	Sn 2.0um (80u")MIN. OVER IN 1.27um (50u")MIN.	_____
3	Insulator	1	HEAT RESISTING PLASTIC	_____	UL94 V-0
4	Shell	1	STAINLESS STEEL	Sn 2.0um (80u")MIN. OVER IN 1.27um (50u")MIN.	_____

3. THE PRODUCT MEETS THE EUROPEAN UNION DIRECTIVE AS DESCRIBED IN GS-22-008.
4. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C. PEAK TEMPERATURE FOR 5 SECONDS IN A CONVECTION, IR OR VAPOR PHASE RETLOW OVEN
5. SPEC : PRODUCT SPEC: GS-12-293
PACKING SPEC: GS-14-988




APPLICABLE P.C.B. DIMENSION(REF.)



SHEET INDEX	ISSUE	H	H	H															
	SH NO.	1	2	3															
TOLERANCES UNLESS OTHERWISE SPECIFIED				MAT				DR				DATE				CUSTOMER			
				SEE NOTE				Sterling Lin				12/28/05				COPY			
.				±0.8				ENGR				12/28/05							
LINEAR				.X ±0.4				CHK				12/28/05							
ANGLES				.XX ±0.1				SEE NOTE				12/28/05							
								H C Liou				12/28/05							
								APPD				12/28/05							
								H C Liou				12/28/05							

TITLE		Standard Locking Type LND5	
Board Connector for LCD (On Type)		Panels	
PRODUCT FAMILY		CODE	
		JP	
SCALE	SIZE	DWG. NO.	REV
2/1	B	10041195	G
			SHEET
			1 of 3

PRODUCT NO.				REVISIONS			
10041195-002				REV	DESCRIPTION	ECN	BY DATE
				G	REVISED	T07-1155	A.C. 10/12/07
				H	REVISED	T08-1129	S.LIN 07/07/08




NOTE1: COPLANARITY BETWEEN TERMINAL AND HOLD DOWN OF SHELL SHOULD BE 0.08mm MAX.
2. TERMINALS No.1 AND No.32 ARE APPROPRIATE FOR GROUND CONTACTS.



3. THE PRODUCT MEETS THE EUROPEAN UNION DIRECTIVE AS DESCRIBED IN GS-22-008.
4. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 5 SECONDS IN A CONVECTION, IR OR VAPOR PHASE REFLOW OVEN.
5. SPEC : PRODUCT SPEC: GS-12-293
PACKING SPEC: GS-14-988

NO	DESCRIPTION	Quantity (pcs)	Material	FINISH	REMARKS
1	Signal Contact	30	COPPER ALLOY	CONTACT AREA : Au 0.2um (80u")MIN. OVER Ni 1.5um (60u")MIN.	SOLDER AREA : Sn 2.0um(80u")MIN. OVER Ni 1.5um (60u")MIN.
2	Ground Contact	1	COPPER ALLOY	Sn 2.0um (80u")MIN. OVER Ni 1.27um (60u")MIN.	UL94 V-0
3	Insulator	1	HEAT RESISTING PLASTIC		
4	Shell	1	STAINLESS STEEL	Sn 2.0um (80u")MIN. OVER Ni 1.27um (60u")MIN.	




APPLICABLE P.C.B. DIMENSION(REF.)


SHEET INDEX	ISSUE	H	H	H	MAT	DATE	CUSTOMER
SH NO.	1	2	3				
TOLERANCES UNLESS OTHERWISE SPECIFIED	±0.8	±0.4	±0.1	±0.1	±0.1	±0.1	±0.1
FINISH	SEE NOTE	SEE NOTE	SEE NOTE	SEE NOTE	SEE NOTE	SEE NOTE	SEE NOTE
DR	Sterling Lin	8/17/05	8/17/05	8/17/05	8/17/05	8/17/05	8/17/05
ENGR	Sterling Lin	8/17/05	8/17/05	8/17/05	8/17/05	8/17/05	8/17/05
CHK	Sterling Lin	8/17/05	8/17/05	8/17/05	8/17/05	8/17/05	8/17/05
APPD	H C Liou	8/17/05	8/17/05	8/17/05	8/17/05	8/17/05	8/17/05



TITLE
Standard Locking Type LVDS Board Connector for LCD (On Type) Panels
PRODUCT FAMILY



FEEDING

DO NOT SCALE PRINT
DE-004A REV F