




SIGN	DATE	DESCRIPTION	APPROVER
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

- Material:
- Insulator(housing): Thermoplastic (UL94V-0)
 - Insulator(cover): Thermoplastic (UL94V-0)
 - Metal housing: Steel
 - Terminal screw: Steel Zinc plating "-" slot type.
 - Contact: Brass,Tin plated.

- Electrical:
- cULus
- Voltage rating: 300V
 - Current rating: 8A
 - Wire range:
 - Solid wire(AWG): 16-28
 - Stranded wire(AWG): 16-28
 - Torque: 1.7 Lb-In.
 - Screw: M2
 - Wire strip length: 8-9mm
 - Withstanding Voltage: 1.6KV
 - Operating temperature: -40°C to +115°C

RoHS Compliant

PART NUMBER:

OSTTRXX3550

No. of Poles
02 2 Poles
03 3 Poles
...
24 24 Poles

COLOR
0: Black
5: Green (Standard)
6: Blue
8: Grey



ON-SHORE TECHNOLOGY, INC.

TITLE		OSTTR 3.81mm 90D Series			
PART NO.	OSTTRXX3550			DWG NO.	OSTTRXX3550.DWG
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Tony 2008.06.10	Tony 2008.06.10		UNIT: mm SCALE: NONE SHEET: 01/01 Tolerance X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
				REV.: B	