






DETAIL F
2 PLC




DETAIL C



DETAIL D




DETAIL E



P.C. BOARD MOUNTING DIMENSIONS
P.C. BOARD THICKNESS: 1.57[.062]

		TRAY	SEE DETAIL E	6	4	7-747840-1
		—	SEE DETAIL E	6	3	7-747840-0
		TRAY	SEE DETAIL D	6	4	6-747840-9
9	OBSOLETE	TRAY	SEE DETAIL D	6	3	-6-747840-8
9	OBSOLETE	—	—	6	4	-6-747840-7
	OBSOLETE	TRAY SPECIAL	SEE DETAIL D	5	4	1-747840-2
SUPSD BY 747840-6		TUBE	SEE DETAIL E	5	4	1-747840-0
SUPSD BY 747840-3		TUBE	SEE DETAIL D	5	3	747840-9
SUPSD BY 747840-4		TUBE	SEE DETAIL D	5	4	747840-8
	OBSOLETE	—	SEE DETAIL C	5	3	747840-7
		TRAY	SEE DETAIL E	5	4	747840-6
		—	SEE DETAIL E	5	3	747840-5
		TRAY	SEE DETAIL D	5	4	747840-4
		TRAY	SEE DETAIL D	5	3	747840-3
SUPSD BY 5747840-2		—	—	5	4	747840-2
SUPSD BY 5747840-2		—	—	5	3	747840-1
		PACKAGING	MOUNTING HARDWARE	BOARDLOCK FINISH	CONTACT FINISH	PART NUMBER

THIS DRAWING IS A CONTROL DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009		OWN W.G. LENKER 05 OCT 89		 TE Connectivity	
		DW R. STONE 05 FEB 90			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 P/LC ± .- 1 P/LC ± .- 2 P/LC ± 0.13[.005] 3 P/LC ± .- 4 P/LC ± .- ANGLES ± 2° 0'		M.D. GALLOWAY 06 FEB 90 PRODUCT SPEC 108-40025 APPLICATION SPEC 114-40010	
		SIZE		CAGE CODE	
		DRAWING NO		RESTRICTED TO	
		MATERIAL		FINISH	
				A1 00779 ©=747840	
CUSTOMER DRAWING		SCALE		SHEET	
		4:1		1 of 1	
				REV 7	