

TLP3121

MEASUREMENT INSTRUMENTS


LOGIC IC TESTERS / MEMORY TESTERS

BOARD TESTERS / SCANNERS


The TOSHIBA TLP3121 Mini-flat photorelay is a small-outline photorelay, suitable for surface-mount assembly. The TLP3121 consists of a GaAs infrared-emitting diode optically coupled to a photo-MOS FET and housed in a 4-pin package. Its characteristics include low OFF-state current and low output pin capacitance.

FEATURES


- 4 pin SOP (2.54SOP4) : 2.1 mm high, 2.54 mm pitch
- 1-Form-A
- Peak Off-State Voltage : 80 V (MIN.)
- Trigger LED Current : 4 mA (MAX.)
- On-State Current : 350 mA (MAX.)
- On-State Resistance : 1.2 Ω (MAX.)
- Output Capacitance : 40 pF (MAX.)
- Isolation Voltage : 1500 Vrms (MIN.)



PIN CONFIGURATION (TOP VIEW)



SCHEMATIC



MAXIMUM RATINGS (Ta = 25°C)

| CHARACTERISTIC | | SYMBOL | RATING | UNIT |
|--|---------------------------------------|--------------------------------|---------|-------|
| LED | Forward Current | I_F | 50 | mA |
| | Forward Current Derating (Ta ≥ 25°C) | $\Delta I_F/^\circ\text{C}$ | -0.5 | mA/°C |
| | Reverse Voltage | V_R | 5 | V |
| | Junction Temperature | T_j | 125 | °C |
| DETECTOR | Off-State Output Terminal Voltage | V_{OFF} | 80 | V |
| | On-State Current | I_{ON} | 350 | mA |
| | On-State Current Derating (Ta ≥ 25°C) | $\Delta I_{ON}/^\circ\text{C}$ | -3.5 | mA/°C |
| | Junction Temperature | T_j | 125 | °C |
| Storage Temperature Range | | T_{stg} | -40~125 | °C |
| Operating Temperature Range | | T_{opr} | -20~85 | °C |
| Lead Soldering Temperature (10 s) | | T_{sol} | 260 | °C |
| Isolation Voltage (AC, 1 minute, R.H. ≤ 60%) (NOTE1) | | BV_S | 1500 | Vrms |

(NOTE1) : Device considered a two-terminal device : Pins 1 and, 2 shorted together, and pins 3 and 4 shorted together.

RECOMMENDED OPERATING CONDITIONS

| CHARACTERISTIC | SYMBOL | MIN. | TYP. | MAX. | UNIT |
|-----------------------|-----------|------|------|------|------|
| Supply Voltage | V_{DD} | — | — | 64 | V |
| Forward Current | I_F | 5 | — | 30 | mA |
| On-State Current | I_{ON} | — | — | 350 | mA |
| Operating Temperature | T_{opr} | 25 | — | 60 | °C |

INDIVIDUAL ELECTRICAL CHARACTERISTICS (Ta = 25°C)

| CHARACTERISTIC | | SYMBOL | TEST CONDITION | MIN. | TYP. | MAX. | UNIT |
|----------------|-------------------|-----------|--|------|------|------|------|
| LED | Forward Voltage | V_F | $I_F = 10 \text{ mA}$ | 1.0 | 1.15 | 1.3 | V |
| | Reverse Current | I_R | $V_R = 5 \text{ V}$ | — | — | 10 | μA |
| | Capacitance | C_T | $V = 0, f = 1 \text{ MHz}$ | — | 15 | — | pF |
| DETECTOR | Off-State Current | I_{OFF} | $V_{OFF} = 30 \text{ V}, T_a = 50^\circ\text{C}$ | — | 200 | 1000 | pA |
| | Capacitance | C_{OFF} | $V = 0, f = 100 \text{ MHz}$ | — | 30 | 40 | pF |

COUPLED ELECTRICAL CHARACTERISTICS (Ta = 25°C)

| CHARACTERISTIC | SYMBOL | TEST CONDITION | MIN. | TYP. | MAX. | UNIT |
|---------------------|----------|--|------|------|------|----------|
| Trigger LED Current | I_{FT} | $I_{ON} = 350 \text{ mA}$ | — | 1 | 4 | mA |
| Return LED Current | I_{FC} | $I_{OFF} = 10 \text{ } \mu\text{A}$ | 0.2 | 0.75 | — | mA |
| On-State Resistance | R_{ON} | $I_{ON} = 350 \text{ mA}$, $I_F = 5 \text{ mA}$ | — | 1.0 | 1.2 | Ω |

ISOLATION CHARACTERISTICS (Ta = 25°C)







| CHARACTERISTIC | SYMBOL | TEST CONDITION | MIN. | TYP. | MAX. | UNIT |
|-----------------------------|--------|---|--------------------|-----------|------|-----------|
| Capacitance Input to Output | C_S | $V_S = 0 \text{ V}$, $f = 1 \text{ MHz}$ | — | 0.8 | — | pF |
| Isolation Resistance | R_S | $V_S = 500 \text{ V}$, R.H. $\leq 60\%$ | 5×10^{10} | 10^{14} | — | Ω |
| Isolation Voltage | BV_S | AC, 1 minute | 1500 | — | — | V_{rms} |
| | | AC, 1 second (in oil) | — | 3000 | — | |
| | | DC, 1 minute (in oil) | — | 3000 | — | Vdc |




SWITCHING CHARACTERISTICS (Ta = 25°C)

| CHARACTERISTIC | SYMBOL | TEST CONDITION | MIN. | TYP. | MAX. | UNIT |
|----------------|-----------|--|------|------|------|---------------|
| Turn-on Time | t_{ON} | $R_L = 200 \text{ } \Omega$ (NOTE 2) $V_{DD} = 20 \text{ V}$, $I_F = 5 \text{ mA}$ | — | 300 | 500 | μs |
| Turn-off Time | t_{OFF} | | — | 300 | 500 | |

(NOTE 2) : SWITCHING TIME TEST CIRCUIT

L





RESTRICTIONS ON PRODUCT USE

030619EBC

- The information contained herein is subject to change without notice.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA for any infringements of patents or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of TOSHIBA or others.
- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The products described in this document are subject to the foreign exchange and foreign trade laws.
- TOSHIBA products should not be embedded to the downstream products which are prohibited to be produced and sold, under any law and regulations.
- GaAs(Gallium Arsenide) is used in this product. The dust or vapor is harmful to the human body. Do not break, cut, crush or dissolve chemically.