










RECOMMENDED CIRCUIT PATTERN
PER IPC-D300 TYPE II, CLASS C
(COMPONENT SIDE)

5	OBSELETE	NO	214	107	215.88		540	1-223008-2
	OBSELETE	NO	130	65	131.88		330	1-223008-1
5	OBSELETE	NO	118	59	119.88		300	1-223008-0
	OBSELETE	NO	106	53	107.88		270	223008-9
	OBSELETE	NO	94	47	95.88		240	223008-8
	OBSELETE	NO	82	41	83.88		210	223008-7
	OBSELETE	NO	70	35	71.88		180	223008-6
	OBSELETE	NO	58	29	59.88		150	223008-5
	OBSELETE	NO	46	23	47.88		120	223008-4
	OBSELETE	NO	34	17	35.88		90	223008-3
	NO	22	11	23.88		60	223008-2	
	YES	10	5	11.88		30	223008-1	
	POSITIONING PEGS	C	B	A	FINISH	NO. OF SIGNAL POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 08/FEB/96 R. BUCHHEISTER CHK 08/FEB/96 D. BAECHTLE 08/FEB/96		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES: UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 0.13 3 PLC ± 4 PLC ± 5 ANGLES ± ±		NAME ASSEMBLY, RECEPTACLE, SIGNAL, RIGHT ANGLE, Z-PACK 2mm FB, 5 ROW, PRESS FIT LEAD PRODUCT SPEC APPLICATION SPEC	
MATERIAL 		WEIGHT FINISH 		SIZE CAGE CODE DRAWING NO RESTRICTED TO A1 00779 C=223008	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 of 1 REV R	