








DATE	ECO NO	DESCRIPTION	BY
Sep 5 1994	CDN 94067		A.K



IC TO BE SEATED



RECOMMENDED IC (REF.)



FOOTPRINT

FOOTPRINT AS VIEWED LOOKING DOWN FROM TOP OF SOCKET

Performance.

1. Insulation Resistance : 1000 MΩ min. at 500V.D.C
2. Dielectric Withstanding Voltage : 600 V.A.C (RMS)
3. Contact Resistance : 30 mΩ max. at 20 mV max.
4. Temperature Range : -40°C ~ +150°C

④	CONTACT- (2)	Be Cu	4	PLATING : Au
③	CONTACT- (1)	Be Cu	4	PLATING : Au
②	BASE-8P	PEI	1	COLOR : BLACK
①	COVER-8P	PEI	1	COLOR : BLACK
P.NO	PART DESCRIPTION	MATERIAL	QTY	NOTE
GENERAL TOLERANCES ±0.3 (±.012)		 WELLS JAPAN LIMITED ウエルズ・ジャパン株式会社		
UNIT	SCALE			
mm (in.)	—			
DRAWN	—			
CHECKED	—			
APPROVED	—			
		TITLE		
		SOP 8P SOCKET		
		DWG NO.		
		652B0082211-002		