

Features

LED Driver

- Low Profile Case (13mm height max.)
- 350mA to 700mA Constant Current Outputs
- Terminal Block Input/Output with Cable Clamps
- Fully Protected (OLP, SCP, OCP, OTP)
- Low Standby Power, ErP conform
- Low cost

Description

These low profile constant current LED drivers have been designed for cost-sensitive applications. The SELV outputs are suitable for both independently supplied or built-in power-supply LED luminaires. Their low profile design allows them to be invisibly built into furniture, discreetly mounted under shelves or integrated in space-restricted applications such as coving lighting, strip lighting or troffer lighting systems. The power supplies are short circuit and overload protected and come with a full 3-year warranty.

RECOM
AC/DC Converter

RACD12-LP

**12 Watt
Constant
Current Single
Output**



Selection Guide

Part Number	nom. Input Voltage [VAC]	Input Current [mA]	Output Voltage Range [VDC]	Output Current [mA]	Efficiency typ. [%]	Output Power max. [W]
RACD12-350-LP	230	130	2-37	350	86	13W
RACD12-500-LP	230	130	2-24	500	81	12W
RACD12-700-LP	230	130	2-19	700	85	13W

All LED Drivers may not be used without a load. They must be switched on the primary side only.

Noncompliance may damage the LED or reduce its lifetime.

Specifications (measured @ ta= 25°C, 240VAC and rated load)

BASIC CHARACTERISTICS

Parameter	Condition	Min.	Typ.	Max.
Input Voltage Range		198VAC	230VAC	264VAC
Inrush Current				8.0A
Start-up Time				500ms
Input Frequency Range		47Hz		63Hz
No Load Power Consumption				0.5W
Power Factor	full load, 230VAC			0.55
Internal Operating Frequency	full load	60kHz		140kHz
Output Ripple Current ⁽¹⁾				50mA _{p-p}

Notes:

Note1: Measured at 20MHz BW using 0.1µF & 47µF parallel capacitor.



IEC/EN61347-1 Certified
IEC/EN61347-2-13 Certified
ENEC Certified
CB Report
EN55015 Compliant

REGULATIONS

Parameter	Condition	Value
Output Current Accuracy		±5% max.
Line Regulation		5% max.
Load Regulation		5% max.

Specifications (measured @ $ta = 25^\circ\text{C}$, 240VAC and rated load)

PROTECTION		
Parameter	Condition	Value
Input Fuse	external fuse is recommended	T1A
Open Circuit Protection (OCP)		auto recovery after fault condition is removed
Over Load Protection (OLP)		auto recovery after fault condition is removed
Over Voltage Protection (OVP)		auto recovery after fault condition is removed
Over Temperature Protection (OTP)	110°C Tcase	auto recovery after fault condition is removed
Isolation Voltage	I/P to O/P	3.75kVAC / 1 minute

Maximum loading of automatic circuit breakers


@ 230VAC, 10hm, 90° phase angle and max. load

Circuit Breaker	Circuit Breaker Current				
	Typ	10A	16A	20A	25A
B		17	28	35	44
C		37	59	74	92

ENVIRONMENTAL

Parameter	Condition	Value
Operating Temperature Range		-20°C to +50°C, Ambient
Maximum Case Temperature		+80°C
Operating Altitude		2000m
Operating Humidity		5% to 85% RH, non condensing
IP Rating		IP20
Pollution Degree		PD2
Design Lifetime		30 x 10 ³ hours

Derating Graph




SAFETY AND CERTIFICATIONS

Certificate Type	Report Number	Standard
Lamp Controlgear General Requirements for Safety	305987 + 305985	IEC61347-1, 2nd Edition, 2012 EN61347-1, 2nd Edition 2013
Lamp Controlgear Particular Requirements		IEC61347-2-13, 2nd Edition, 2014 EN61347-2-13, 2014
D.C. or A.C. Controlgears for LED Performance Requirements	305984-1 + 305984-1	IEC/EN62384, 1st Edition, 2009
RoHS 2.1	LCS1606201548R	RoHS-2011/65/EU + AM-2015/863

continued on next page

Specifications (measured @ $ta = 25^\circ\text{C}$, 240VAC and rated load)


EMI Compliance		Standard / Criterion
Equipment for general Lighting Purpose - EMC Immunity Requirements	305984 + 305985	EN61547, 2009
Limits and methods of measurement of radio disturbance characteristics of electrical lighting and similar equipment		EN55015, 2015
Assessment of lighting equipment related to human exposure to electromagnetic fields		EN61493, 2015
ESD Electrostatic discharge immunity test	$\pm 8\text{kV}$ Air Discharge, $\pm 4\text{kV}$ Contact Discharge	EN61000-4-2, 2009, Criteria B
Radiated, radio-frequency, electromagnetic field immunity test	3V/m	EN61000-4-3, 2010, Criteria A
Fast Transient and Burst Immunity	$\pm 0.5\text{kV}$ (DC Output) $\pm 1\text{kV}$ (AC Input)	EN61000-4-4, 2012, Criteria B
Surge Immunity	$\pm 0.5\text{kV}$ (AC Input)	EN61000-4-5, 2014, Criteria C
Immunity to conducted disturbances, induced by radio-frequency fields	3V	EN61000-4-6, 2014, Criteria A
Voltage Dips and Interruptions	95% reduction 30% reduction	EN61000-4-11, 2014, Criteria B EN61000-4-11, 2014, Criteria C
Limits of Harmonic Current Emissions		EN61000-3-2, Class C, 2014
Voltage Fluctuations and Flicker in Public Low-Voltage Systems $\leq 16\text{A}$ per phase		EN61000-3-3, 2013

DIMENSION and PHYSICAL CHARACTERISTICS																											
Parameter	Type	Value																									
Material	Case	Plastic (UL94V-2)																									
Package Dimension (LxWxH)		128.0 x 50.0 x 13.0mm																									
Package Weight		70g																									
Mechanical Dimensions																											
																											
<p>2 mounting screws are included</p>																											
<p>Connection via Screw Terminal</p> <table border="1"> <thead> <tr> <th>#</th> <th>Function</th> <th>Solid Wire</th> <th>Stranded Wire ⁽²⁾</th> <th>AWG</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>VAC in (N)</td> <td>0.75-1.5mm²</td> <td>0.75-1.5mm²</td> <td>20-16</td> </tr> <tr> <td>2</td> <td>VAC in (L)</td> <td>0.75-1.5mm²</td> <td>0.75-1.5mm²</td> <td>20-16</td> </tr> <tr> <td>3</td> <td>LED+</td> <td>0.5-1.5mm²</td> <td>0.5-1.5mm²</td> <td>21-16</td> </tr> <tr> <td>4</td> <td>LED-</td> <td>0.5-1.5mm²</td> <td>0.5-1.5mm²</td> <td>21-16</td> </tr> </tbody> </table> <p>Notes:</p> <p>Note2: The use of sleeve or ferrule terminations is recommended.</p>			#	Function	Solid Wire	Stranded Wire ⁽²⁾	AWG	1	VAC in (N)	0.75-1.5mm ²	0.75-1.5mm ²	20-16	2	VAC in (L)	0.75-1.5mm ²	0.75-1.5mm ²	20-16	3	LED+	0.5-1.5mm ²	0.5-1.5mm ²	21-16	4	LED-	0.5-1.5mm ²	0.5-1.5mm ²	21-16
#	Function	Solid Wire	Stranded Wire ⁽²⁾	AWG																							
1	VAC in (N)	0.75-1.5mm ²	0.75-1.5mm ²	20-16																							
2	VAC in (L)	0.75-1.5mm ²	0.75-1.5mm ²	20-16																							
3	LED+	0.5-1.5mm ²	0.5-1.5mm ²	21-16																							
4	LED-	0.5-1.5mm ²	0.5-1.5mm ²	21-16																							
<p>wire stripping length: 6-7mm recommended tightening torque: 0.25Nm tc= case temperature measuring point FC= fixing centers NC= no connection Tolerance: xx.x= $\pm 0.5\text{mm}$ xx.xx= $\pm 0.35\text{mm}$</p>																											

Specifications (measured @ $ta = 25^\circ\text{C}$, 240VAC and rated load)

INSTALLATION and APPLICATION

Connection



PACKAGING INFORMATION

Parameter	Type	Value
Packaging Dimension (LxWxH)		265.0 x 139.0 x 62.0mm
Packaging Quantity	Cardboard Box	10pcs
Storage Temperature Range		-20°C to +70°C
Storage Humidity		5% - 85% RH

The product information and specifications are subject to change without prior notice. RECOM products are not authorized for use in safety-critical applications (such as life support) without RECOM's explicit written consent. A safety-critical application is defined as an application where a failure of a RECOM product may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The buyer shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.